


SMP Female to Straight Cut Lead Cable Using PE-047SR Coax



PE3C7804

Configuration

- Connector 1: SMP Female
- Connector 2: Straight Cut Lead
- Cable Type: PE-047SR
- Coax Cable Group: 18
- Coax Flex Type: Semi-Rigid



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C7804 50 ohm SMP female to straight cut lead cable using PE-047SR coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.012 lbs [5.44 g]

Cable

Cable Type	PE-047SR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Copper
Repeated Minimum Bend Radius	0.05 in [1.27 mm]

SMP Female to Straight Cut Lead
Cable Using PE-047SR Coax



PE3C7804

Connectors

Description	Connector 1	Connector 2
Type	SMP Female	Straight Cut Lead
Specification	DESC 94008	
Impedance	50 Ohms	0 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	
Contact Plating Specification	MIL-G-45204	
Dielectric Type	PTFE	
Body Material and Plating	Beryllium Copper, Gold	
Body Plating Specification	MIL-G-45204	

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

SMP Female to Straight Cut Lead Cable Using PE-047SR Coax




PE3C7804

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C7804-12 = 12 inches long cable
PE3C7804-100cm = 100 cm long cable

SMP Female to Straight Cut Lead Cable Using PE-047SR Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female to Straight Cut Lead Cable Using PE-047SR Coax PE3C7804](#)

URL: <https://www.pasternack.com/smp-female-to-straight-cut-lead-cable-using-pe-047sr-pe3c7804-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C7804 CAD Drawing

SMP Female to Straight Cut Lead Cable Using PE-047SR Coax

