

2.92mm Male to 2.92mm Female Bulkhead Cable Using PE-SR405FL Coax




RF Cable Assemblies Technical Data Sheet

PE3C6293


Configuration

- Connector 1: 2.92mm Male
- Connector 2: 2.92mm Female Bulkhead
- Cable Type: PE-SR405FL



Features

- 69.5% Phase Velocity



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C6293 2.92mm male to 2.92mm female bulkhead cable using PE-SR405FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack 2.92mm to 2.92mm cable assembly has a male to female gender configuration with 50 ohm formable PE-SR405FL coax. Our RF cable assembly with 2.92mm bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------------|---------|---------------|---------|-----------------|
| Velocity of Propagation | | 69.5 | | % |
| Capacitance | | 29 [95.14] | | pF/ft [pF/m] |
| DC Resistance Inner Conductor | | 65.7 [215.55] | | Ω/1000ft [Ω/Km] |
| DC Resistance Outer Conductor | | 10.2 [33.46] | | Ω/1000ft [Ω/Km] |
| Operating Voltage (AC) | | | 335 | Vrms |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Female Bulkhead Cable Using PE-SR405FL Coax PE3C6293](#)



2.92mm Male to 2.92mm Female Bulkhead Cable Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet

PE3C6293

Mechanical Specifications

Cable Assembly

| | |
|--------------------------------------|---------------------------|
| Weight | 0.035 lbs [15.88 g] |
| Cable | |
| Cable Type | PE-SR405FL |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Outer Conductor Material and Plating | Copper, Tin |
| Repeated Minimum Bend Radius | 0.78 in [19.81 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------------|------------------------------------|------------------------------------|
| Type | 2.92mm Male | 2.92mm Female Bulkhead |
| Impedance | 50 Ohms | 50 Ohms |
| Mating Cycles | 500 | |
| Contact Material and Plating | Beryllium Copper, Gold over Nickel | Beryllium Copper, Gold over Nickel |
| Contact Plating Specification | 50 μ in minimum | 50 μ in minimum |
| Dielectric Type | PEI | |
| Body Material and Plating | Beryllium Copper, Gold over Nickel | Passivated Stainless Steel |
| Body Plating Specification | 50 μ in minimum | SAE-AMS-2700 |
| Coupling Nut Material and Plating | Passivated Stainless Steel | |
| Coupling Nut Plating Specification | ASTM-A582 | |
| Hex Size | 5/16 inch | |
| Torque | 8 in-lbs [0.9 Nm] | |

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Female Bulkhead Cable Using PE-SR405FL Coax PE3C6293](#)



2.92mm Male to 2.92mm Female Bulkhead Cable Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet

PE3C6293

How to Order

Part Number Configuration:

PE3C6293

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C6293-12 = 12 inches long cable
PE3C6293-100cm = 100 cm long cable

2.92mm Male to 2.92mm Female Bulkhead Cable Using PE-SR405FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Female Bulkhead Cable Using PE-SR405FL Coax PE3C6293](#)

URL: <https://www.pasternack.com/2.92mm-male-to-2.92mm-female-bulkhead-cable-using-pe-sr405fl-pe3c6293-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C6293 CAD Drawing

2.92mm Male to 2.92mm Female Bulkhead Cable Using PE-SR405FL Coax

