

2.92mm Male to 2.92mm Male Low Loss Cable  
12 Inch Length Using PECX006 Coax



## RF Cable Assemblies Technical Data Sheet

**PE3C6493-12**

### Configuration

- Connector 1: 2.92mm Male
- Connector 2: 2.92mm Male
- Cable Type: PECX006
- Coax Flex Type: Semi-Rigid

### Features

- Max Frequency 45 GHz
- 76.5% Phase Velocity
- 500 Mating Cycles
- Maximum Cable Assembly Length of 5 Feet

### Applications

- General Purpose
- Laboratory Use

### Description

Pasternack's PE3C6493-12 2.92mm male to 2.92mm male 12 inch cable using 086 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack 2.92mm to 2.92mm cable assembly has a male to male gender configuration with 50 ohm semi-rigid PECX006 coax. The PE3C6493-12 2.92mm male to 2.92mm male cable assembly operates to 45 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		45	GHz
VSWR			1.4:1	
Velocity of Propagation		76.5		%

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	5	10	18	26.5	GHz
Insertion Loss (Typ.)	0.18	0.57	0.82	1.11	1.38	dB/ft

Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Low Loss Cable 12 Inch Length Using PECX006 Coax PE3C6493-12](#)



2.92mm Male to 2.92mm Male Low Loss Cable  
12 Inch Length Using PECK006 Coax

## RF Cable Assemblies Technical Data Sheet

PE3C6493-12

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of  $0.04 * \text{SQRT}(F\text{GHz})$  dB maximum per connector.

## Mechanical Specifications

## Cable Assembly

Weight	0.047 lbs [21.32 g]
<b>Cable</b>	
Cable Type	PECX006
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	Microporous PTFE
Number of Shields	1
Outer Conductor Material and Plating	Copper, Tin
One Time Minimum Bend Radius	0.25 in [6.35 mm]

## Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male Threaded	2.92mm Male Threaded
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	500
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	ASTM-B488	ASTM-B488
Dielectric Type	PTFE	PTFE
Body Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Plating Specification	ASTM-B488	ASTM-B488
Coupling Nut Material and Plating	Steel	Steel
Torque	8 in-lbs [0.9 Nm]	8 in-lbs [0.9 Nm]

## Environmental Specifications

## Temperature

## Operating Range

-65 to +165 deg C

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

### Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Low Loss Cable 12 Inch Length Using PECLX006 Coax PE3C6493-12](#)


2.92mm Male to 2.92mm Male Low Loss Cable  
12 Inch Length Using PECX006 Coax



## RF Cable Assemblies Technical Data Sheet

**PE3C6493-12**

### Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Low Loss Cable 12 Inch Length Using PECX006 Coax PE3C6493-12](#)

2.92mm Male to 2.92mm Male Low Loss Cable  
12 Inch Length Using PECX006 Coax



## RF Cable Assemblies Technical Data Sheet

**PE3C6493-12**

### How to Order

Part Number Configuration:

**PE3C6493**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C6493-12 = 12 inches long cable  
PE3C6493-100cm = 100 cm long cable

2.92mm Male to 2.92mm Male Low Loss Cable 12 Inch Length Using PECX006 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Low Loss Cable 12 Inch Length Using PECX006 Coax PE3C6493-12](#)

URL: <https://www.pasternack.com/2.92mm-male-2.92mm-male-086-cable-assembly-pe3c6493-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C6493-12 CAD Drawing

2.92mm Male to 2.92mm Male Low Loss Cable 12 Inch Length Using PECKX006 Coax

REVISIONS																																			
REV.	DESCRIPTION	DATE	APPROVED																																
A	INITIAL RELEASE	09/11/19	SELLIS																																
<table border="1"> <tr> <td colspan="4">THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.</td></tr> <tr> <td>PE</td><td><b>PASTERNAK</b></td><td>an INFINITI<sup>®</sup> brand</td><td></td></tr> <tr> <td>Pasterнак Enterprises, Inc.</td><td>P.O.Box 16759, Irvine, CA 92623.</td><td></td><td></td></tr> <tr> <td>Phone: 1.949.261.1920</td><td>1.866.727.8376</td><td></td><td></td></tr> <tr> <td>Fax: 1.949.261.7451</td><td></td><td></td><td></td></tr> <tr> <td>www.pasterнак.com</td><td>e-mail: sales@pasterнак.com</td><td></td><td></td></tr> <tr> <td>SIZE / CAGE</td><td>DRAWN BY</td><td>PART NUMBER</td><td>REV</td></tr> <tr> <td>A</td><td>K.DANG</td><td>PE3C6493</td><td>A</td></tr> </table>				THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.				PE	<b>PASTERNAK</b>	an INFINITI <sup>®</sup> brand		Pasterнак Enterprises, Inc.	P.O.Box 16759, Irvine, CA 92623.			Phone: 1.949.261.1920	1.866.727.8376			Fax: 1.949.261.7451				www.pasterнак.com	e-mail: sales@pasterнак.com			SIZE / CAGE	DRAWN BY	PART NUMBER	REV	A	K.DANG	PE3C6493	A
THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.																																			
PE	<b>PASTERNAK</b>	an INFINITI <sup>®</sup> brand																																	
Pasterнак Enterprises, Inc.	P.O.Box 16759, Irvine, CA 92623.																																		
Phone: 1.949.261.1920	1.866.727.8376																																		
Fax: 1.949.261.7451																																			
www.pasterнак.com	e-mail: sales@pasterнак.com																																		
SIZE / CAGE	DRAWN BY	PART NUMBER	REV																																
A	K.DANG	PE3C6493	A																																

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN ( ) ARE MILLIMETERS  
TOLERANCES:  
 $\pm 0.2$  [6.08] FRACTIONS  
 $\pm 0.01$  [0.25]  $\pm 1/32$   
 $\pm 0.005$  [0.13] ANGLES  $\pm 1^\circ$   
 ALL DIMENSIONS SHOWN  
 ARE FOR REFERENCE ONLY.

THIRD ANGLE PROJECTION

**PE** **PASTERNAK**  
an INFINITI<sup>®</sup> brand

Pasterнак Enterprises, Inc.  
P.O.Box 16759, Irvine, CA 92623.  
Phone: 1.949.261.1920 | 1.866.727.8376  
Fax: 1.949.261.7451  
www.pasterнак.com | e-mail: sales@pasterнак.com

SCALE N/A

1 OF 1

REV A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO US LAW PROHIBITED.

T-Rev 3