



Mini SMP Female to SMA Male Right Angle Cable  
24 Inch Length Using PE-SR405FL Coax

**RF Cable Assemblies Technical Data Sheet**

**PE3C7629-24**

**Configuration**

- Connector 1: Mini SMP Female
- Connector 2: SMA Male Right Angle
- Cable Type: PE-SR405FL

**Features**

- Max Frequency 12.4 GHz
- 69.5% Phase Velocity


**Applications**

- General Purpose
- Laboratory Use

**Description**

Pasternack's PE3C7629-24 Mini SMP female to SMA male right angle 24 inch cable using PE-SR405FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack Mini SMP to SMA cable assembly has a female to male gender configuration with 50 ohm formable PE-SR405FL coax. The PE3C7629-24 Mini SMP female to SMA male cable assembly operates to 12.4 GHz. The right angle SMA interface on the PE-SR405FL cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female to SMA Male Right Angle Cable 24 Inch Length Using PE-SR405FL Coax PE3C7629-24](#)



## Mini SMP Female to SMA Male Right Angle Cable 24 Inch Length Using PE-SR405FL Coax

### RF Cable Assemblies Technical Data Sheet

**PE3C7629-24**

#### Electrical Specifications

| Description                   | Minimum | Typical       | Maximum | Units           |
|-------------------------------|---------|---------------|---------|-----------------|
| Frequency Range               | DC      |               | 12.4    | GHz             |
| VSWR                          |         |               | 1.4:1   |                 |
| Velocity of Propagation       |         | 69.5          |         | %               |
| Capacitance                   |         | 29 [95.14]    |         | pF/ft [pF/m]    |
| DC Resistance Inner Conductor |         | 65.7 [215.55] |         | Ω/1000ft [Ω/Km] |
| DC Resistance Outer Conductor |         | 10.2 [33.46]  |         | Ω/1000ft [Ω/Km] |

#### Specifications by Frequency

| Description           | F1  | F2   | F3  | F4  | F5   | Units |
|-----------------------|-----|------|-----|-----|------|-------|
| Frequency             | 0.5 | 1    | 2.5 | 5   | 12.4 | GHz   |
| Insertion Loss (Typ.) | 0.6 | 0.76 | 1   | 1.4 | 2.04 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

#### Mechanical Specifications

##### Cable Assembly

|          |                  |
|----------|------------------|
| Length*  | 24 in [609.6 mm] |
| Diameter | 0.315 in [8 mm]  |

##### Cable

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Type                           | PE-SR405FL                |
| Impedance                            | 50 Ohms                   |
| Inner Conductor Type                 | Solid                     |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type                      | PTFE                      |
| Number of Shields                    | 1                         |
| Outer Conductor Material and Plating | Copper, Tin               |
| Repeated Minimum Bend Radius         | 0.78 in [19.81 mm]        |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female to SMA Male Right Angle Cable 24 Inch Length Using PE-SR405FL Coax PE3C7629-24](#)



## Mini SMP Female to SMA Male Right Angle Cable 24 Inch Length Using PE-SR405FL Coax

### RF Cable Assemblies Technical Data Sheet

**PE3C7629-24**

#### Connectors

| Description                        | Connector 1            | Connector 2           |
|------------------------------------|------------------------|-----------------------|
| Type                               | Mini SMP Female        | SMA Male Right Angle  |
| Specification                      |                        | MIL-STD-348A          |
| Impedance                          | 50 Ohms                | 50 Ohms               |
| Contact Material and Plating       | Beryllium Copper, Gold | Brass, Gold           |
| Contact Plating Specification      | MIL-G-45204            | 50 µin minimum        |
| Dielectric Type                    | PTFE                   | PTFE                  |
| Body Material and Plating          | Beryllium Copper, Gold | Stainless Steel, Gold |
| Body Plating Specification         | MIL-G-45204            | 30 µin minimum        |
| Coupling Nut Material and Plating  |                        | Brass, Nickel         |
| Coupling Nut Plating Specification |                        | 100 µin minimum       |
| Hex Size                           |                        | 5/16 inch             |
| Torque                             |                        | 3 in-lbs [0.34 Nm]    |

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female to SMA Male Right Angle Cable 24 Inch Length Using PE-SR405FL Coax PE3C7629-24](#)



## Mini SMP Female to SMA Male Right Angle Cable 24 Inch Length Using PE-SR405FL Coax

### RF Cable Assemblies Technical Data Sheet

**PE3C7629-24**

#### How to Order

Part Number Configuration:

**PE3C7629**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C7629-12 = 12 inches long cable  
PE3C7629-100cm = 100 cm long cable

Mini SMP Female to SMA Male Right Angle Cable 24 Inch Length Using PE-SR405FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female to SMA Male Right Angle Cable 24 Inch Length Using PE-SR405FL Coax PE3C7629-24](https://www.pasternack.com/mini-smp-female-sma-male-pe-sr405fl-cable-assembly-pe3c7629-24-p.aspx)


URL: <https://www.pasternack.com/mini-smp-female-sma-male-pe-sr405fl-cable-assembly-pe3c7629-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C7629-24 CAD Drawing

Mini SMP Female to SMA Male Right Angle Cable  
24 Inch Length Using PE-SR405FL Coax

| REVISIONS |                 |            |          |
|-----------|-----------------|------------|----------|
| REV.      | DESCRIPTION     | DATE       | APPROVED |
| A         | INITIAL RELEASE | 10/16/2020 | S. ELLIS |



|                                                                                                                                                                                                                                                                                                                                                                                         |  |                                                                                                                                                                                                                                                                                                                                                                                                                                           |                    |                                                                                                                                                                                                                                                                                  |                      |          |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|----------|
| UNLESS OTHERWISE SPECIFIED<br>LEADING DIMENSIONS ARE INCHES<br>DIMENSIONS IN [ ] ARE MILLIMETERS                                                                                                                                                                                                                                                                                        |  | <div> <b>PASTERNAK®</b><br/>an INFINITE brand</div> <div>Pasternack Enterprises, Inc.<br/>P.O Box 16759, Irvine, CA 92623.<br/>Phone: 1.949.261.1920   1.866.727.8376<br/>Fax: 1.949.261.7451<br/>Website: <a href="http://www.pasternack.com">www.pasternack.com</a><br/>E-mail: <a href="mailto:sales@pasternack.com">sales@pasternack.com</a></div> |                    | THIRD-ANGLE PROJECTION                                                                                                                                                                                                                                                           |                      |          |
| TOLERANCES:<br><br>X = ± .2    [ .008 ]    FRACTIONS<br>.XX = ± .02    [ .51 ]    ± 1/32<br>.XXX = ± .005    [ .13 ]    ANGLES ± 1°<br><br>CABLE LENGTH (L) TOLERANCES:<br><br>L ≤ 12 [305] = ± .1 [25] / -0<br>12 [305] < L ≤ 60 [1524] = ± .2 [51] / -0<br>60 [1524] < L ≤ 120 [3048] = ± .4 [102] / -0<br>120 [3048] < L ≤ 300 [7620] = ± .6 [152] / -0<br>300 [7620] < L = +5% / -0 |  | <div></div> <div>THE INFORMATION AND<br/>DESIGN IN THIS DOCUMENT<br/>IS THE PROPERTY OF<br/>PASTERNAK CORPORATION<br/>ALL RIGHTS RESERVED.</div> <div>SHEET 1 OF 1</div> <div>SCALE N/A</div>                                                                                                                                                          |                    | <div></div> <div>THE INFORMATION AND<br/>DESIGN IN THIS DOCUMENT<br/>IS THE PROPERTY OF<br/>PASTERNAK CORPORATION<br/>ALL RIGHTS RESERVED.</div> <div>SHEET 1 OF 1</div> <div>SCALE N/A</div> |                      |          |
| ALL DIMENSIONS SHOWN<br>ARE FOR REFERENCE ONLY.                                                                                                                                                                                                                                                                                                                                         |  | SIZE<br>A                                                                                                                                                                                                                                                                                                                                                                                                                                 | CAGE CODE<br>53919 | DRAWN BY<br>K.DANG                                                                                                                                                                                                                                                               | ITEM NO.<br>PE3C7629 | REV<br>A |

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.