



NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM
Cable 60 Inch Length Using 1/4 inch Superflexible Coax

RF Cable Assemblies Technical Data Sheet


PE3C7855-60

Configuration

- Connector 1: NEX10 Male Right Angle
- Connector 2: NEX10 Female Bulkhead
- Cable Type: 1/4" Superflexible

Features

- Max Frequency 6 GHz
- Low PIM: -150 dBc Max
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket
- Low PIM and Low Loss
- 100% Tested with PIM Test Results Marked on Cable



Applications

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Low PIM Applications and PIM Testing

Description

Pasternack's PE3C7855-60 NEX10 male right angle to NEX10 female bulkhead 60 inch cable using 1/4 inch superflexible coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack NEX10 to NEX10 cable assembly has a male to female gender configuration with 50 ohm corrugated 1/4" superflexible coax. The PE3C7855-60 NEX10 male to NEX10 female cable assembly operates to 6 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -150 dBc. The right angle NEX10 interface on the 1/4" superflexible cable allows for easier connections in tight spaces. Our RF cable assembly with NEX10 bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM Cable 60 Inch Length Using 1/4 inch Superflexible Coax PE3C7855-60](#)



NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM Cable 60 Inch Length Using 1/4 inch Superflexible Coax

RF Cable Assemblies Technical Data Sheet

PE3C7855-60

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.5:1	
Velocity of Propagation		82		%
RF Shielding	120			dB
Passive Intermodulation			-150	dBc
Capacitance		24.4 [80.05]		pF/ft [pF/m]
Inductance		0.059 [0.19]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		2.53 [8.3]		Ω/1000ft [Ω/Km]
Jacket Spark			2,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.33	0.38	0.44	0.53	0.78	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated 0.15 dB for the right angle connector and 0.1 dB for the straight connector.

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Diameter	0.62 in [15.75 mm]

Cable

Cable Type	1/4" Superflexible
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	1
Shield Layer 1	Helically Corrugated Copper Tube

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM Cable 60 Inch Length Using 1/4 inch Superflexible Coax PE3C7855-60](#)



NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM
Cable 60 Inch Length Using 1/4 inch Superflexible Coax

RF Cable Assemblies Technical Data Sheet

PE3C7855-60

Jacket Material	PE, Black
Jacket Diameter	0.303 in [7.7 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Typical Flex Cycles	20
Tensile Strength	79 lbs [35.83 Kg]

Connectors

Description	Connector 1	Connector 2
Type	NEX10 Male Right Angle	NEX10 Female Bulkhead
Specification	NEX10	NEX10
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Silver	
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Bronze, Silver
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
-----------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM Cable 60 Inch Length Using 1/4 inch Superflexible Coax PE3C7855-60](#)



NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM Cable 60 Inch Length Using 1/4 inch Superflexible Coax

RF Cable Assemblies Technical Data Sheet

PE3C7855-60

How to Order

Part Number Configuration:

PE3C7855

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C7855-12 = 12 inches long cable
PE3C7855-100cm = 100 cm long cable

NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM Cable 60 Inch Length Using 1/4 inch Superflexible Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM Cable 60 Inch Length Using 1/4 inch Superflexible Coax PE3C7855-60](https://www.pasternack.com/nex10-male-nex10-female-pe-1-4-sfhc-cable-assembly-pe3c7855-60-p.aspx)

URL: <https://www.pasternack.com/nex10-male-nex10-female-pe-1-4-sfhc-cable-assembly-pe3c7855-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

NEX10 Male Right Angle to NEX10 Female Bulkhead Low PIM
Cable 60 Inch Length Using 1/4 inch Superflexible Coax

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	PE PASTERNAK® an INFINITE® brand		THIRD-ANGLE PROJECTION	
	TOOLERANCES: $X \pm .2$ [5.08] FRACTIONS $.XX \pm .02$ [.51] $\frac{1}{32}$ $XXX \pm .005$ [.13] ANGLES $\pm ^\circ$		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION ALL RIGHTS ARE RESERVED.	
CABLE LENGTH (L) TOLERANCES: $L \leq 12$ [305] $\pm$ [25] / -0 $L \leq 12$ [305] $\pm$ [25] / -0 12 [305] $< L \leq 60$ [1524] $\pm$ [2.5] / -0 60 [1524] $< L \leq 120$ [3048] $\pm$ [4] [102] / -0 120 [3048] $< L \leq 300$ [7620] $\pm$ [6] [152] / -0 300 [7620] $< L = +5\%$ / -0	Pasternack Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasternack.com E-mail: sales@pasternack.com		1 OF 1	
	SCALE		N/A	
SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	K.DANG	PE3C7855	A
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.				

