



SMA Male to Trimmed Lead Test Probe Cable
6 Inch Length Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet


PE3C8144-6

Configuration

- Connector 1: SMA Male
- Connector 2: Trimmed Lead
- Cable Type: PE-SR405FL

Features

- Max Frequency 18 GHz
- 69.5% Phase Velocity
- 100% RF Tested prior to final trim
- 1.4 Max VSWR to 18 GHz
- 100% High Pot Tested to 500V
- 0.086 Diameter Formable coax
- Individually packed in protective tube



Applications

- General Purpose
- Test & Measurement
- Laboratory Use
- Used as an RF Test Probe to 18 GHz
- RF PCB Board Measurements
- Signal Injection

Description

Pasternack's PE3C8144-6 50 ohm SMA Male to pre-trimmed cut cable using PE-SR405FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable cable assemblies provide a convenient alternative to their semi-rigid versions, as they offer similar electrical performance but can be bent to desired shape without the use of special tools.

These SMA Male to unterminated pre-trimmed cut cable assemblies are designed to be used as convenient test probes. A common research and development application is to solder the trimmed end of the cable to an exposed microstrip trace to inject a signal or to measure a signal of interest. Each cable assembly is individually packaged in a reusable protective tube. These test probes have been 100% RF tested as a two-ended assembly prior to trimming to verify the assembly's performance to 18 GHz with a maximum VSWR of 1.4:1. Flush Cut Test Probes are also available.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to Trimmed Lead Test Probe Cable 6 Inch Length Using PE-SR405FL Coax PE3C8144-6](#)



SMA Male to Trimmed Lead Test Probe Cable 6 Inch Length Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet

PE3C8144-6

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ω /1000ft [Ω /Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ω /1000ft [Ω /Km]

Mechanical Specifications

Cable Assembly

Length* 6 in [152.4 mm]

Cable

Cable Type PE-SR405FL
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper Clad Steel, Silver
 Dielectric Type PTFE
 Number of Shields 1
 Outer Conductor Material and Plating Copper, Tin
 Repeated Minimum Bend Radius 0.78 in [19.81 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to Trimmed Lead Test Probe Cable 6 Inch Length Using PE-SR405FL Coax PE3C8144-6](#)



SMA Male to Trimmed Lead Test Probe Cable
6 Inch Length Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet

PE3C8144-6

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	Trimmed Lead
Specification	MIL-STD-348A	
Impedance	50 Ohms	
Mating Cycles	500	
Contact Material and Plating	Brass, Gold	
Contact Plating Specification	50 µin minimum	
Dielectric Type	PTFE	
Body Material and Plating	Stainless Steel, Gold	
Body Plating Specification	10 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	
Hex Size	5/16 inch	
Torque	3 in-lbs [0.34 Nm]	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to Trimmed Lead Test Probe Cable 6 Inch Length Using PE-SR405FL Coax PE3C8144-6](#)



SMA Male to Trimmed Lead Test Probe Cable
6 Inch Length Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet

PE3C8144-6

How to Order

Part Number Configuration:

PE3C8144

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C8144-12 = 12 inches long cable
PE3C8144-100cm = 100 cm long cable

SMA Male to Trimmed Lead Test Probe Cable 6 Inch Length Using PE-SR405FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to Trimmed Lead Test Probe Cable 6 Inch Length Using PE-SR405FL Coax PE3C8144-6](https://www.pasternack.com/sma-male-trimmed-lead-sexless-pe-sr405fl-cable-assembly-pe3c8144-6-p.aspx)


URL: <https://www.pasternack.com/sma-male-trimmed-lead-sexless-pe-sr405fl-cable-assembly-pe3c8144-6-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C8144-6 CAD Drawing

SMA Male to Trimmed Lead Test Probe Cable 6 Inch Length Using PE-SR405FL Coax

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/11/2021	S.ELLIS



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		THIRD-ANGLE PROJECTION	
TOLERANCES: X = ± .008 FRACTIONS XX = ± .02 .51 ± 1/32 XXX = ± .005 .13 ANGLES ± 1° CABLE LENGTH (L) TOLERANCES: L ≤ 12 [305] = ± .125 / -0 12 [305] < L ≤ 60 [1524] = ± .25 / -0 60 [1524] < L ≤ 120 [3048] = ± .4 [102] / -0 120 [3048] < L ≤ 300 [7620] = ± .6 [152] / -0 300 [7620] < L = ± 5% / -0		 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION ALL RIGHTS RESERVED.	
PE PASTERNAK® an INFINITE® brand		SHEET 1 OF 1	
Pasternack Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasternack.com E-mail: sales@pasternack.com		SCALE N/A	
SIZE A	CAGE CODE 53919	DRAWN BY K.DANG	ITEM NO. PE3C8144
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		REV	A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.