



Outdoor Rated 7/16 DIN Male to 7/16 DIN Male  
Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax  
Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet


**PE3C8510-48**

### Configuration

- Connector 1: 7/16 DIN Male
- Connector 2: 7/16 DIN Male Right Angle
- Cable Type: SPO-250

### Features

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- 83% Phase Velocity
- PE Jacket
- 100% Tested with PIM Test Results Marked on Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components



### Applications

- General Purpose
- Laboratory Use
- Low PIM Applications
- Outdoor Rated Applications
- Distributed Antenna Systems (DAS)
- Multi-Carrier Communication Systems
- PIM Testing

### Description

Pasternack's PE3C8510-48 7/16 DIN male to 7/16 DIN male right angle 48 inch cable using SPO-250 coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack 7/16 DIN to 7/16 DIN cable assembly has a male to male gender configuration with 50 ohm corrugated SPO-250 coax. The PE3C8510-48 7/16 DIN male to 7/16 DIN male cable assembly operates to 5.8 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The right angle 7/16 DIN interface on the SPO-250 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description             | Minimum | Typical | Maximum | Units |
|-------------------------|---------|---------|---------|-------|
| Frequency Range         | DC      |         | 5.8     | GHz   |
| VSWR                    |         |         | 1.4:1   |       |
| Velocity of Propagation |         | 83      |         | %     |
| Passive Intermodulation |         |         | -160    | dBc   |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Outdoor Rated 7/16 DIN Male to 7/16 DIN Male Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax Using Times Microwave Parts PE3C8510-48](#)



Outdoor Rated 7/16 DIN Male to 7/16 DIN Male  
Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax  
Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C8510-48**

|             |              |              |
|-------------|--------------|--------------|
| Capacitance | 24 [78.74]   | pF/ft [pF/m] |
| Inductance  | 0.054 [0.18] | uH/ft [uH/m] |

### Specifications by Frequency

| Description           | F1   | F2   | F3   | F4   | F5   | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency             | 0.25 | 0.5  | 1    | 2.5  | 5.8  | GHz   |
| Insertion Loss (Typ.) | 0.22 | 0.32 | 0.45 | 0.73 | 1.15 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1\*SQRT(FGHz) dB per connector.

### Mechanical Specifications

#### Cable Assembly

|          |                   |
|----------|-------------------|
| Length*  | 48 in [121.92 cm] |
| Diameter | 0 in [0 mm]       |

#### Cable

|                                      |                       |
|--------------------------------------|-----------------------|
| Cable Type                           | SPO-250               |
| Impedance                            | 50 Ohms               |
| Inner Conductor Type                 | Solid                 |
| Inner Conductor Material and Plating | Copper Clad Aluminum  |
| Dielectric Type                      | Foam PE               |
| Number of Shields                    | 1                     |
| Outer Conductor Material and Plating | Copper                |
| Jacket Material                      | PE, Black             |
| Jacket Diameter                      | 0.303 in [7.7 mm]     |
| One Time Minimum Bend Radius         | 1.25 in [31.75 mm]    |
| Bending Moment                       | 0.5 lbs-ft [0.68 N-m] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Outdoor Rated 7/16 DIN Male to 7/16 DIN Male Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax Using Times Microwave Parts PE3C8510-48](#)



Outdoor Rated 7/16 DIN Male to 7/16 DIN Male  
Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax  
Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C8510-48**

### Connectors

| Description                        | Connector 1      | Connector 2               |
|------------------------------------|------------------|---------------------------|
| Type                               | 7/16 DIN Male    | 7/16 DIN Male Right Angle |
| Impedance                          | 50 Ohms          | 50 Ohms                   |
| Contact Material and Plating       | Brass, Silver    | Brass, Silver             |
| Contact Plating Specification      | 196 µin          | 196 µin                   |
| Dielectric Type                    | PTFE             | PTFE                      |
| Body Material and Plating          | Brass, Tri-Metal | Brass, Nickel             |
| Body Plating Specification         | 118 µin          | 118 µin                   |
| Coupling Nut Material and Plating  | Brass, Nickel    | Brass, Nickel             |
| Coupling Nut Plating Specification | 118 µin          | 118 µin                   |

### Environmental Specifications

#### Temperature

Operating Range

-40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Outdoor Rated 7/16 DIN Male to 7/16 DIN Male Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax Using Times Microwave Parts PE3C8510-48](#)



Outdoor Rated 7/16 DIN Male to 7/16 DIN Male  
Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax  
Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C8510-48**

### How to Order

Part Number Configuration:

**PE3C8510**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C8510-12 = 12 inches long cable  
PE3C8510-100cm = 100 cm long cable

Outdoor Rated 7/16 DIN Male to 7/16 DIN Male Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax Using Times Microwave Parts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Outdoor Rated 7/16 DIN Male to 7/16 DIN Male Right Angle Low PIM Cable 48 Inch Length Using SPO-250 Coax Using Times Microwave Parts PE3C8510-48](#)


URL: <https://www.pasternack.com/7-16-din-male-7-16-din-male-spo250-cable-assembly-pe3c8510-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C8510-48 CAD Drawing

Outdoor Rated 7/16 DIN Male to 7/16 DIN Male Right Angle Low PIM Cable  
48 Inch Length Using SPO-250 Coax Using Times Microwave Parts

| REVISIONS |                 |           |            |
|-----------|-----------------|-----------|------------|
| REV.      | DESCRIPTION     | DATE      | APPROVED   |
| A         | INITIAL RELEASE | 9/21/2021 | A. GANWANI |



## NOTES:

1. CABLES 84" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 84" HAVE 2 LABELS, ONE AT EACH END 12.0" FROM THE END OF THE CONNECTOR.
2. 6" FROM CABLE END 1 PLACE FOR ALL LENGTHS OF CABLE.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

|                                                                                                                                                                                                                                                                                                                                                                          |                 |                                                                                                                       |                   |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-----------------------------------------------------------------------------------------------------------------------|-------------------|
| UNLESS OTHERWISE SPECIFIED<br>LEADING DIMENSIONS ARE INCHES<br>DIMENSIONS IN [ ] ARE MILLIMETERS                                                                                                                                                                                                                                                                         |                 | THIRD-ANGLE PROJECTION                                                                                                |                   |
| TOLERANCES:<br><br>X = ± .2 [ .008]      FRACTIONS<br>.XX = ± .02 [ .51]      ± 1/32<br>XXX = ± .005 [ .13]      ANGLES ± 1°<br><br>CABLE LENGTH (L) TOLERANCES:<br><br>L ≤ 12 [305] = +1 [25] / -0<br>12 [305] < L ≤ 60 [1524] = +2 [51] / -0<br>60 [1524] < L ≤ 120 [3048] = +4 [102] / -0<br>120 [3048] < L ≤ 300 [7620] = +6 [152] / -0<br>300 [7620] < L = +5% / -0 |                 | THE INFORMATION AND<br>DESIGN IN THIS DOCUMENT<br>IS THE PROPERTY OF<br>PASTERNAK CORPORATION<br>ALL RIGHTS RESERVED. |                   |
| PE PASTERNAK®<br>an INFINITE® brand                                                                                                                                                                                                                                                                                                                                      |                 | SHEET 1 OF 1                                                                                                          |                   |
| Pasternack Enterprises, Inc.<br>P.O. Box 16759, Irvine, CA 92623.<br>Phone: 1.949.261.1920   1.866.727.8376<br>Fax: 1.949.261.7451<br>Website: www.pasternack.com<br>E-mail: sales@pasternack.com                                                                                                                                                                        |                 | SCALE N/A                                                                                                             |                   |
| SIZE A                                                                                                                                                                                                                                                                                                                                                                   | CAGE CODE 53919 | DRAWN BY K.DANG                                                                                                       | ITEM NO. PE3C8510 |
| ALL DIMENSIONS SHOWN<br>ARE FOR REFERENCE ONLY.                                                                                                                                                                                                                                                                                                                          |                 | REV A                                                                                                                 |                   |