

Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts



RF Cable Assemblies Technical Data Sheet

PE3C8514-24


Configuration

- Connector 1: 7/16 DIN Female
- Connector 2: N Male
- Cable Type: SPO-375



Features

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- 83% Phase Velocity
- PE Jacket
- 100% Tested with PIM Test Results Marked on Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components



Applications

- General Purpose
- Laboratory Use
- Low PIM Applications
- Outdoor Rated Applications
- Distributed Antenna Systems (DAS)
- Multi-Carrier Communication Systems
- PIM Testing

Description

Pasternack's PE3C8514-24 7/16 DIN female to type N male 24 inch cable using SPO-375 coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack 7/16 DIN to type N cable assembly has a female to male gender configuration with 50 ohm corrugated SPO-375 coax. The PE3C8514-24 7/16 DIN female to type N male cable assembly operates to 6 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation	83			%
Passive Intermodulation			-160	dBc

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts PE3C8514-24](#)

Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts



RF Cable Assemblies Technical Data Sheet

PE3C8514-24

Capacitance	24 [78.74]	pF/ft [pF/m]
-------------	------------	--------------

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	4	6	GHz
Insertion Loss (Typ.)	0.21	0.29	0.46	0.58	0.73	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of $0.1 * \text{SQRT}(F\text{GHz})$ dB per connector.

Mechanical Specifications

Cable Assembly

Length*

24 in [609.6 mm]

Diameter

0 in [0 mm]

Cable

Cable Type

SPO-375

Impedance

50 Ohms

Inner Conductor Type

Solid

Inner Conductor Material and Plating

Copper Clad Aluminum

Dielectric Type

Foam PE

Number of Shields

1

Outer Conductor Material and Plating

Copper

Jacket Material

PE, Black

Jacket Diameter

0.43 in [10.92 mm]

One Time Minimum Bend Radius

1.75 in [44.45 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts PE3C8514-24](#)

Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts



RF Cable Assemblies Technical Data Sheet

PE3C8514-24

Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Female	N Male
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Phosphor Bronze, Silver	Brass, Silver
Contact Plating Specification	200 μ in	200 μ in
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Tri-Metal
Outer Conductor Plating Specification		100 μ in
Body Material and Plating	Brass, Tri-Metal	
Body Plating Specification	100 μ in	
Coupling Nut Material and Plating		Brass, Tri-Metal
Coupling Nut Plating Specification		100 μ in
Torque		9.74 in-lbs [1.1 Nm]

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts PE3C8514-24](#)

Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts



RF Cable Assemblies Technical Data Sheet

PE3C8514-24

How to Order

Part Number Configuration:

PE3C8514

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C8514-12 = 12 inches long cable
PE3C8514-100cm = 100 cm long cable

Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts PE3C8514-24](#)

URL: <https://www.pasternack.com/7-16-din-female-n-male-spo375-cable-assembly-pe3c8514-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C8514-24 CAD Drawing

Outdoor Rated 7/16 DIN Female to N Male Low PIM Cable 24 Inch Length Using SPO-375 Coax Using Times Microwave Parts

