

## N Female Bulkhead to SMA Male Right Angle Cable Using PE-SR405FLJ Coax




### PE3C9934

#### Configuration

- Connector 1: N Female Bulkhead
- Connector 2: SMA Male Right Angle
- Cable Type: PE-SR405FLJ
- Coax Flex Type: Formable

#### Features

- Max Frequency 10 GHz
- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3C9934 type N female bulkhead to SMA male right angle cable using PE-SR405FLJ coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack type N to SMA cable assembly has a female to male gender configuration with 50 ohm formable PE-SR405FLJ coax. The PE3C9934 type N female to SMA male cable assembly operates to 10 GHz. The right angle SMA interface on the PE-SR405FLJ cable allows for easier connections in tight spaces. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

| Description                   | Minimum | Typical       | Maximum | Units                 |
|-------------------------------|---------|---------------|---------|-----------------------|
| Frequency Range               | DC      |               | 10      | GHz                   |
| VSWR                          |         |               | 1.4:1   |                       |
| Velocity of Propagation       |         | 69.5          |         | %                     |
| RF Shielding                  | 100     |               |         | dB                    |
| Group Delay                   |         | 1.43 [4.69]   |         | ns/ft [ns/m]          |
| Capacitance                   |         | 29 [95.14]    |         | pF/ft [pF/m]          |
| DC Resistance Inner Conductor |         | 65.7 [215.55] |         | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor |         | 10.2 [33.46]  |         | Ohms/1000ft [Ohms/Km] |

#### Specifications by Frequency

## N Female Bulkhead to SMA Male Right Angle Cable Using PE-SR405FLJ Coax



### PE3C9934

| Part Number | Length                   | Description           | F1   | F2   | F3    | F4    | F5    | Units | Weight (lbs) |
|-------------|--------------------------|-----------------------|------|------|-------|-------|-------|-------|--------------|
|             |                          | Frequency             | 500  | 1000 | 2500  | 5000  | 10000 | MHz   |              |
| PE3C9934    | Custom Lengths Available | Insertion Loss (Typ.) | 0.15 | 0.23 | 0.346 | 0.549 | 0.812 | dB/ft |              |
|             |                          |                       | 0.5  | 0.74 | 1.14  | 1.81  | 2.67  | dB/m  |              |
| PE3C9934-6  | 6 inch                   | Insertion Loss (Typ.) | 0.38 | 0.42 | 0.48  | 0.58  | 0.71  | dB    | 0.106        |
| PE3C9934-9  | 9 inch                   | Insertion Loss (Typ.) | 0.42 | 0.47 | 0.56  | 0.72  | 0.91  | dB    | 0.11         |
| PE3C9934-12 | 12 inch                  | Insertion Loss (Typ.) | 0.45 | 0.53 | 0.65  | 0.85  | 1.12  | dB    | 0.113        |
| PE3C9934-18 | 18 inch                  | Insertion Loss (Typ.) | 0.53 | 0.64 | 0.82  | 1.13  | 1.52  | dB    | 0.121        |
| PE3C9934-24 | 24 inch                  | Insertion Loss (Typ.) | 0.6  | 0.75 | 1     | 1.4   | 1.93  | dB    | 0.128        |

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

|                             |                |
|-----------------------------|----------------|
| Loss due to Connector 1:    | 0.1 dB         |
| Loss due to Connector 2:    | 0.2 dB         |
| Base Weight:                | 0.113 pounds   |
| Additional Weight per Inch: | 0.00117 pounds |

### Mechanical Specifications

#### Cable Assembly

|                |                     |
|----------------|---------------------|
| Width/Diameter | 0.5 in [12.7 mm]    |
| Weight         | 0.113 lbs [51.26 g] |

#### Cable

|                                        |                               |
|----------------------------------------|-------------------------------|
| Cable Type                             | PE-SR405FLJ                   |
| Impedance                              | 50 Ohms                       |
| Inner Conductor Type                   | Solid                         |
| Inner Conductor Material and Plating   | Copper Clad Steel, Silver     |
| Dielectric Type                        | PTFE                          |
| Number of Shields                      | 1                             |
| Outer Conductor 1 Material and Plating | Tinned Copper Composite Braid |
| Jacket Material                        | FEP, Black                    |
| Jacket Diameter                        | 0.105 in [2.67 mm]            |
| One Time Minimum Bend Radius           | 0.5 in [12.7 mm]              |
| Repeated Minimum Bend Radius           | 0.787 in [19.99 mm]           |

## N Female Bulkhead to SMA Male Right Angle Cable Using PE-SR405FLJ Coax



### PE3C9934

#### Connectors

| Description                        | Connector 1                       | Connector 2           |
|------------------------------------|-----------------------------------|-----------------------|
| Type                               | N Female Bulkhead                 | SMA Male Right Angle  |
| Specification                      |                                   | MIL-STD-348A          |
| Impedance                          | 50 Ohms                           | 50 Ohms               |
| Configuration                      | Straight                          | Right Angle           |
| Contact Material and Plating       | Phosphor Bronze, Gold over Nickel | Brass, Gold           |
| Contact Plating Specification      |                                   | 50 µin minimum        |
| Dielectric Type                    | PTFE                              | PTFE                  |
| Body Material and Plating          | Brass, Nickel                     | Stainless Steel, Gold |
| Body Plating Specification         |                                   | 30 µin minimum        |
| Coupling Nut Material and Plating  |                                   | Brass, Nickel         |
| Coupling Nut Plating Specification |                                   | 100 µin minimum       |
| Hex Size                           |                                   | 5/16 inch             |
| Torque                             |                                   | 3 in-lbs 0.34 Nm      |

#### Environmental Specifications

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

## N Female Bulkhead to SMA Male Right Angle Cable Using PE-SR405FLJ Coax



### PE3C9934

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**PE3C9934**

**- xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches

Length

Base Number

Example: PE3C9934-12 = 12 inches long cable  
PE3C9934-100cm = 100 cm long cable


N Female Bulkhead to SMA Male Right Angle Cable Using PE-SR405FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Female Bulkhead to SMA Male Right Angle Cable Using PE-SR405FLJ Coax PE3C9934](#)

URL: <https://www.pasternack.com/n-female-bulkhead-to-sma-male-cable-using-pe-sr405flj-pe3c9934-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C9934 CAD Drawing
N Female Bulkhead to SMA Male Right Angle Cable Using PE-SR405FLJ Coax



- NOTES:
- 1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCH OR LESS, ONE LABEL APPROXIMATELY CENTERED, LONGER THAN 36 INCH, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- 2. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
- 3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVISION CONTRARY TO U.S. LAW PROHIBITED.

|                                                                                                                                                                                                                        |  |                                                                     |  |                                                        |  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------|--|--------------------------------------------------------|--|
| UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [ ] ARE IN MILLIMETERS.                                                                                                                    |  | <b>PE PASTERNAK</b><br>an INFINITE® brand                           |  | INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 |  |
| TOLERANCES:                                                                                                                                                                                                            |  | Website: <a href="http://www.Pasternack.com">www.Pasternack.com</a> |  | SCALE                                                  |  |
| X = ±.2 [5]                                                                                                                                                                                                            |  | Phone: 1.866.727.8376   1.949.261.1920                              |  | NONE                                                   |  |
| .XX = ±.02 [0.5]                                                                                                                                                                                                       |  |                                                                     |  | SHEET                                                  |  |
| .XXX = ±.005 [0.13]                                                                                                                                                                                                    |  |                                                                     |  | 1 OF 1                                                 |  |
| ANGLES ± 1°                                                                                                                                                                                                            |  |                                                                     |  |                                                        |  |
| CABLE LENGTH TOLERANCES:                                                                                                                                                                                               |  | DESCRIPTION                                                         |  |                                                        |  |
| >12 [305] ≤ 60 [1524] = ±.125 [-0]                                                                                                                                                                                     |  | N FEMALE BULKHEAD TO SMA MALE RIGHT ANGLE                           |  |                                                        |  |
| >60 [1524] ≤ 120 [3048] = ±.125 [-0]                                                                                                                                                                                   |  | CABLE USING PE-SR405FLJ COAX                                        |  |                                                        |  |
| >120 [3048] ≤ 300 [7620] = ±.5% [-0]                                                                                                                                                                                   |  |                                                                     |  |                                                        |  |
| ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS SHALL BE DETERMINED BY ITEM PN AND DESCRIPTION. UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [ ] ARE IN MILLIMETERS. COLORS MAY VARY. |  | SIZE                                                                |  | REV                                                    |  |
|                                                                                                                                                                                                                        |  | A                                                                   |  | A                                                      |  |
|                                                                                                                                                                                                                        |  | CAGE CODE                                                           |  | ITEM NO.                                               |  |
|                                                                                                                                                                                                                        |  | 53919                                                               |  | PE3C9934                                               |  |
|                                                                                                                                                                                                                        |  | DRAWN BY                                                            |  |                                                        |  |
|                                                                                                                                                                                                                        |  | AKRESOWSKI                                                          |  |                                                        |  |