



## SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141 Flex Coax, RoHS

### RF Cable Assemblies Technical Data Sheet



PE3CA1036-12

#### Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male Right Angle
- Cable Type: PE-141FLEX

#### Features

- Design operates to 27 GHz
- Shielding effectivity > 90dB
- One time minimum bend radius: 0.4 inch
- Typical SMA VSWR 1.22:1 to 27 GHz



#### Applications

- High Performance RF equipment interconnect
- Flexible in the cabinet or in the rack requirements
- Inside the box RF routing
- General purpose lighter duty lab use

#### Description

These new high performance flexible cables are made using our PE-141 FLEX coax and our new low profile connectors. The high performance flexible design is well suited for connecting RF devices in rack-mount systems, inside RF equipment and for general lab hookup where a more expensive test cable are not required. These cables are similar to the PE30X series which have retractable coupling nuts and thick wall SMA connectors. The heavier duty PE35X test series cables have similar performance, but include a heavy duty strain relief mechanism and extra booting material as well as a thick wall SMA connector to increase the ruggedness of the PE35X cables for use in more demanding test environments.

PE-141FLEX is a flexible cable alternate to Semi Rigid coax and has a solid PTFE resulting in a 69.5% phase velocity. The smooth wall formed by the Braid over Spiral Ribbon design allows for a flexible cable that has similar performance to a solid wall 141 Semi Rigid (RG402) cable.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		27	GHz
VSWR			1.4:1	
Return Loss	15.56			dB
Velocity of Propagation		69.5		%
RF Shielding	90			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141FLEX Coax, RoHS PE3CA1036-12](#)



## SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141 Flex Coax, RoHS

### RF Cable Assemblies Technical Data Sheet

**PE3CA1036-12**

Operating Voltage (AC)	250	Vrms
------------------------	-----	------

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	3	6	12	18	27	GHz
Insertion Loss (Max.)	0.38	0.55	0.85	1.03	1.3	dB
VSWR (Max.)	1.08:1	1.12:1	1.2:1	1.3:1	1.4:1	
Power Handling (Max.)	215	150	105	88	75	Watts

#### Mechanical Specifications

##### Cable Assembly

Length

12 in [304.8 mm]

Weight

0.05 lbs [22.68 g]

##### Cable

Cable Type

PE-141FLEX

Impedance

50 Ohms

Inner Conductor Type

Solid

Inner Conductor Material and Plating

Copper Clad Steel, Silver

Dielectric Type

PTFE

Number of Shields

2

Shield Layer 1

Silver Plated Copper Tape

Shield Layer 2

Silver Plated Copper Braid

Outer Conductor 1 Material and Plating

Silver Plated Copper Tape

Outer Conductor 2 Material and Plating

Silver Plated Copper Braid

Jacket Material

FEP

Jacket Diameter

0.163 in [4.14 mm]

One Time Minimum Bend Radius

0.39 in [9.91 mm]

Repeated Minimum Bend Radius

1.57 in [39.88 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141FLEX Coax, RoHS PE3CA1036-12](#)



## SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141 Flex Coax, RoHS

### RF Cable Assemblies Technical Data Sheet

PE3CA1036-12

#### Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male Right Angle
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	500
Contact Material and Plating	Brass, Gold	Brass, Gold
Dielectric Type	PTFE	PTFE
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Hex Size	5/16 Inch	5/16 Inch
Body Material and Plating	Stainless Steel, Gold	Stainless Steel, Gold

#### Environmental Specifications

##### Temperature

Operating Range

-40 to +150 deg C

#### Compliance Certifications (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

RoHS Compliant

Yes

REACH Compliant

12/17/2015

#### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141FLEX Coax, RoHS PE3CA1036-12](#)





SMA Male to SMA Male Right Angle Cable 12 Inch  
Length Using PE-141 Flex Coax, RoHS

## RF Cable Assemblies Technical Data Sheet

PE3CA1036-12

### Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141FLEX Coax, RoHS PE3CA1036-12](#)



## SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141 Flex Coax, RoHS

### RF Cable Assemblies Technical Data Sheet

PE3CA1036-12

#### How to Order

Part Number Configuration:

PE3CA1036

- xx

uu

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3CA1036-12 = 12 inches long cable  
PE3CA1036-100cm = 100 cm long cable

SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141 Flex Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141FLEX Coax, RoHS PE3CA1036-12](#)

URL: <http://www.pasternack.com/sma-male-sma-male-pe-141flex-cable-assembly-pe3ca1036-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3CA1036-12 CAD Drawing

SMA Male to SMA Male Right Angle Cable 12 Inch Length Using PE-141 Flex Coax, RoHS



Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451

Website: [www.pasternack.com](http://www.pasternack.com) | E-Mail: [sales@pasternack.com](mailto:sales@pasternack.com)

#### NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. LENGTH TOLERANCE IS  $\pm 1.5\%$  OR 3/8", WHICHEVER IS GREATER.

#### DWG TITLE

**PE3CA1036**

**FSCM NO. 53919**

CAD FILE

032715

SCALE N/A

SIZE A

150