



78 Ohm 3-Slot TRB Solder/Clamp Plug with
Blunt Cut for PE-30-02001 24" Cable

RF Cable Assemblies Technical Data Sheet

PE3CA2219-24

Configuration

- Connector 1: TRB Plug
- Connector 2: Blunt Cut Genderless
- Cable Type: 30-02001
- Coax Flex Type: Flexible

• Features

- Max Frequency 400 MHz
- PVC Jacket
- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

Applications

- General Purpose
- Laboratory Use
- MIL-STD-1553
- Data

Description

Pasternack's PE3CA2219-24 78 ohm TRB plug to Blunt cut genderless 24 inch cable using 78 ohm PE-30-02001 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to Blunt Cut cable assembly has a plug to genderless gender configuration with 78 ohm flexible 30-02001 twinax. The PE3CA2219-24 TRB plug to Blunt cut genderless cable assembly operates to 400 MHz. The PE3CA2219 cable assembly consists of a 3-slot solder/clamp TRB plug to Blunt Cut on PE-30-02001, that is a standard lab-rated PVC cable for MIL-STD-1553 applications. It features a larger diameter cable (0.242" O.D.)

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Twinax \(.242 O.D.\) 24" Cable PE3CA2219-24](#)



78 Ohm 3-Slot TRB Solder/Clamp Plug with
Blunt Cut for PE-30-02001 24" Cable

RF Cable Assemblies Technical Data Sheet

PE3CA2219-24

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		400	MHz
Capacitance		19.7 [64.63]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	400	MHz

Insertion Loss (Typ.)

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	24 in [609.6 mm]
Weight	0.21208 lbs [96.2 g]

Cable

Cable Type	30-02001
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	PVC, Blue

One Time Minimum Bend Radius	2.42 in [61.47 mm]
------------------------------	--------------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Twinax \(.242 O.D.\) 24" Cable PE3CA2219-24](#)



78 Ohm 3-Slot TRB Solder/Clamp Plug with
Blunt Cut for PE-30-02001 24" Cable

RF Cable Assemblies Technical Data Sheet

PE3CA2219-24

Connectors

Description	Connector 1	Connector 2
Type	TRB Plug	Blunt Cut Genderless
Impedance	78 Ohms	
Contact Material and Plating	Bronze, Gold 30 micro inches	
Contact Plating Specification	ASTM-B-488	
Dielectric Type	Teflon	
Outer Conductor Material and Plating	Phosphor Bronze, Gold	
Outer Conductor Plating Specification	30 micro inches	
Body Material and Plating	Brass, Nickel	
Body Plating Specification	ASTM-B-733	

Environmental Specifications

Temperature

Operating Range

-20 to +75 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Twinax \(.242 O.D.\) 24" Cable PE3CA2219-24](#)



78 Ohm 3-Slot TRB Solder/Clamp Plug with
Blunt Cut for PE-30-02001 24" Cable

RF Cable Assemblies Technical Data Sheet

PE3CA2219-24

How to Order

Part Number Configuration:

PE3CA2219

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3CA2219-12 = 12 inches long cable
PE3CA2219-100cm = 100 cm long cable

78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 24" Cable from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Twinax \(.242 O.D.\) 24" Cable PE3CA2219-24](#)

URL: <https://www.pasternack.com/trb-plug-to-blunt-cut-genderless-1553-cable-24-inch-length-using-pe-30-02001-pe3ca2219-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 24" Cable

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/28/2016	DMAY	EKIM



ITEM NUMBER	LENGTH	
	FEET	METERS
PE3CA2219-12	1.0	.31
PE3CA2219-24	2.0	.61
PE3CA2219-36	3.0	.92
PE3CA2219-48	4.0	1.22
PE3CA2219-60	5.0	1.52

NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR PART WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		PASTERNAK® an INFINITO brand		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES: .X ± .2 [5] FRACTIONS .XX ± .02 [.5] ± 1/32 .XXX ± .005 [.13] ANGLES ± °		CABLE LENGTH TOLERANCES: ≤ 12 [305] ± .1 [25] / -0 > 12 [305] ≤ 60 [1524] ± .2 [51] / -0 > 60 [1524] ≤ 120 [3048] ± .4 [102] / -0 > 120 [3048] ≤ 300 [7620] ± .6 [152] / -0 > 300 [7620] > ± .8% / -0		DESCRIPTION CA TRB PLUG-BLUNT END LAB	
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		SCALE NONE		SHEET 1 OF 1	
SIZE A	CAGE CODE 53919	DRAWN BY DMAY	ITEM NO.		REV A
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.					