



TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable 24 Inch Length Using 78 Ohm PE-30-02003 Coax

RF Cable Assemblies Technical Data Sheet

PE3CA2375-24

Configuration

- Connector 1: TRS Subminiature Plug
- Connector 2: TRB Jack
- Cable Type: PE-30-02003
- Coax Flex Type: Flexible

Features

- Max Frequency 500 MHz
- PVC Jacket
- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

Applications

- General Purpose
- Laboratory Use
- MIL-STD-1553
- Data

Description

Pasternack's PE3CA2375-24 78 ohm TRS Subminiature plug to 78 ohm TRB jack 24 inch cable using 78 ohm PE-30-02003 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRS Subminiature to TRB cable assembly has a plug to jack gender configuration with 78 ohm flexible PE-30-02003 twinax. The PE3CA2375-24 TRS Subminiature plug to TRB jack cable assembly operates to 500 MHz. The PE3CA2375 cable assembly consists of a 3-slot solder/clamp TRS Subminiature jack to a 3-slot solder/clamp TRB plug on PE-30-02003, that is a standard lab-rated PVC cable for MIL-STD-1553 applications, with an O.D. 0.150

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable 24 Inch Length Using 78 Ohm PE-30-02003 Coax PE3CA2375-24](#)



TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable
24 Inch Length Using 78 Ohm PE-30-02003 Coax

RF Cable Assemblies Technical Data Sheet

PE3CA2375-24

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Capacitance		20.3 [66.6]		pF/ft [pF/m]
Operating Voltage (AC)			300	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	500	MHz
Insertion Loss (Typ.)	0.306	0.438	0.536	0.674	0.95	dB

Mechanical Specifications

Cable Assembly

Length*	24 in [609.6 mm]
Weight	0.102 lbs [46.27 g]

Cable

Cable Type	PE-30-02003
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	PVC, Blue

One Time Minimum Bend Radius	1.5 in [38.1 mm]
------------------------------	------------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable 24 Inch Length Using 78 Ohm PE-30-02003 Coax PE3CA2375-24](#)



TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable
24 Inch Length Using 78 Ohm PE-30-02003 Coax

RF Cable Assemblies Technical Data Sheet

PE3CA2375-24

Connectors

Description	Connector 1	Connector 2
Type	TRS Subminiature Plug	TRB Jack
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

Environmental Specifications

Temperature

Operating Range

-20 to +75 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable 24 Inch Length Using 78 Ohm PE-30-02003 Coax PE3CA2375-24](#)



TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable
24 Inch Length Using 78 Ohm PE-30-02003 Coax

RF Cable Assemblies Technical Data Sheet

PE3CA2375-24

How to Order

Part Number Configuration:

PE3CA2375

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3CA2375-12 = 12 inches long cable
PE3CA2375-100cm = 100 cm long cable

TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable 24 Inch Length Using 78 Ohm PE-30-02003 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable 24 Inch Length Using 78 Ohm PE-30-02003 Coax PE3CA2375-24](https://www.pasternack.com/trs-subminiature-plug-to-trb-jack-1553-cable-24-inch-length-using-pe-30-02003-coax-pe3ca2375-24)

URL: <https://www.pasternack.com/trs-subminiature-plug-to-trb-jack-1553-cable-24-inch-length-using-pe-30-02003-pe3ca2375-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3CA2375-24 CAD Drawing

TRS 3-Slot Submini Plug to TRB 3-Lug Jack 1553 Cable
24 Inch Length Using 78 Ohm PE-30-02003 Coax



ITEM NUMBER	LENGTH	
	FEET	METERS
PE3CA2375-12	1.0	.31
PE3CA2375-24	2.0	.61
PE3CA2375-36	3.0	.92
PE3CA2375-48	4.0	1.22
PE3CA2375-60	5.0	1.52

NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS; ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE: NONE SHEET: 1 OF 1	
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		DESCRIPTION: TWINAX CA TRB JACK-TRS PLUG LAB	
SIZE: A	CAGE CODE: 53919	DRAWN BY: DMAY	ITEM NO.: PE3CA2375
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES: .X = ±.2 [.5] FRACTIONS ±.1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13] CABLE LENGTH TOLERANCES: ≤12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.			