

MIL-DTL-17 SMA Male to SMA Male Right Angle Cable 100 cm Length Using M17/113-RG316 Coax



RF Cable Assemblies Technical Data Sheet

PE3M0091-100CM

Configuration

- Connector 1: M39012/55-3026 (SMA Male)
- Connector 2: M39012/56-3107 (SMA Male Right Angle)
- Cable: M17/113-RG316

Features

- Max Frequency 3 GHz
- 69.5% Phase Velocity
- FEP Jacket
- Lot Traceability
- J-STD-Soldering
- Qualified (QPL) cable and connectors
- RF Test Plots
- Test Report
- In stock and ready to ship

Applications

| | | |
|-------------------|---------------------------|----------|
| • General Purpose | • MIL-DTL-17 Requirements | • SATCOM |
| • Laboratory Use | • Avionics | • ECM |
| • Hi-Rel | • IFF | |

Description

Pasternack's MIL-DTL-17 cable assemblies are part of our full line of reliable RF components available for same-day shipping. These commercial-off-the-shelf (COTS), military grade cable assemblies are designed and processed with high reliability in mind. MIL-PRF-39012 connectors and MIL-C-17 coaxial cable are assembled using J-STD soldering processes and WHMA-A-620 workmanship criteria. The combination of materials, processing and acceptance testing work together to create a dependable cable assembly for applications where performance over time is important or the cost of failure is high. Each finished MIL-DTL-17 cable assembly is traceable to its component lots and a test report is available for every lot produced.

Our MIL-DTL-17 cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide reliable mil-spec connections or fielding dependable RF cable assemblies, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Referenced Specifications

| | |
|----------------|---|
| IPC/WHMA-A-620 | Requirements and Acceptance for Cable and Wire Harness Assemblies |
| MIL-DTL-17 | Cables, Radio Frequency, Flexible and Semirigid, General Specification for |
| MIL-STD-348 | Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF... |
| MIL-PRF-39012 | Connectors, Coaxial, Radio Frequency, General Specification for |
| IPC J-STD-001 | Requirements for Soldered Electrical and Electronic Assemblies |
| IPC J-STD-006 | Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for Electronic Soldering Applications |
| SAE AS5942 | Marking of Electrical Insulating Materials |
| SAE AS23053 | Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to SMA Male Right Angle Cable 100 cm Length Using M17/113-RG316 Coax PE3M0091-100CM](#)

**MIL-DTL-17 SMA Male to SMA Male Right Angle Cable
100 cm Length Using M17/113-RG316 Coax**

RF Cable Assemblies Technical Data Sheet
PE3M0091-100CM

SAE AS22520

Crimping Tools, Wire Termination, General Specification For

Material Specifications

| Component | Specification |
|---------------|---|
| Cable | M17/113-RG316 in accordance with MIL-DTL-17 |
| Connector 1 | M39012/55-3026 in accordance with MIL-PRF-39012 |
| Connector 2 | M39012/56-3107 in accordance with MIL-PRF-39012 |
| Heat Shrink 1 | M23053/5-104-0 in accordance with SAE AS23053 |
| Heat Shrink 2 | M23053/5-105-0 in accordance with SAE AS23053 |
| Solder | SN63 in accordance with J-STD-006 |

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|--------------------------------------|---------|-------------|---------|-----------------|
| Frequency Range | DC | | 3 | GHz |
| VSWR | | | 1.6:1 | |
| Velocity of Propagation | | 69.5 | | % |
| Capacitance | | 32 [104.99] | | pF/ft [pF/m] |
| DC Resistance Inner Conductor | | 0.84 [2.76] | | Ω/1000ft [Ω/Km] |
| Dielectric Withstanding Voltage (AC) | | | 750 | Vrms |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency | 0.05 | 0.1 | 0.4 | 1 | 3 | GHz |
| Insertion Loss (Max.) | 0.55 | 0.67 | 0.99 | 1.55 | 2.21 | |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

Mechanical Specifications
Cable Assembly

| Description | Minimum | Typical | Maximum | Units |
|-------------|---------------|------------------|---------------|---------|
| Length* | 39.3701 [100] | 40.3701 [102.54] | 39.3701 [100] | in [cm] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to SMA Male Right Angle Cable 100 cm Length Using M17/113-RG316 Coax PE3M0091-100CM](#)

**MIL-DTL-17 SMA Male to SMA Male Right Angle Cable
100 cm Length Using M17/113-RG316 Coax**

RF Cable Assemblies Technical Data Sheet
PE3M0091-100CM

| | | | | |
|----------------------|-------|---------------|--------------|---------|
| Cable Outer Diameter | 0.094 | 0.098 | 0.102 | in |
| Weight | | 0.063 [28.58] | 0.09 [40.82] | lbs [g] |

Cable Characteristics

| Description | Specification |
|--------------------------------------|---------------------------|
| Cable Type | M17/113-RG316 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Stranded |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Shield Layer 1 | Silver Clad Copper |
| Outer Conductor Diameter | 0.081 in [2.06 mm] |
| Jacket Material | FEP |

Connector Characteristics

| Description | Connector 1 | Connector 2 |
|------------------------------------|-------------------|----------------------|
| Type | SMA Male | SMA Male Right Angle |
| Specification | MIL-PRF-39012 | MIL-PRF-39012 |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material and Plating | Brass, Gold | Brass, Gold |
| Contact Plating Specification | ASTM B488 | ASTM B488 |
| Dielectric Type | Teflon | Teflon |
| Body Material and Plating | Steel, Passivated | Steel, Gold |
| Body Plating Specification | QQ-P-35 | ASTM B488 |
| Coupling Nut Material and Plating | Steel, Passivated | Steel, Passivated |
| Coupling Nut Plating Specification | QQ-P-35 | AMS-QQ-P-35 |
| Seal Gasket Material | Silicone Rubber | Silicone Rubber |
| Contact Gage Specification | 0.000 in min | 0.000 in min |
| Insulator Gage Specification | 0.000 in min | 0.000 in min |

Mechanical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to SMA Male Right Angle Cable 100 cm Length Using M17/113-RG316 Coax PE3M0091-100CM](#)

**MIL-DTL-17 SMA Male to SMA Male Right Angle Cable
100 cm Length Using M17/113-RG316 Coax**

RF Cable Assemblies Technical Data Sheet
PE3M0091-100CM
Environmental Specifications

| Description | Specification |
|-----------------------------|-------------------|
| Temperature Operating Range | -55 to +165 deg C |

Compliance Certifications (see product page for current document)

Process Specifications

| Process | Specification |
|-------------|---|
| Soldering | in accordance with J-STD-001, class 3 |
| Crimping | dies in accordance with SAE AS22520 |
| Marking | shall meet the adherence requirements of SAE AS5942 |
| Workmanship | shall be in accordance with IPC/WHMA-A-620, class 3 |

Tests and Inspections

| Description | Sampling |
|---|--------------|
| Connector Gaging (pin and insulator position) | 100% |
| Insertion Loss | 100% |
| VSWR | 100% |
| Dielectric Withstanding Voltage (DWV) | 100% |
| Visual - workmanship, configuration and marking | 100% |
| Length | C=0, 1.5 AQL |
| Mass | C=0, 1.5 AQL |

Plotted and Other Data
Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to SMA Male Right Angle Cable 100 cm Length Using M17/113-RG316 Coax PE3M0091-100CM](#)

**MIL-DTL-17 SMA Male to SMA Male Right Angle Cable
100 cm Length Using M17/113-RG316 Coax**

RF Cable Assemblies Technical Data Sheet
PE3M0091-100CM
How to Order

Part Number Configuration:

PE3M0091
- xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3M0091-12 = 12 inches long cable
PE3M0091-100cm = 100 cm long cable

Cable Assembly Length Tolerances:

| Imperial English | | Metric | |
|---------------------|-----------------|---------------------|------------------|
| "L" ≤ 1 ft | +0.5 in / -0 in | "L" ≤ 0.3 m | +12.5 mm / -0 mm |
| 1 ft < "L" ≤ 5 ft | +1 in / -0 in | 0.3 m < "L" ≤ 1.5 m | +25 mm / -0 mm |
| 5 ft < "L" ≤ 10 ft | +2 in / -0 in | 1.5 m < "L" ≤ 3 m | +50 mm / -0 mm |
| 10 ft < "L" ≤ 25 ft | +3 in / -0 in | 3 m < "L" ≤ 7.5 m | +75 mm / -0 mm |
| 25 ft < "L" | +2%"L" / -0%"L" | 7.5 m < "L" | +2%"L" / -0%"L" |

* Cable Length = "L"


MIL-DTL-17 SMA Male to SMA Male Right Angle Cable 100 cm Length Using M17/113-RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to SMA Male Right Angle Cable 100 cm Length Using M17/113-RG316 Coax PE3M0091-100CM](#)

URL: <https://www.pasternack.com/sma-male-sma-male-m17-113-rg316-cable-assembly-pe3m0091-100cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3M0091-100CM CAD Drawing
MIL-DTL-17 SMA Male to SMA Male Right Angle Cable
100 cm Length Using M17/113-RG316 Coax



| STANDARD TOLERANCES | |
|---------------------|--------|
| X | ±0.2 |
| .XX | ±0.01 |
| .XXX | ±0.005 |

*STANDARD TOLERANCES APPLY
ONLY TO DIMENSIONS IN INCHES

NOTES:
1. BLACK HEAT SHRINK WITH WHITE
MARKINGS 3 PLACES.

PE PASTERACK[®]
THE ENGINEER'S RF SOURCE

P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451
E-Mail: sales@pasternack.com

Website: www.pasternack.com | CAGE CODE: 53919 | CAD FILE: 09/10/18 | SCALE: N/A | SIZE: A | CN2379

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE3M0091

CAGE CODE
53919