


## BMB Size 8 D38999 Contact Pin to SMA Female Cable Using PE-141FL-NM Coax with HeatShrink, LF Solder



### PE3M0314

#### Configuration

- Connector 1: Push-on BMB Pin
- Connector 2: SMA Female
- Cable Type: PE-141FL-NM
- Coax Flex Type: Formable



#### Features

- Max Frequency: 18 GHz
- Can be installed in all D38999 size 8 inserts
- Lot traceability
- High speed RF cable assembly

#### Applications

- Military and Aerospace
- Avionics
- Industrial Automation

#### Description

The PE3M0314 from Pasternack is a D38999 contact cable assembly that is built with a size 8 BMB pin contact on one end and a SMA female connector on the other. Pasternack MIL-DTL-38999 (also known as D38999 or 38999) coaxial cable assembly products are used in applications requiring high quality such as laboratory RF test and measurement, rugged and designed for defense/military, production environments, general use, etc. This BMB to SMA cable assembly is a part of one of the largest selections of same-day ship coaxial cables for RF, microwave, and millimeter wave interconnect solutions. This high frequency D38999 cable assembly operates at a maximum frequency of 18 GHz.

The RF cable has a copper jacket. This PE3M0314 radio frequency cable assembly can withstand temperatures ranging from -65 to 165 degrees C. Our BMB pin to SMA female cable has a maximum VSWR of 1.4:1. This RF cable assembly with a 0.5-inch diameter has silver plated copper as the cable's inner conducting material and PTFE dielectric type.

This BMB pin to SMA female cable assembly is built with PE-141FL-NM, which is a formable coax type. The Pasternack PE3M0314 formable cable assembly has a 50 Ohm impedance. Additional dimensions, specifications, and CAD drawings for this BMB to SMA RF cable are available on our downloadable PDF datasheet.

BMB pin to SMA female cable assembly is just one of more than one million in-stock RF products available. Pasternack is where to buy high quality custom RF cable assembly products for rugged and MIL-STD designed military/defense, aerospace, outdoor and harsh environment, microwave and millimeter wave radio transmitter receiver, component inter-connection and more for RF test & measurement labs, telecom, phase stable, phase and delay matching, and other radio frequency applications can be manufactured. Variations of BMB and SMA cable assemblies can also be built and will ship on the same day as well, search this website or contact us for assistance. For further information on similar products, our expert technical support and trained sales team can get you the ideal BMB to SMA RF cable assembly as per your requirements.

**BMB Size 8 D38999 Contact Pin to SMA Female Cable  
Using PE-141FL-NM Coax with HeatShrink, LF Solder**



**PE3M0314**

**Referenced Specifications**

IPC J-STD-001	Requirements for Soldered Electrical and Electronic Assemblies
IPC J-STD-006	Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for Electronic Soldering Applications
IPC/WHMA-A-620	Requirements and Acceptance for Cable and Wire Harness Assemblies
MIL-DTL-17	Cables, Radio Frequency, Flexible and Semirigid, General Specification for
MIL-PRF-39012	Connectors, Coaxial, Radio Frequency, General Specification for
MIL-STD-348	Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF-55339, MIL-DTL-83517
SAE AS22520	Crimping Tools, Wire Termination, General Specification For
SAE AS23053	Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For
SAE AS5942	Marking of Electrical Insulating Materials
IPC J-STD-001	Requirements for Soldered Electrical and Electronic Assemblies

**Material Specifications**

Component	Specification
Cable	PE-141FL-NM in accordance with PE-141FL-NM datasheet
Connector 1	in accordance with MIL-DTL-38999
Heat Shrink 1	M23053/5-106-0 in accordance with SAE AS23053
Heat Shrink 2	M23053/5-106-0 in accordance with SAE AS23053
Solder	SAC305 in accordance with J-STD-006

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	
Velocity of Propagation		70		%
RF Shielding	90			dB

**Specifications by Frequency**

BMB Size 8 D38999 Contact Pin to SMA Female Cable  
Using PE-141FL-NM Coax with HeatShrink, LF Solder



**PE3M0314**

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency		1000	2000	4500	9000	
PE3M0314	Custom Lengths Available	Insertion Loss (Typ.)	0.16	0.22	0.36	0.55	0.852	dB/ft	
			0.54	0.72	1.2	1.82	2.8	dB/m	
PE3M0314-6	6 inch	Insertion Loss (Typ.)	0.29	0.31	0.39	0.48	0.63	dB	0.68
PE3M0314-12	12 inch	Insertion Loss (Typ.)	0.37	0.42	0.57	0.76	1.06	dB	1.34
PE3M0314-24	24 inch	Insertion Loss (Typ.)	0.53	0.64	0.93	1.31	1.91	dB	2.66
PE3M0314-36	36 inch	Insertion Loss (Typ.)	0.69	0.86	1.29	1.86	2.76	dB	3.98
PE3M0314-48	48 inch	Insertion Loss (Typ.)	0.85	1.08	1.66	2.42	3.61	dB	5.3
PE3M0314-60	60 inch	Insertion Loss (Typ.)	1.01	1.3	2.02	2.97	4.46	dB	6.62

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	1.34 pounds
Additional Weight per Foot:	1.32 pounds

Electrical Specification Notes:  
Values at 25°C, sea level.

**Mechanical Specifications**

**Cable Assembly**

Description	Minimum	Typical	Maximum	Units
Length*			0 [0]	in [mm]
Weight		1.34 [607.81]		lbs [g]
Repeated Minimum Bend Radius	0.375			in

**Cable Characteristics**

Description	Specification
Cable Type	PE-141FL-NM
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Silver Plated Copper
Dielectric Type	PTFE
Outer Conductor 1 Material and Plating	Copper-Tin Composite
Jacket Material	Copper

**Connector Characteristics**

Description	Connector 1	Connector 2
Type	BMB Pin	SMA Female
Specification	MIL-DTL-38999	

BMB Size 8 D38999 Contact Pin to SMA Female Cable  
Using PE-141FL-NM Coax with HeatShrink, LF Solder



**PE3M0314**

**Connector Characteristics**

Description	Connector 1	Connector 2
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Connection Method	Push-on	
Contact Size	8	
Mating Cycles	1,000	
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Beryllium Copper, Gold	
Body Material and Plating	Stainless Steel, Passivated	Stainless Steel, Gold

Mechanical Specification Notes:

**Environmental Specifications**

Description	Specification
Temperature Operating Range	-65 to +165 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:  
Values at 25°C, sea level.

**BMB Size 8 D38999 Contact Pin to SMA Female Cable  
Using PE-141FL-NM Coax with HeatShrink, LF Solder**



**PE3M0314**

**How to Order**

Part Number Configuration:

**PE3M0314 - xx uu**



Example: PE3M0314-12 = 12 inches long cable  
PE3M0314-100cm = 100 cm long cable

Cable Assembly Length Tolerances:

Imperial English		Metric	
"L" ≤ 1 ft	+0.5 in / -0 in	"L" ≤ 0.3 m	+12.5 mm / -0 mm
1 ft < "L" ≤ 5 ft	+1 in / -0 in	0.3 m < "L" ≤ 1.5 m	+25 mm / -0 mm
5 ft < "L" ≤ 10 ft	+2 in / -0 in	1.5 m < "L" ≤ 3 m	+50 mm / -0 mm
10 ft < "L" ≤ 25 ft	+3 in / -0 in	3 m < "L" ≤ 7.5 m	+75 mm / -0 mm
25 ft < "L"	+2%"L" / -0%"L"	7.5 m < "L"	+2%"L" / -0%"L"

\* Cable Length = "L"

BMB Size 8 D38999 Contact Pin to SMA Female Cable Using PE-141FL-NM Coax with HeatShrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BMB Size 8 D38999 Contact Pin to SMA Female Cable Using PE-141FL-NM Coax with HeatShrink, LF Solder PE3M0314](https://www.pasternack.com/bmb-size-8-d38999-contact-pin-to-sma-female-cable-using-pe-141fl-nm-coax-with-heatshrink-lf-solder-pe3m0314-p.aspx)

URL: <https://www.pasternack.com/bmb-size-8-d38999-contact-pin-to-sma-female-cable-using-pe-141fl-nm-coax-with-heatshrink-lf-solder-pe3m0314-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3M0314 CAD Drawing

BMB Size 8 D38999 Contact Pin to SMA Female Cable Using PE-141FL-NM Coax with HeatShrink, LF Solder



**NOTES:**

1. BLACK HEATSHRINK WITH WHITE MARKINGS 3 PLACES.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SERVICE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-D4 Add2

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [ ] ARE MILLIMETERS.

**TOLERANCES:**  
 .X = ±.2 [5]  
 .XX = ±.02 [0.5]  
 .XXX = ±.005 [0.13]

**FRACTIONS**  
 ± 1/32

**ANGLES ± 1°**

**CABLE LENGTH TOLERANCES:**  
 <math>+12 [305] \leq 60 [1524] \leq +0.5 [13] / -0</math>  
 <math>+60 [1524] \leq 120 [3048] \leq +2.5 [63] / -0</math>  
 <math>+300 [7620] \leq +2.5 [63] / -0</math>

ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS OF CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.



an INFINITE brand

Website: [www.Pasternack.com](http://www.Pasternack.com)  
 Phone: 1.866.727.8376 | 1.949.261.1920

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE NONE

SHEET 1 OF 1

DESCRIPTION		REV	
BMB #8 CONTACT PIN TO SMA FEMALE CABLE USING PE-141FL-NM COAX WITH HEATSHRINK, LF SOLDER		A	
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	53919	HBAKKE	PE3M0314