


SMPM Size 12 D38999 Contact Pin to SMPM  
Size 12 D38999 Contact Socket Cable Using PE-  
SR047FL Coax with Heat Shrink, LF Solder



**PE3M0441**

**Configuration**

- Connector 1: Push-on Mini SMP Pin
- Connector 2: Push-on Mini SMP Socket
- Cable Type: PE-SR047FL
- Coax Flex Type: Formable



**Features**

- Max Frequency: 20 GHz
- Can be installed in all D38999 size 12 inserts
- Lot traceability
- High speed RF cable assembly

**Applications**

- Military and Aerospace
- Avionics
- Industrial Automation

**Description**

The PE3M0441 from Pasternack is a D38999 contact cable assembly that is built with a size 12 mini SMP pin contact connection on one end and a mini SMP socket connector on the other. Pasternack MIL-DTL-38999 (also known as D38999 or 38999) coaxial cable assembly products are used in applications requiring high quality such as laboratory RF test and measurement, rugged and designed for defense/military, production environments, general use, etc. This mini SMP to mini SMP cable assembly is a part of one of the largest selections of same-day ship coaxial cables for RF, microwave, and millimeter wave interconnect solutions. This high frequency D38999 cable assembly operates at a maximum frequency of 20 GHz.

This radio frequency cable assembly can withstand temperatures ranging from -55 to 100 degrees C. Our mini SMP pin to mini SMP socket cable has a maximum VSWR of 1.4:1. This RF cable assembly with a 0.5-inch diameter has copper clad steel as the cable's inner conducting material and PTFE dielectric type.

Mini SMP pin to mini SMP socket cable assembly is built with PE-SR047FL, which is a formable coax type. The Pasternack PE3M0441 formable cable assembly has a 50 Ohm impedance and is single shielded. Additional dimensions, specifications, and CAD drawings for this mini SMP to mini SMP RF cable are available on our downloadable PDF datasheet.

Mini SMP pin to mini SMP socket cable assembly is just one of more than one million in-stock RF products available. Pasternack is where to buy high quality custom RF cable assembly products for rugged and MIL-STD designed military/defense, aerospace, outdoor and harsh environment, microwave and millimeter wave radio transmitter receiver, component inter-connection and more for RF test & measurement labs, telecom, phase stable, phase and delay matching, and other radio frequency applications can be manufactured. Variations of mini SMP cable assemblies can also be built and will ship on the same day as well, search this website or contact us for assistance. For further information on similar products, our expert technical support and trained sales team can get you the ideal mini SMP to mini SMP RF cable assembly as per your requirements.

SMPM Size 12 D38999 Contact Pin to SMPM  
Size 12 D38999 Contact Socket Cable Using PE-  
SR047FL Coax with Heat Shrink, LF Solder



**PE3M0441**

**Referenced Specifications**

IPC J-STD-001	Requirements for Soldered Electrical and Electronic Assemblies
IPC J-STD-006	Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for Electronic Soldering Applications
IPC/WHMA-A-620	Requirements and Acceptance for Cable and Wire Harness Assemblies
MIL-DTL-17	Cables, Radio Frequency, Flexible and Semirigid, General Specification for
MIL-PRF-39012	Connectors, Coaxial, Radio Frequency, General Specification for
MIL-STD-348	Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF-55339, MIL-DTL-83517
SAE AS22520	Crimping Tools, Wire Termination, General Specification For
SAE AS23053	Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For
SAE AS5942	Marking of Electrical Insulating Materials
IPC J-STD-001	Requirements for Soldered Electrical and Electronic Assemblies

**Material Specifications**

Component	Specification
Cable	PE-SR047FL in accordance with PE-SR047FL datasheet
Connector 1	in accordance with MIL-DTL-38999
Connector 2	in accordance with MIL-DTL-38999
Heat Shrink 1	M23053/5-103-0 in accordance with SAE AS23053
Heat Shrink 2	M23053/5-103-0 in accordance with SAE AS23053
Solder	SAC305 in accordance with J-STD-006

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		20	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
Capacitance		32 [104.99]		pF/ft [pF/m]
DC Resistance Inner Conductor		207 [679.13]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		8 [26.25]		[Ω/Km]

**Specifications by Frequency**

SMPM Size 12 D38999 Contact Pin to SMPM  
Size 12 D38999 Contact Socket Cable Using PE-  
SR047FL Coax with Heat Shrink, LF Solder



**PE3M0441**

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency		1000	2000	4500	9000	
PE3M0441	Custom Lengths Available	Insertion Loss (Typ.)	0.36	0.51	0.81	1.2	1.92	dB/ft	
			1.19	1.66	2.65	3.93	6.3	dB/m	
PE3M0441-6	6 inch	Insertion Loss (Typ.)	0.38	0.46	0.61	0.8	1.16	dB	0.0215
PE3M0441-12	12 inch	Insertion Loss (Typ.)	0.56	0.71	1.01	1.4	2.12	dB	0.023
PE3M0441-24	24 inch	Insertion Loss (Typ.)	0.92	1.21	1.82	2.6	4.04	dB	0.026
PE3M0441-36	36 inch	Insertion Loss (Typ.)	1.28	1.72	2.63	3.79	5.96	dB	0.029
PE3M0441-48	48 inch	Insertion Loss (Typ.)	1.64	2.22	3.43	4.99	7.88	dB	0.032
PE3M0441-60	60 inch	Insertion Loss (Typ.)	2	2.73	4.24	6.18	9.8	dB	0.035

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.023 pounds
Additional Weight per Foot:	0.003 pounds

Electrical Specification Notes:  
Values at 25°C, sea level.

**Mechanical Specifications**

**Cable Assembly**

Description	Minimum	Typical	Maximum	Units
Length*			0 [0]	in [mm]
Weight		0.023 [10.43]		lbs [g]

**Cable Characteristics**

Description	Specification
Cable Type	PE-SR047FL
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Tinned Copper Braid

**Connector Characteristics**

Description	Connector 1	Connector 2
Type	Mini SMP Pin	Mini SMP Socket
Specification	MIL-DTL-38999	MIL-DTL-38999
Impedance	50 Ohms	50 Ohms

SMPM Size 12 D38999 Contact Pin to SMPM  
Size 12 D38999 Contact Socket Cable Using PE-  
SR047FL Coax with Heat Shrink, LF Solder



## PE3M0441

### Connector Characteristics

Description	Connector 1	Connector 2
Configuration	Straight	Straight
Connection Method	Push-on	Push-on
Contact Size	12	12
Mating Cycles	1,000	1,000
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Beryllium Copper, Gold	Stainless Steel, Passivated
Body Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold

Mechanical Specification Notes:

### Environmental Specifications

Description	Specification
Temperature Operating Range	-55 to +100 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data


Notes:  
Values at 25°C, sea level.

SMPM Size 12 D38999 Contact Pin to SMPM Size 12 D38999 Contact Socket Cable Using PE-SR047FL Coax with Heat Shrink, LF Solder



**PE3M0441**

**How to Order**



Example: PE3M0441-12 = 12 inches long cable  
PE3M0441-100cm = 100 cm long cable

Cable Assembly Length Tolerances:

Imperial English		Metric	
"L" ≤ 1 ft	+0.5 in / -0 in	"L" ≤ 0.3 m	+12.5 mm / -0 mm
1 ft < "L" ≤ 5 ft	+1 in / -0 in	0.3 m < "L" ≤ 1.5 m	+25 mm / -0 mm
5 ft < "L" ≤ 10 ft	+2 in / -0 in	1.5 m < "L" ≤ 3 m	+50 mm / -0 mm
10 ft < "L" ≤ 25 ft	+3 in / -0 in	3 m < "L" ≤ 7.5 m	+75 mm / -0 mm
25 ft < "L"	+2%"L" / -0%"L"	7.5 m < "L"	+2%"L" / -0%"L"

\* Cable Length = "L"

SMPM Size 12 D38999 Contact Pin to SMPM Size 12 D38999 Contact Socket Cable Using PE-SR047FL Coax with Heat Shrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMPM Size 12 D38999 Contact Pin to SMPM Size 12 D38999 Contact Socket Cable Using PE-SR047FL Coax with Heat Shrink, LF Solder PE3M0441](https://www.pasternack.com/smpm-12-contact-pin-to-smpm-12-contact-socket-cable-using-pe-sr047fl-coax-with-heatshrink-lf-solder-pe3m0441-p.aspx)

URL: <https://www.pasternack.com/smpm-12-contact-pin-to-smpm-12-contact-socket-cable-using-pe-sr047fl-coax-with-heatshrink-lf-solder-pe3m0441-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3M0441 CAD Drawing

SMPM Size 12 D38999 Contact Pin to SMPM Size 12 D38999 Contact Socket  
Cable Using PE-SR047FL Coax with Heat Shrink, LF Solder

