



TNC Male to TNC Male Low Loss Cable 24 Inch Length Using TCOM-240 Coax with Times Microwave Components

RF Cable Assemblies Technical Data Sheet

PE3C9816-24

Configuration

- Connector 1: TNC Male
- Connector 2: TNC Male
- Cable Type: TCOM-240
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Double Shielded
- PE Jacket
- 500 Mating Cycles

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C9816-24 TNC male to TNC male 24 inch cable using TCOM-240 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to TNC cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-240 coax. The PE3C9816-24 TNC male to TNC male cable assembly operates to 6 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	

--

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.18	0.25	0.35	0.63	0.89	dB

--

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of $0.1 \cdot \sqrt{F(\text{GHz})}$ dB per connector.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to TNC Male Low Loss Cable 24 Inch Length Using TCOM-240 Coax with Times Microwave Components PE3C9816-24](#)



TNC Male to TNC Male Low Loss Cable 24 Inch Length Using
TCOM-240 Coax with Times Microwave Components

RF Cable Assemblies Technical Data Sheet

PE3C9816-24

Mechanical Specifications

Cable Assembly

Length* 24 in [609.6 mm]

Weight 0.16 lbs [72.57 g]

Cable

Cable Type TCOM-240
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper
Dielectric Type PE (F)
Number of Shields 2
Shield Layer 1 Silver Plated Copper Braid
Shield Layer 2 Tinned Copper Braid
Jacket Material PE, Black
Jacket Diameter 0.24 in [6.1 mm]

Connectors

Description	Connector 1	Connector 2
Type	TNC Male Threaded	TNC Male Threaded
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	500
Contact Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Contact Plating Specification	50µ in. minimum	50µ in. minimum
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80µ in. minimum	80µ in. minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	80µ in. minimum	80µ in. minimum

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to TNC Male Low Loss Cable 24 Inch Length Using TCOM-240 Coax with Times Microwave Components PE3C9816-24](#)



TNC Male to TNC Male Low Loss Cable 24 Inch Length Using TCOM-240 Coax with Times Microwave Components

RF Cable Assemblies Technical Data Sheet

PE3C9816-24

How to Order

Part Number Configuration:

PE3C9816

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C9816-12 = 12 inches long cable
PE3C9816-100cm = 100 cm long cable

TNC Male to TNC Male Low Loss Cable 24 Inch Length Using TCOM-240 Coax with Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to TNC Male Low Loss Cable 24 Inch Length Using TCOM-240 Coax with Times Microwave Components PE3C9816-24](#)

URL: <https://www.pasternack.com/tnc-male-to-tnc-male-low-loss-cable-24-inch-length-using-tcom-240-pe3c9816-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C9816-24 CAD Drawing

TNC Male to TNC Male Low Loss Cable 24 Inch Length Using
TCOM-240 Coax with Times Microwave Components



NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT:
36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED.
LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

				INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
PE PASTERNAK[®] an INFINITI@ brand					
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920					
DESCRIPTION TNC MALE TO TNC MALE LOW LOSS CABLE USING TCOM-240 COAX WITH TIMES MICROWAVE COMPONENTS					
SIZE	CAGE CODE	DRAWN BY	ITEM NO.	SCALE	SHEET
A	53919	KGLEBOVA	PE3C9816	NONE	1 OF 1
UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES. DIMENSIONS IN [] ARE MILLIMETERS.					
TOLERANCES:					
X = ±.2 [5]		FRACTIONS ± 1/32			
XX = ±.02 [0.5]		ANGLES ± 1°			
CABLE LENGTH TOLERANCES:					
≤120 [305] = ±.1 [25] / -0					
>120 [305] ≤ 300 [7620] = ±.001 [0.025] / -0					
>300 [7620] ≤ 600 [1524] = ±.002 [0.051] / -0					
>600 [1524] ≤ 1200 [3048] = ±.004 [0.102] / -0					
>1200 [3048] ≤ 3000 [7620] = ±.01 [.152] / -0					
>3000 [7620] = +.05% / -0					
ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS ARE TO BE TAKEN FROM THE END OF THE CABLE AND SUBJECT TO CHANGE WITHOUT NOTICE. UNDIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.					