

N Male Right Angle to SMA Male Low Loss Cable 36 Inch Length  
Using TCOM-240 Coax with Times Microwave Components



## RF Cable Assemblies Technical Data Sheet

**PE3C9829-36**

### Configuration

- Connector 1: N Male Right Angle
- Connector 2: SMA Male
- Cable Type: TCOM-240
- Coax Flex Type: Flexible

### Features

- Max Frequency 6 GHz
- Double Shielded
- PE Jacket
- 500 Mating Cycles

### Applications

- General Purpose
- Laboratory Use

### Description

Pasternack's PE3C9829-36 type N male right angle to SMA male 36 inch cable using TCOM-240 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to SMA cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-240 coax. The PE3C9829-36 type N male to SMA male cable assembly operates to 6 GHz. The right angle type N interface on the TCOM-240 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.41	0.48	0.58	0.88	1.09	dB

Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to SMA Male Low Loss Cable 36 Inch Length Using TCOM-240 Coax with Times Microwave Components PE3C9829-36](#)

## N Male Right Angle to SMA Male Low Loss Cable 36 Inch Length Using TCOM-240 Coax with Times Microwave Components



### RF Cable Assemblies Technical Data Sheet

**PE3C9829-36**

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.25 dB for the SMA male connector and  $0.1 * \text{SQRT}(F \text{GHz})$  dB for the N male right angle connector.

#### Mechanical Specifications

**Cable Assembly**

Length*	36 in [914.4 mm]
Weight	0.21 lbs [95.25 g]

**Cable**

Cable Type	TCOM-240
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.24 in [6.1 mm]

**Connectors**

Description	Connector 1	Connector 2
Type	N Male Right Angle Threaded	SMA Male Threaded
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	500
Contact Material and Plating	Beryllium Bronze, Gold	Beryllium Copper, Gold
Contact Plating Specification	50 $\mu\text{in}$ minimum	ASTM B488
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Tri-Metal
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 $\mu\text{in}$ minimum	
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	80 $\mu\text{in}$ minimum	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to SMA Male Low Loss Cable 36 Inch Length Using TCOM-240 Coax with Times Microwave Components PE3C9829-36](#)

N Male Right Angle to SMA Male Low Loss Cable 36 Inch Length  
Using TCOM-240 Coax with Times Microwave Components



**RF Cable Assemblies Technical Data Sheet**

**PE3C9829-36**


**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration:



Example: PE3C9829-12 = 12 inches long cable  
PE3C9829-100cm = 100 cm long cable

N Male Right Angle to SMA Male Low Loss Cable 36 Inch Length Using TCOM-240 Coax with Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to SMA Male Low Loss Cable 36 Inch Length Using TCOM-240 Coax with Times Microwave Components PE3C9829-36](#)


URL: <https://www.pasternack.com/n-male-right-angle-to-sma-male-low-loss-cable-36-inch-length-using-tcom-240-pe3c9829-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C9829-36 CAD Drawing

## N Male Right Angle to SMA Male Low Loss Cable 36 Inch Length Using TCOM-240 Coax with Times Microwave Components

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	06/26/2023	KGLEBOVA	AGANWANI



## NOTES

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT:  
36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED.  
LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES  
FROM EACH CONNECTOR.
2. CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE, WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.