

MCX Plug Right Angle to Push-On SMB Plug Cable Using PE-SR405FLJ Coax



PE3C9930

Configuration

- Connector 1: MCX Plug Right Angle
- Connector 2: Push-On SMB Plug
- Cable Type: PE-SR405FLJ
- Coax Flex Type: Formable

Features

- Max Frequency 4 GHz
- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C9930 MCX plug right angle to SMB plug push-on cable using PE-SR405FLJ coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack MCX to SMB cable assembly has a plug to plug gender configuration with 50 ohm formable PE-SR405FLJ coax. The PE3C9930 MCX plug to SMB plug cable assembly operates to 4 GHz. The right angle MCX interface on the PE-SR405FLJ cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ohms/1000ft [Ohms/Km]

Specifications by Frequency

MCX Plug Right Angle to Push-On SMB Plug Cable Using PE-SR405FLJ Coax



PE3C9930

Part Number	Length	Description	F1	F2	F3	Units	Weight (lbs)
		Frequency	500	1000	4000	MHz	
PE3C9930	Custom Lengths Available	Insertion Loss (Typ.)	0.15	0.23	0.468	dB/ft	
			0.5	0.74	1.54	dB/m	
PE3C9930-6	6 inch	Insertion Loss (Typ.)	0.38	0.42	0.54	dB	0.021
PE3C9930-9	9 inch	Insertion Loss (Typ.)	0.42	0.47	0.66	dB	0.025
PE3C9930-12	12 inch	Insertion Loss (Typ.)	0.45	0.53	0.77	dB	0.028
PE3C9930-18	18 inch	Insertion Loss (Typ.)	0.53	0.64	1.01	dB	0.036
PE3C9930-24	24 inch	Insertion Loss (Typ.)	0.6	0.75	1.24	dB	0.043

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.2 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.028 pounds
Additional Weight per Inch:	0.00117 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.028 lbs [12.7 g]

Cable

Cable Type	PE-SR405FLJ
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Tinned Copper Composite Braid
Jacket Material	FEP, Black
Jacket Diameter	0.105 in [2.67 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	0.787 in [19.99 mm]

MCX Plug Right Angle to Push-On SMB Plug Cable Using PE-SR405FLJ Coax



PE3C9930

Connectors

Description	Connector 1	Connector 2
Type	MCX Plug Right Angle	SMB Plug
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Connection Method		Push-On
Contact Material and Plating	Brass, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification		30µin. minimum
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Gold over Nickel	Brass, Gold
Body Plating Specification		3µin. minimum
Coupling Nut Material and Plating		Brass, Gold
Coupling Nut Plating Specification		3µin. minimum

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

MCX Plug Right Angle to Push-On SMB Plug Cable Using PE-SR405FLJ Coax



PE3C9930

Typical Performance Data

How to Order

Part Number Configuration:

PE3C9930

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: PE3C9930-12 = 12 inches long cable
PE3C9930-100cm = 100 cm long cable

MCX Plug Right Angle to Push-On SMB Plug Cable Using PE-SR405FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug Right Angle to Push-On SMB Plug Cable Using PE-SR405FLJ Coax PE3C9930](#)

URL: <https://www.pasternack.com/mcx-plug-right-angle-to-push-on-smb-plug-cable-using-pe-sr405flj-pe3c9930-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C9930 CAD Drawing
MCX Plug Right Angle to Push-On SMB Plug Cable Using PE-SR405FLJ Coax

