

Lead Free High Temp 1553 Twinax Cable
Assembly TRB Plug To Blunt Cut, 48 Inch

RF Cable Assemblies Technical Data Sheet

PE3MSA00437-48

Configuration

- Connector 1: TRB Plug
- Connector 2: Blunt Cut
- Cable Type: M17/176-00002

Features

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Description

Pasternack's PE3MSA00437-48 78 ohm TRB plug to Blunt cut 48 inch cable using 78 ohm M17/176-00002 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. The PE3MSA00437-48 TRB plug to Blunt cut cable assembly operates to 10 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications


Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Insertion Loss (Typ.)

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free High Temp 1553 Twinax Cable Assembly TRB Plug To Blunt Cut, 48 Inch PE3MSA00437-48](#)



Lead Free High Temp 1553 Twinax Cable
Assembly TRB Plug To Blunt Cut, 48 Inch

RF Cable Assemblies Technical Data Sheet

PE3MSA00437-48

Mechanical Specifications

Cable Assembly

Length*	48 in [121.92 cm]
Weight	0.25289 lbs [114.71 g]

Cable

Cable Type	M17/176-00002
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Shield Layer 1	Silver Plated Copper
Jacket Material	PFA, Blue

One Time Minimum Bend Radius	1.5 in [38.1 mm]
------------------------------	------------------

Connectors

Description	Connector 1	Connector 2
Type	TRB Plug	Blunt Cut
Impedance	78 Ohms	
Contact Material and Plating	Bronze, Gold 30 micro inches	
Contact Plating Specification	ASTM-B-488	
Dielectric Type	Teflon	
Outer Conductor Material and Plating	Phosphor Bronze, Gold	
Outer Conductor Plating Specification	30 micro inches	
Body Material and Plating	Brass, Nickel	
Body Plating Specification	ASTM-B-733	

Environmental Specifications

Temperature


Operating Range	-55 to +200 deg C
-----------------	-------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free High Temp 1553 Twinax Cable Assembly TRB Plug To Blunt Cut, 48 Inch PE3MSA00437-48](#)



Lead Free High Temp 1553 Twinax Cable Assembly TRB Plug To Blunt Cut, 48 Inch

RF Cable Assemblies Technical Data Sheet

PE3MSA00437-48

How to Order

Part Number Configuration:

PE3MSA00437

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3MSA00437-12 = 12 inches long cable
PE3MSA00437-100cm = 100 cm long cable


Lead Free High Temp 1553 Twinax Cable Assembly TRB Plug To Blunt Cut, 48 Inch from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free High Temp 1553 Twinax Cable Assembly TRB Plug To Blunt Cut, 48 Inch PE3MSA00437-48](https://www.pasternack.com/trb-plug-to-blunt-cut-1553-cable-48-inch-length-using-m17-176-00002-pe3msa00437-48-p.aspx)

URL: <https://www.pasternack.com/trb-plug-to-blunt-cut-1553-cable-48-inch-length-using-m17-176-00002-pe3msa00437-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

1
2
3
4
5
6



ITEM NUMBER	LENGTH	
	FEET	METERS
PE3MSA00437-12	1.0	.31
PE3MSA00437-24	2.0	.61
PE3MSA00437-36	3.0	.92
PE3MSA00437-48	4.0	1.22
PE3MSA00437-60	5.0	1.52

- NOTES:
1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR PART WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		 		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES: .X = ±.2 [5] FRACTIONS .XX = ±.02 [.5] ± 1/32 .XXX = ±.005 [.13] ANGLES ±°		SCALE NONE SHEET 1 OF 1			
CABLE LENGTH TOLERANCES: ≤12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +6 [%] / -0		DESCRIPTION LEAD FREE HT 1553 TWNX PLUG-BLUNT			
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920					
SIZE		CAGE CODE	DRAWN BY	ITEM NO.	REV
A		53919	DMAY	PE3MSA00437	A
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.					