



Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable 24 Inch Length Using 78 Ohm M17/176-00002 Coax

RF Cable Assemblies Technical Data Sheet

PE3CA2342-24

Configuration

- Connector 1: TRB Plug
- Connector 2: Blunt Cut Genderless
- Cable Type: M17/176-00002
- Coax Flex Type: Flexible

Features

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Description

Pasternack's PE3CA2342-24 78 ohm TRB plug to Blunt cut genderless 24 inch cable using 78 ohm M17/176-00002 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to Blunt Cut cable assembly has a plug to genderless gender configuration with 78 ohm flexible M17/176-00002 twinax. The PE3CA2342-24 TRB plug to Blunt cut genderless cable assembly operates to 10 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	7	10	MHz

Insertion Loss (Typ.)

Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable 24 Inch Length Using 78 Ohm M17/176-00002 Coax PE3CA2342-24](#)



Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable
24 Inch Length Using 78 Ohm M17/176-00002 Coax

RF Cable Assemblies Technical Data Sheet

PE3CA2342-24

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	24 in [609.6 mm]
Weight	0.086 lbs [39.01 g]

Cable

Cable Type	M17/176-00002
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Shield Layer 1	Silver Plated Copper
Jacket Material	PFA, Blue

One Time Minimum Bend Radius	1.5 in [38.1 mm]
------------------------------	------------------

Connectors

Description	Connector 1	Connector 2
Type	TRB Plug Bayonet	Blunt Cut Genderless Other
Option	Bend Relief Spring	
Impedance	78 Ohms	
Contact Material and Plating	Bronze, Gold 30 micro inches	
Contact Plating Specification	ASTM-B-488	
Dielectric Type	Teflon	
Outer Conductor Material and Plating	Phosphor Bronze, Gold	
Outer Conductor Plating Specification	30 micro inches	
Body Material and Plating	Brass, Nickel	
Body Plating Specification	ASTM-B-733	

Environmental Specifications

Temperature

Operating Range	-55 to +200 deg C
-----------------	-------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable 24 Inch Length Using 78 Ohm M17/176-00002 Coax PE3CA2342-24](#)



Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable
24 Inch Length Using 78 Ohm M17/176-00002 Coax

RF Cable Assemblies Technical Data Sheet

PE3CA2342-24

How to Order

Part Number Configuration:

PE3CA2342

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3CA2342-12 = 12 inches long cable
PE3CA2342-100cm = 100 cm long cable

Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable 24 Inch Length Using 78 Ohm M17/176-00002 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable 24 Inch Length Using 78 Ohm M17/176-00002 Coax PE3CA2342-24](https://www.pasternack.com/trb-plug-to-blunt-cut-genderless-1553-cable-24-inch-length-using-m17-176-00002-pe3ca2342-24)

URL: <https://www.pasternack.com/trb-plug-to-blunt-cut-genderless-1553-cable-24-inch-length-using-m17-176-00002-pe3ca2342-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3CA2342-24 CAD Drawing

Bend Relief TRB Plug to Blunt Cut Genderless 1553 Cable
24 Inch Length Using 78 Ohm M17/176-00002 Coax



NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PASTERNAK
an INFINITE brand

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE: NONE

SHEET: 1 OF 1

DESCRIPTION: 3 SLOT SOLDER CLAMP PLUG TO BLUNT

SIZE: A	CAGE CODE: 53919	DRAWN BY: DMAY	ITEM NO.: PE3CA2342	REV: A
---------	------------------	----------------	---------------------	--------

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
.XX = ±.02 [.5] ±.1/32
.XXX = ±.005 [.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.