



Lead Free 2-Slot TRB Plug to 3-Lug TRB Jack 1553 Cable
48 Inch Length Using 78 Ohm M17/176-00002 Twinax

RF Cable Assemblies Technical Data Sheet

PE3MSA00464-48

Configuration

- Connector 1: TRB PLUG
- Connector 2: TRB Jack
- Cable Type: M17/176-00002
- Coax Flex Type: Flexible

Features

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Description

Pasternack's PE3MSA00464-48 78 ohm TRB plug to 78 ohm TRB jack 48 inch cable using 78 ohm M17/176-00002 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to TRB cable assembly has a plug to jack gender configuration with 78 ohm flexible M17/176-00002 twinax. The PE3MSA00464-48 TRB plug to TRB jack cable assembly operates to 10 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	7	10	MHz
Insertion Loss (Typ.)	0.256	0.284	0.312	0.34	0.38	dB

Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free 2-Slot TRB Plug to 3-Lug TRB Jack 1553 Cable 48 Inch Length Using 78 Ohm M17/176-00002 Twinax PE3MSA00464-48](#)



Lead Free 2-Slot TRB Plug to 3-Lug TRB Jack 1553 Cable
48 Inch Length Using 78 Ohm M17/176-00002 Twinax

RF Cable Assemblies Technical Data Sheet

PE3MSA00464-48

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	48 in [121.92 cm]
Weight	0.148 lbs [67.13 g]

Cable

Cable Type	M17/176-00002
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Shield Layer 1	Silver Plated Copper
Jacket Material	PFA, Blue

One Time Minimum Bend Radius	1.5 in [38.1 mm]
------------------------------	------------------

Connectors

Description	Connector 1	Connector 2
Type	TRB PLUG	TRB Jack
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

Environmental Specifications

Temperature

Operating Range	-55 to +200 deg C
-----------------	-------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free 2-Slot TRB Plug to 3-Lug TRB Jack 1553 Cable 48 Inch Length Using 78 Ohm M17/176-00002 Twinax PE3MSA00464-48](#)



Lead Free 2-Slot TRB Plug to 3-Lug TRB Jack 1553 Cable
48 Inch Length Using 78 Ohm M17/176-00002 Twinax

RF Cable Assemblies Technical Data Sheet

PE3MSA00464-48

How to Order

Part Number Configuration:

PE3MSA00464

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3MSA00464-12 = 12 inches long cable
PE3MSA00464-100cm = 100 cm long cable

Lead Free 2-Slot TRB Plug to 3-Lug TRB Jack 1553 Cable 48 Inch Length Using 78 Ohm M17/176-00002 Twinax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free 2-Slot TRB Plug to 3-Lug TRB Jack 1553 Cable 48 Inch Length Using 78 Ohm M17/176-00002 Twinax PE3MSA00464-48](#)


URL: <https://www.pasternack.com/lead-free-trb-plug-to-trb-jack-1553-cable-48-inch-length-using-m17-176-00002-pe3msa00464-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3MSA00464-48 CAD Drawing

Lead Free 2-Slot TRB Plug to 3-Lug TRB Jack 1553 Cable
48 Inch Length Using 78 Ohm M17/176-00002 Twinax

LEAD FREE SOLDER



ITEM NUMBER	LENGTH	
	FEET	METERS
PE3MSA00464-12	1.0	.31
PE3MSA00464-24	2.0	.61
PE3MSA00464-36	3.0	.92
PE3MSA00464-48	4.0	1.22
PE3MSA00464-60	5.0	1.52

- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/11/2023	DMAY	EKIM

PASTERNAK
an INFINITE brand

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
XX = ±.02 [.5] ±.1/32
XXX = ±.005 [.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = ±.1 [25] / -0
>12 [305] ≤ 60 [1524] = ±.2 [5] / -0
>60 [1524] ≤ 120 [3048] = ±.4 [102] / -0
>120 [3048] ≤ 300 [7620] = ±.6 [152] / -0
>300 [7620] = ±.5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE: NONE
SHEET: 1 OF 1

DESCRIPTION:
LEAD FREE HIGH TEMP TRB 2-SLOT PLUG - 3-LUG CABLE JACK

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	DMAY	PE3MSA00464	A