



TRB 3-Slot Solder/Clamp Plug to TRB 2-slot Solder/  
Clamp Plug M17/176-00002 .129 O.D. 36" Cable

## RF Cable Assemblies Technical Data Sheet

**PE3MP2377-36**

### Configuration

- Connector 1: TRB Plug
- Connector 2: TRB Plug
- Cable Type: M17/176-00002
- Coax Flex Type: Flexible

### • Features

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

### Applications

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

### Description

Pasternack's PE3MP2377-36 78 ohm TRB plug to 78 ohm TRB plug 36 inch cable using 78 ohm M17/176-00002 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to TRB cable assembly has a plug to plug gender configuration with 78 ohm flexible M17/176-00002 twinax. The PE3MP2377-36 TRB plug to TRB plug cable assembly operates to 10 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description            | Minimum | Typical    | Maximum | Units        |
|------------------------|---------|------------|---------|--------------|
| Frequency Range        | DC      |            | 10      | MHz          |
| Capacitance            |         | 24 [78.74] |         | pF/ft [pF/m] |
| Operating Voltage (AC) |         |            | 750,000 | Vrms         |

### Specifications by Frequency

| Description           | F1    | F2    | F3    | F4    | F5    | Units |
|-----------------------|-------|-------|-------|-------|-------|-------|
| Frequency             | 1     | 3     | 5     | 7     | 10    | MHz   |
| Insertion Loss (Typ.) | 0.242 | 0.263 | 0.284 | 0.305 | 0.335 | dB    |

Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Slot Solder/Clamp Plug to TRB 2-slot Solder/Clamp Plug M17/176-00002 .129 O.D. 36" Cable PE3MP2377-36](#)



TRB 3-Slot Solder/Clamp Plug to TRB 2-slot Solder/  
Clamp Plug M17/176-00002 .129 O.D. 36" Cable

**RF Cable Assemblies Technical Data Sheet**

**PE3MP2377-36**

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

**Mechanical Specifications**

**Cable Assembly**

|         |                       |
|---------|-----------------------|
| Length* | 36 in [914.4 mm]      |
| Weight  | 0.3025 lbs [137.21 g] |

**Cable**

|                                      |                      |
|--------------------------------------|----------------------|
| Cable Type                           | M17/176-00002        |
| Impedance                            | 78 Ohms              |
| Inner Conductor Type                 | Stranded             |
| Inner Conductor Material and Plating | Copper, Silver       |
| Dielectric Type                      | PTFE                 |
| Shield Layer 1                       | Silver Plated Copper |
| Jacket Material                      | PFA, Blue            |

|                              |                  |
|------------------------------|------------------|
| One Time Minimum Bend Radius | 1.5 in [38.1 mm] |
|------------------------------|------------------|

**Connectors**

| Description                           | Connector 1                  | Connector 2                  |
|---------------------------------------|------------------------------|------------------------------|
| Type                                  | TRB Plug                     | TRB Plug                     |
| Impedance                             | 78 Ohms                      | 78 Ohms                      |
| Contact Material and Plating          | Bronze, Gold 30 micro inches | Bronze, Gold 30 micro inches |
| Contact Plating Specification         | ASTM-B-488                   | ASTM-B-488                   |
| Dielectric Type                       | Teflon                       | Teflon                       |
| Outer Conductor Material and Plating  | Phosphor Bronze, Gold        | Phosphor Bronze, Gold        |
| Outer Conductor Plating Specification | 30 micro inches              | 30 micro inches              |
| Body Material and Plating             | Brass, Nickel                | Brass, Nickel                |
| Body Plating Specification            | ASTM-B-733                   | ASTM-B-733                   |

**Environmental Specifications**

**Temperature**

|                 |                   |
|-----------------|-------------------|
| Operating Range | -55 to +200 deg C |
|-----------------|-------------------|

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Slot Solder/Clamp Plug to TRB 2-slot Solder/Clamp Plug M17/176-00002 .129 O.D. 36" Cable PE3MP2377-36](#)



TRB 3-Slot Solder/Clamp Plug to TRB 2-slot Solder/  
Clamp Plug M17/176-00002 .129 O.D. 36" Cable

## RF Cable Assemblies Technical Data Sheet

**PE3MP2377-36**

### How to Order

Part Number Configuration:

**PE3MP2377**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3MP2377-12 = 12 inches long cable  
PE3MP2377-100cm = 100 cm long cable

TRB 3-Slot Solder/Clamp Plug to TRB 2-slot Solder/Clamp Plug M17/176-00002 .129 O.D. 36" Cable from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Slot Solder/Clamp Plug to TRB 2-slot Solder/Clamp Plug M17/176-00002 .129 O.D. 36" Cable PE3MP2377-36](#)

URL: <https://www.pasternack.com/trb-plug-to-trb-plug-1553-cable-36-inch-length-using-m17-176-00002-pe3mp2377-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

