



ROHS Low Smoke Zero Halogen 78 Ohm TRB  
2-Slot Solder/Clamp Plug with Blunt Cut for TWCH-  
78-2, 12" Cable (.242" O.D.) -30C +80C

## RF Cable Assemblies Technical Data Sheet

**PE3MSA00604-12**

### Configuration

- Connector 1: TRB Plug
- Connector 2: Blunt Cut
- Cable Type: TWCH-78-2

### Features

- Max Frequency 500 MHz
- HF POF Jacket
- MIL-STD-1553
- -30°C to +80°C
- 78 ohms
- ROHS Low Smoke Zero Halogen
- Non-Toxic

### Applications

- General Purpose
- Laboratory Use
- Military Contractors
- MIL-STD-1553
- Data
- Safer Environments
- Ventilation critical areas
- Hospitals

### Description

Pasternack's PE3MSA00604-12 78 ohm TRB plug to Blunt cut 12 inch cable using 78 ohm TWCH-78-2 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. The PE3MSA00604-12 TRB plug to Blunt cut cable assembly operates to 500 MHz. The PE3MSA00604 cable assembly consists of a 78 Ohm ROHS Low Smoke Zero Halogen TRB 2-Slot Solder/Clamp Plug with Blunt Cut for TWCH-78-2 cable (.242 O.D.) suitable for MIL-STD-1553 Applications. The zero halogen jacket cable reduces the amount of toxic and corrosive gases emitted during combustion. Typically used in poorly ventilated areas, zero halogen is very popular with military contractors and anywhere the protection of people and equipment from toxic and corrosive gases is critical.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB Plug to Blunt Cut 1553 Cable 12 Inch Length Using 78 Ohm TWCH-78-2 Coax PE3MSA00604-12](#)



ROHS Low Smoke Zero Halogen 78 Ohm TRB  
2-Slot Solder/Clamp Plug with Blunt Cut for TWCH-  
78-2, 12" Cable (.242" O.D.) -30C +80C

## RF Cable Assemblies Technical Data Sheet

PE3MSA00604-12

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Capacitance		21.2 [69.55]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Insertion Loss (Typ.)

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length*	12 in [304.8 mm]
Weight	0.27 lbs [122.47 g]

#### Cable

Cable Type	TWCH-78-2
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	HF POF, Blue

One Time Minimum Bend Radius	1.25 in [31.75 mm]
------------------------------	--------------------

### Connectors

Description	Connector 1	Connector 2
Type	TRB Plug	Blunt Cut
Impedance	78 Ohms	
Contact Material and Plating	Bronze, Gold 30 micro inches	
Contact Plating Specification	ASTM-B-488	
Dielectric Type	Teflon	
Outer Conductor Material and Plating	Phosphor Bronze, Gold	
Outer Conductor Plating Specification	30 micro inches	
Body Material and Plating	Brass, Nickel	
Body Plating Specification	ASTM-B-733	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB Plug to Blunt Cut 1553 Cable 12 Inch Length Using 78 Ohm TWCH-78-2 Coax PE3MSA00604-12](#)



ROHS Low Smoke Zero Halogen 78 Ohm TRB  
2-Slot Solder/Clamp Plug with Blunt Cut for TWCH-  
78-2, 12" Cable (.242" O.D.) -30C +80C

## RF Cable Assemblies Technical Data Sheet

**PE3MSA00604-12**

### Environmental Specifications

#### Temperature

Operating Range

-30 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

### How to Order

Part Number Configuration:

**PE3MSA00604**

- **xx**

**uu**

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE3MSA00604-12 = 12 inches long cable  
PE3MSA00604-100cm = 100 cm long cable

ROHS Low Smoke Zero Halogen 78 Ohm TRB 2-Slot Solder/Clamp Plug with Blunt Cut for TWCH-78-2, 12" Cable (.242" O.D.) -30C +80C from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB Plug to Blunt Cut 1553 Cable 12 Inch Length Using 78 Ohm TWCH-78-2 Coax PE3MSA00604-12](#)

URL: <https://www.pasternack.com/trb-plug-to-blunt-cut-1553-cable-12-inch-length-using-twch-78-2-pe3msa00604-12-p.aspx>



The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3MSA00604-12 CAD Drawing

ROHS Low Smoke Zero Halogen 78 Ohm TRB 2-Slot Solder/Clamp Plug  
with Blunt Cut for TWCH-78-2, 12" Cable (.242" O.D.) -30C +80C



**LEAD FREE SOLDER**



WIRING MAP

ITEM NUMBER	LENGTH	
	FEET	METERS
PE3MSA00604-12	1.0	.31
PE3MSA00604-24	2.0	.61
PE3MSA00604-36	3.0	.92
PE3MSA00604-48	4.0	1.22
PE3MSA00604-60	5.0	1.52

REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV			
	A	04/28/2016	DMAY	EKIM
DESCRIPTION				
INITIAL RELEASE				

**PE PASTERNAK**  
an INFINIT® brand

Website: [www.Pasternack.com](http://www.Pasternack.com)  
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION  
**LEAD FREE LSZH 0.242" O.D. 1553 TWNX 2-SLOT PL-BLUNT**

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE: NONE SHEET: 1 OF 1

---

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
 .X = ±.2 [ .5 ] FRACTIONS  
 .XX = ±.02 [ .5 ] ±.1/32  
 .XXX = ±.005 [ .13 ] ANGLES ± 1°

CABLE LENGTH TOLERANCES:  
 ≤12 [305] = +1 [25] / -0  
 >12 [305] ≤ 60 [1524] = +2 [51] / -0  
 >60 [1524] ≤ 120 [3048] = +4 [102] / -0  
 >120 [3048] ≤ 300 [7620] = +6 [152] / -0  
 >300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.

- NOTES:**
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
  - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.