



TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless  
1553 Cable 48 Inch Length Using 124 Ohm  
TWC-124-2 Coax Bend Relief Spring

## RF Cable Assemblies Technical Data Sheet

**PE3MSA00671-48**

### Configuration

- Connector 1: TRB 3-Lug Jack Bulkhead
- Connector 2: Blunt Cut Genderless
- Cable Type: TWC-124-2
- Coax Flex Type: Flexible

### Features

- Max Frequency 500 MHz
- PVC Jacket
- 124 ohms
- Twinaxial
- MIL-STD-1553B
- -40°C to +80°C
- Lead Free Solder
- Standard and Custom Lengths Available

### Applications

- General Purpose
- Laboratory Use
- MIL-STD-1553B Applications
- Data Transmission

### Description

Pasternack's PE3MSA00671-48 78 ohm TRB 3-Lug jack bulkhead to Blunt cut genderless 48 inch cable using 124 ohm TWC-124-2 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB 3-Lug to Blunt Cut cable assembly has a jack to genderless gender configuration with 124 ohm flexible TWC-124-2 twinax. The PE3MSA00671-48 TRB 3-Lug jack to Blunt cut genderless cable assembly operates to 500 MHz. Our RF cable assembly with TRB 3-Lug bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless 1553 Cable 48 Inch Length Using 124 Ohm TWC-124-2 Coax Bend Relief Spring PE3MSA00671-48](#)



TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless  
 1553 Cable 48 Inch Length Using 124 Ohm  
 TWC-124-2 Coax Bend Relief Spring

## RF Cable Assemblies Technical Data Sheet

**PE3MSA00671-48**

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Capacitance		12.3 [40.35]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	500	MHz

Insertion Loss (Typ.)

### Mechanical Specifications

#### Cable Assembly

Length\* 48 in [121.92 cm]  
 Weight 0.33275 lbs [150.93 g]

#### Cable

Cable Type TWC-124-2  
 Impedance 124 Ohms  
 Inner Conductor Type Stranded  
 Inner Conductor Material and Plating Copper, Silver  
 Dielectric Type PE  
 Shield Layer 1 Silver Plated Copper  
 Jacket Material PVC, Blue

One Time Minimum Bend Radius 1.25 in [31.75 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless 1553 Cable 48 Inch Length Using 124 Ohm TWC-124-2 Coax Bend Relief Spring PE3MSA00671-48](#)



TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless  
 1553 Cable 48 Inch Length Using 124 Ohm  
 TWC-124-2 Coax Bend Relief Spring

## RF Cable Assemblies Technical Data Sheet

**PE3MSA00671-48**

### Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Lug Jack Bulkhead Bayonet	Blunt Cut Genderless Other
Option	Bend Relief Spring	
Specification	MIL-STD-1553	
Impedance	78 Ohms	
Contact Material and Plating	Bronze, Gold 30 micro inches	
Contact Plating Specification	ASTM-B-488	
Dielectric Type	Teflon	
Outer Conductor Material and Plating	Phosphor Bronze, Gold	
Outer Conductor Plating Specification	30 micro inches	
Body Material and Plating	Brass, Nickel	
Body Plating Specification	ASTM-B-733	

### Environmental Specifications

#### Temperature

Operating Range -40 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless 1553 Cable 48 Inch Length Using 124 Ohm TWC-124-2 Coax Bend Relief Spring PE3MSA00671-48](#)



TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless  
 1553 Cable 48 Inch Length Using 124 Ohm  
 TWC-124-2 Coax Bend Relief Spring

## RF Cable Assemblies Technical Data Sheet

**PE3MSA00671-48**

### How to Order

Part Number Configuration:

**PE3MSA00671**

- **xx**

**uu**

Unit of Measure:  
 cm = Centimeters  
 <blank> = Inches  
 Length  
 Base Number

Example: PE3MSA00671-12 = 12 inches long cable  
 PE3MSA00671-100cm = 100 cm long cable

TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless 1553 Cable 48 Inch Length Using 124 Ohm TWC-124-2 Coax Bend Relief Spring from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless 1553 Cable 48 Inch Length Using 124 Ohm TWC-124-2 Coax Bend Relief Spring PE3MSA00671-48](https://www.pasternack.com/trb-3-lug-jack-bulkhead-to-blunt-cut-genderless-1553-cable-48-inch-length-using-twc-124-2-pe3msa00671-48)

URL: <https://www.pasternack.com/trb-3-lug-jack-bulkhead-to-blunt-cut-genderless-1553-cable-48-inch-length-using-twc-124-2-pe3msa00671-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3MSA00671-48 CAD Drawing

TRB 3-Lug Jack Bulkhead to Blunt Cut Genderless 1553 Cable 48 Inch Length Using 124 Ohm TWC-124-2 Coax Bend Relief Spring



ITEM NUMBER	LENGTH	
	FEET	METERS
PE3MSA00671-12	1.0	.31
PE3MSA00671-24	2.0	.61
PE3MSA00671-36	3.0	.92
PE3MSA00671-48	4.0	1.22
PE3MSA00671-60	5.0	1.52

## LEAD FREE SOLDER

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/18/2023	DMAY	EKIM

**PE PASTERNAK**  
an INFINITO brand

Website: [www.Pasternack.com](http://www.Pasternack.com)  
Phone: 1.866.727.8376 | 1.949.261.1920

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE: NONE

SHEET: 1 OF 1

---

**DESCRIPTION**  
ROHS LAB RATED 124 OHM 1553 TWINAX TRB BULKHEAD JACK BR - BLUNT CUT

SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	53919	DMAY	PE3MSA00671

---

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:

<small>.X = ±.2 [5]</small>	<small>FRACTIONS ±.1/32</small>
<small>.XX = ±.02 [5]</small>	<small>ANGLES ± 1°</small>
<small>.XXX = ±.005 [13]</small>	<small>CABLE LENGTH TOLERANCES:</small>

<12 [305] = +1 [25] / -0  
>12 [305] ≤ 60 [1524] = +2 [51] / -0  
>60 [1524] ≤ 120 [3048] = +4 [102] / -0  
>120 [3048] ≤ 300 [7620] = +6 [152] / -0  
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.

- NOTES:**
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
  - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.