

## 1.85mm Male to 1.85mm Female Precision Cable 24 Inch Length Using High Flex VNA Test Coax



### PE3TC0900-24

#### Configuration

- Connector 1: 1.85mm Male
- Connector 2: 1.85mm Female
- Cable Type: PE-VNA-HF
- Coax Flex Type: Flexible

#### Features

- Max Frequency 70 GHz
- Shielding Effectivity > 100 dB
- 78% Phase Velocity
- Triple Shielded
- Designed for use as VNA test port extenders
- Highly flexible armored cable construction
- Excellent amplitude and phase stability with flexure
- Non-conductive protective Nomex outer sleeve
- Each serialized assembly comes with test data
- In-stock and ready to ship same-day

#### Applications

- General Purpose
- Laboratory Use
- Vector Network analyzer test port extenders
- Precise bench-top testing
- Semiconductor probe testing
- Lab and production testing

#### Description

Pasternack high performance high flex VNA test cables are designed to provide customers repeatable and accurate VNA measurements. These Test cables have excellent electrical properties including low Insertion Loss, low VSWR and phase stability of +/- 8° with flexure. The braided stainless steel armoring provides a rugged, but flexible cable with a life exceeding 100,000 flex cycles. The rugged connectors provide up to 5,000 mating cycles when attached with proper care. The flexibility of these cables makes it easier and safer to test your Device Under Test (DUT). When used with the appropriate calibration kit, these test cables effectively extend the test port of the VNA allowing for accurate measurements of devices that cannot be directly connected to a network analyzer test port.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		70	GHz
VSWR			1.4:1	
Velocity of Propagation		78		%
RF Shielding	100			dB
Group Delay		1.34 [4.4]		ns/ft [ns/m]
Capacitance		25.9 [84.97]		pF/ft [pF/m]
Input Power (Average)			18	Watts

1.85mm Male to 1.85mm Female Precision Cable  
24 Inch Length Using High Flex VNA Test Coax



## PE3TC0900-24

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Phase Stability with Flexure		8		Degrees

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	5	10	20	40	50	GHz
Insertion Loss (Max.)	1.36	1.76	2.4	3.3	3.73	dB
Power Handling (Max.)					18	Watts

Electrical Specification Notes:  
Values at 25°C, sea level.

### Mechanical Specifications

#### Cable Assembly

Width/Diameter 0 in [0 mm]  
Weight 0.203 lbs [92.08 g]

#### Cable

Cable Type	PE-VNA-HF
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	3
Shield Layer 1	Silver Plated Copper Tape
Shield Layer 2	Silver Plated Copper Braid
Shield Layer 3	Silver Plated Copper Braid
Jacket Diameter	0.27 in [6.86 mm]
One Time Minimum Bend Radius	1 in [25.4 mm]
Flat Plate Crush	317 lbs/in [5.66 Kg/mm]

1.85mm Male to 1.85mm Female Precision Cable  
24 Inch Length Using High Flex VNA Test Coax



## PE3TC0900-24

### Connectors

Description	Connector 1	Connector 2
Type	1.85mm Male	1.85mm Female
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	ULTEM	ULTEM
Outer Conductor Material and Plating		Passivated Stainless Steel
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Material and Plating	Passivated Stainless Steel	
Torque	8 in-lbs 0.9 Nm	

### Environmental Specifications

Operating Range Temperature -65 to +125 deg C

### Compliance Certifications

(see product page for current document)

### Plotted and Other Data

Notes:


Values at 25°C, sea level.

1.85mm Male to 1.85mm Female Precision Cable  
24 Inch Length Using High Flex VNA Test Coax



## PE3TC0900-24

### Typical Performance Data



1.85mm Male to 1.85mm Female Precision Cable  
24 Inch Length Using High Flex VNA Test Coax



## PE3TC0900-24

### How to Order

Part Number Configuration:

PE3TC0900 - **xx** **uu**

			Unit of Measure:
			cm = Centimeters
			<blank> = Inches
			Length
			Base Number

Example: PE3TC0900-12 = 12 inches long cable  
PE3TC0900-100cm = 100 cm long cable

1.85mm Male to 1.85mm Female Precision Cable 24 Inch Length Using High Flex VNA Test Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [1.85mm Male to 1.85mm Female Precision Cable 24 Inch Length Using High Flex VNA Test Coax PE3TC0900-24](#)

URL: <https://www.pasternack.com/1.85mm-male-1.85mm-female-vna-cable-cable-assembly-pe3tc0900-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3TC0900-24 CAD Drawing

1.85mm Male to 1.85mm Female Precision Cable 24 Inch Length Using High Flex VNA Test Coax

