



SMC Plug to 10-32 Male Right Angle Cable
150 cm Length Using RG196 Coax

RF Cable Assemblies Technical Data Sheet



PE3W00597-150CM

Configuration

- Connector 1: SMC Plug
- Connector 2: 10-32 Male Right Angle
- Cable Type: RG196

Features

- Max Frequency 400 MHz
- PTFE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W00597-150CM SMC plug to 10-32 male right angle 150 cm cable using RG196 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMC to 10-32 cable assembly has a plug to male gender configuration with 50 ohm flexible RG196 coax. The PE3W00597-150CM SMC plug to 10-32 male cable assembly operates to 400 MHz. The right angle 10-32 interface on the RG196 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-----------------|---------|-------------|---------|--------------|
| Frequency Range | DC | | 400 | MHz |
| VSWR | | | 1.5:1 | |
| Capacitance | | 32 [104.99] | | pF/ft [pF/m] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Plug to 10-32 Male Right Angle Cable 150 cm Length Using RG196 Coax PE3W00597-150CM](#)



SMC Plug to 10-32 Male Right Angle Cable
150 cm Length Using RG196 Coax

RF Cable Assemblies Technical Data Sheet

PE3W00597-150CM

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|-----|----|----|----|-------|
| Frequency | 100 | 400 | | | | MHz |
| Insertion Loss (Typ.) | 0.78 | 1.8 | | | | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length* 59.06 in [150.01 cm]
Diameter 0.25 in [6.35 mm]

Cable

Cable Type RG196
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Silver Plated Copper
Jacket Material PTFE, White
Jacket Diameter 0.08 in [2.03 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Plug to 10-32 Male Right Angle Cable 150 cm Length Using RG196 Coax PE3W00597-150CM](#)



SMC Plug to 10-32 Male Right Angle Cable
150 cm Length Using RG196 Coax

RF Cable Assemblies Technical Data Sheet

PE3W00597-150CM

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------------|------------------------|------------------------|
| Type | SMC Plug | 10-32 Male Right Angle |
| Specification | MIL-STD-348A | MIL-C-39012 |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material and Plating | Beryllium Copper, Gold | Gold |
| Contact Plating Specification | 30µ in. minimum | MIL-G-45204 |
| Dielectric Type | Teflon | Teflon |
| Body Material and Plating | Brass, Nickel | Brass, Nickel |
| Body Plating Specification | 100µ in. minimum | |
| Coupling Nut Material and Plating | Brass, Nickel | Brass, Nickel |
| Coupling Nut Plating Specification | 100µ in. minimum | |
| Hex Size | 1/4 in | |
| Torque | 3 in-lbs [0.34 Nm] | |

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Plug to 10-32 Male Right Angle Cable 150 cm Length Using RG196 Coax PE3W00597-150CM](#)



SMC Plug to 10-32 Male Right Angle Cable
150 cm Length Using RG196 Coax

RF Cable Assemblies Technical Data Sheet

PE3W00597-150CM

How to Order

Part Number Configuration:

PE3W00597

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W00597-12 = 12 inches long cable
PE3W00597-100cm = 100 cm long cable

SMC Plug to 10-32 Male Right Angle Cable 150 cm Length Using RG196 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Plug to 10-32 Male Right Angle Cable 150 cm Length Using RG196 Coax PE3W00597-150CM](https://www.pasternack.com/smc-plug-10-32-male-right-angle-cable-assembly-pe3w00597-150cm-p.aspx)

URL: <https://www.pasternack.com/smc-plug-10-32-male-rg196au-cable-assembly-pe3w00597-150cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W00597-150CM CAD Drawing

SMC Plug to 10-32 Male Right Angle Cable 150 cm Length Using RG196 Coax



10-32 MALE
RIGHT ANGLE

STANDARD TOLERANCES

- .X ±0.2
- .XX ±0.01
- .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

PE PASTERNAK
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE
PE3W00597

CAGE CODE 53919

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

CAD FILE 02/07/18

SCALE N/A

SIZE A

GF0006