

MHV Female to MHV Female Cable Using RG174 Coax





PE3W00564

Configuration

- Connector 1: MHV Female
- Connector 2: MHV Female
- Cable Type: RG174
- Coax Flex Type: Flexible

Features

- 66% Phase Velocity
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W00564 MHV female to MHV female cable using RG174 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MHV to MHV cable assembly has a female to female gender configuration with 50 ohm flexible RG174 coax.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.091 lbs [41.28 g]

Cable

Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE (LD)
Number of Shields	1

MHV Female to MHV Female Cable Using RG174 Coax

**PE3W00564**

Shield Layer 1
Jacket Material
Jacket Diameter

Tinned Copper Braid
PVC, Black
0.1 in [2.54 mm]

Connectors

Description	Connector 1	Connector 2
Type	MHV Female	MHV Female
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Body Material and Plating	Brass, Nickel	Brass, Nickel

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

MHV Female to MHV Female Cable Using RG174 Coax

**PE3W00564****Typical Performance Data****How to Order**

Part Number Configuration:



Example: PE3W00564-12 = 12 inches long cable
PE3W00564-100cm = 100 cm long cable

MHV Female to MHV Female Cable Using RG174 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MHV Female to MHV Female Cable Using RG174 Coax PE3W00564](#)

URL: <https://www.pasternack.com/mhv-female-to-mhv-female-cable-using-rg174-pe3w00564-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W00564 CAD Drawing

MHV Female to MHV Female Cable Using RG174 Coax

