PASTERNACK®
THE ENGINEER'S RF SOURCE



# 75 Ohm F Male Right Angle Connector Crimp/ Solder Attachment for RG6-CATV

## RF Connectors Technical Data Sheet PE44320

## Configuration

- F Male Connector
- 75 Ohms
- Right Angle Body Geometry
- RG6-CATV Interface Type
- Crimp/Solder Attachment
- 7/16 inch Hex

## Features

- Max. Operating Frequency 2 GHz
- Excellent VSWR of 1.23:1
- Gold Plated Brass Contact

## Applications

- General Purpose Test
- Custom Cable Assemblies

### Description

Pasternack's PE44320 75 ohm type F male right angle connector crimp/solder attachment for RG6-CATV is part of our full line of RF components available for same-day shipping. Our type F male connector operates up to a maximum frequency of 2 GHz and offers excellent VSWR of 1.23:1. Its right angle body geometry allows for easier connections in tight spaces.

Our 75 ohm type F male right angle connector PE44320 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable connector assemblies for you and ship same-day.

### Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|---|---|---|---|---|
| Frequency Range | DC | | 2 | GHz |
| VSWR | | | 1.23:1 | |

### Mechanical Specifications

**Size**

| | |
|---|---|
| Length | 0.87 in [22.1 mm] |
| Width/Dia. | 0.438 in [11.13 mm] |
| Height | 1 in [25.4 mm] |
| Weight | 0.046 lbs [20.87 g] |
| Mating Torque | 12 to 15 in-lbs [1.36 to 1.70 Nm] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 75 Ohm F Male Right Angle Connector Crimp/Solder Attachment for RG6-CATV PE44320

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623
**Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451
Sales@Pasternack.com • Techsupport@Pasternack.com

© 2016 Pasternack Enterprises All Rights Reserved



# 75 Ohm F Male Right Angle Connector Crimp/ Solder Attachment for RG6-CATV



### Material Specifications

| Description | Material | Plating |
|---|---|---|
| Contact | Brass | Gold |
| Insulation | PTFE | |
| Body | Brass | Nickel |
| Coupling Nut | Brass | Nickel |

### Environmental Specifications

**Temperature**

Operating Range -65 to +165 deg C

### Compliance Certifications (see product page for current document)

### Plotted and Other Data

Notes:

75 Ohm F Male Right Angle Connector Crimp/Solder Attachment for RG6-CATV from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in “SEARCH” on website) to obtain additional part information including price, inventory and certifications: 75 Ohm F Male Right Angle Connector Crimp/Solder Attachment for RG6-CATV PE44320

URL: https://www.pasternack.com/f-male-standard-rg6-catv-connector-pe44320-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623
**Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451
Sales@Pasternack.com • Techsupport@Pasternack.com

© 2016 Pasternack Enterprises All Rights Reserved

# PE44320 CAD Drawing

75 Ohm F Male Right Angle Connector Crimp/Solder Attachment for RG6-CATV




STRIPPING DIMENSIONS

ASSEMBLY PROCEDURES

1. STRIP CABLE AS SHOWN. SLIDE FERRULE OVER CABLE.
2. INSTALL CABLE INTO BODY OF CONNECTOR AND SOFT SOLDER CENTER CONDUCTOR IN PLACE.
3. CRIMP FERRULE & PRESS CAP DOWN.

CRIMP SIZE REQUIRED

FERRULE: .314" HEX CRIMP TOOL

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. FITS MIL-C-17 AND EQUIVALENT CABLES.

| CAD FILE | 040811 | SCALE N/A | SIZE A | 2233 |
|---|---|---|---|---|

DWG TITLE **PE44320**

**FSCM NO. 53919**

PASTERNACK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
**Phone:** (949) 261-1920 | **Fax:** (949) 261-7451
**Website:** www.pasternack.com | **E-Mail:** sales@pasternack.com

© 2016 Pasternack Enterprises All Rights Reserved

PASTERNACK®
THE ENGINEER'S RF SOURCE



# 75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV

## RF Connectors Technical Data Sheet PE44452

## Configuration

- F Male Connector
- MIL-STD-348A
- 75 Ohms
- Straight Body Geometry
- RG6-CATV Interface Type
- Crimp/Solder Attachment
- 7/16 inch Hex

## Features

- Silver Plated Brass Contact
- 70 µin minimum contact plating

## Applications

- General Purpose Test
- Custom Cable Assemblies
- CATV

### Description

Pasternack's PE44452 75 ohm type F male connector with crimp/solder attachment for RG6-CATV is part of our full line of RF components available for same-day shipping.

Our 75 ohm type F male connector PE44452 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

### Mechanical Specifications

**Size**

| | |
|---|---|
| Length | 0.768 in [19.51 mm] |
| Width/Dia. | 0.438 in [11.13 mm] |
| Weight | 0.018 lbs [8.16 g] |
| Mating Torque | 12 to 15 in-lbs [1.36 to 1.70 Nm] |

**Material Specifications**

| Description | Material | Plating |
|---|---|---|
| Contact | Brass | Silver<br>70 µin minimum |
| Body | Brass | Nickel<br>100 µin minimum |
| Coupling Nut | Brass | Nickel<br>100 µin minimum |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV PE44452

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623
**Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451
Sales@Pasternack.com • Techsupport@Pasternack.com

© 2016 Pasternack Enterprises All Rights Reserved

PASTERNACK®
THE ENGINEER'S RF SOURCE

# 75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV



## RF Connectors Technical Data Sheet PE44452

**Compliance Certifications** (see product page for current document)

**Plotted and Other Data**

Notes:

75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV PE44452

URL: https://www.pasternack.com/f-male-standard-rg6-catv-connector-pe44452-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623
**Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451
Sales@Pasternack.com • Techsupport@Pasternack.com


© 2016 Pasternack Enterprises All Rights Reserved


© 2016 Pasternack Enterprises All Rights Reserved



# PE44452 CAD Drawing

75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV




STRIPPING DIMENSIONS

ASSEMBLY PROCEDURES

STRIP CABLE AS SHOWN, PUSH CABLE INTO CONNECTOR UNTIL DIELECTRIC IS FLUSH WITH BODY SHOULDER. THEN CRIMP.

CRIMP SIZE REQUIRED

FERRULE: .314" HEX CRIMP TOOL

PASTERNACK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
**Phone:** (949) 261-1920 | **Fax:** (949) 261-7451
**Website:** www.pasternack.com | **E-Mail:** sales@pasternack.com

DWG TITLE

**PE44452**

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. FITS MIL-C-17 AND EQUIVALENT CABLES.

| FSCM NO. 53919 | CAD FILE 062206 | SCALE N/A | SIZE A | 127 |
|---|---|---|---|---|

PASTERNACK®
www.pasternack.com



# 75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket

## TECHNICAL DATA SHEET RG6-CATV

75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket

### Configuration

| | |
|---|---|
| Inner Conductor Material and Plating | Copper |
| Dielectric Type | PE (F) |
| Shield Materials | Aluminum Foil, Aluminum Braid |
| Jacket Material and Color | PVC (NC), Black |

### Electrical Specifications

| | |
|---|---|
| Impedance, Ohms | 75 |
| Velocity of Propagation, % | 85 |
| Maximum Operating Frequency, GHz | 3 |
| RF Shielding, dB | 70 |
| Capacitance, pF/ft [pF/m] | 16.2 [53.15] |

### Electrical Specifications by Frequency

**Frequency 1**

| | |
|---|---|
| Frequency, MHz | 5 |
| Attenuation, dB/100ft [dB/100m] | 0.58 [1.9] |

**Frequency 2**

| | |
|---|---|
| Frequency, MHz | 250 |
| Attenuation, dB/100ft [dB/100m] | 3.3 [10.83] |

**Frequency 3**

| | |
|---|---|
| Frequency, MHz | 550 |
| Attenuation, dB/100ft [dB/100m] | 4.9 [16.08] |

**Frequency 4**

| | |
|---|---|
| Frequency, MHz | 1000 |
| Attenuation, dB/100ft [dB/100m] | 6.55 [21.49] |

**Frequency 5**

| | |
|---|---|
| Frequency, GHz | 1.45 |
| Attenuation, dB/100ft [dB/100m] | 7.9 [25.92] |

**Frequency 6**

| | |
|---|---|
| Frequency, GHz | 1.75 |
| Attenuation, dB/100ft [dB/100m] | 8.75 [28.71] |

**Frequency 7**

| | |
|---|---|
| Frequency, GHz | 2.15 |

Click the following link (or enter part number in “SEARCH” on website) to obtain additional part information including price, inventory and certifications: 75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket RG6-CATV

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623
**Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451
Sales@Pasternack.com • Techsupport@Pasternack.com

© 2013 Pasternack Enterprises All Rights Reserved

PASTERNACK®
www.pasternack.com



# 75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket

## TECHNICAL DATA SHEET RG6-CATV

### Mechanical Specifications

**Temperature**

| | |
|---|---|
| Operating Range, deg C | -40 to +80 |

**Inner Conductor**

| | |
|---|---|
| Number of Strands | 1 |
| Material | Copper |
| Diameter, in [mm] | 0.04 [1.02] |

**Dielectric:**

| | |
|---|---|
| Type | PE (F) |
| Diameter, in [mm] | 0.18 [4.57] |

**Shield:**

| | |
|---|---|
| Number of | 3 |
| Material 1 | Aluminum Foil |
| Material 2 | Aluminum Braid |
| Material 3 | Aluminum Foil |
| Diameter, in [mm] | 0.22 [5.59] |

**Jacket:**

| | |
|---|---|
| Material | PVC (NC) |
| Diameter, in [mm] | 0.275 [6.99] |
| Color | Black |
| One Time Minimum Bend Radius, in [mm] | 1.37 [34.8] |
| Weight, lbs/ft [Kg/m] | 0.033 [0.05] |

### Compliance Certifications (visit www.Pasternack.com for current document)

| | |
|---|---|
| RoHS Compliant | Yes |

### Plotted and Other Data

| | |
|---|---|
| Notes: | Values at 25 °C, sea level |

75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in “SEARCH” on website) to obtain additional part information including price, inventory and certifications: 75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket RG6-CATV

URL: http://www.pasternack.com/flexible-0.275-rg6-catv-75-ohm-coax-cable-pvc-jacket-rg6-catv-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623
**Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451
Sales@Pasternack.com • Techsupport@Pasternack.com

© 2013 Pasternack Enterprises All Rights Reserved

# RG6-CATV CAD Drawing

75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket




NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE: RG6-CATV

| REV. B | FSCM NO. 53919 | CAD FILE 021411-B | SCALE N/A | SIZE A | 147 |
|---|---|---|---|---|---|

PASTERNACK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
**Phone:** (949) 261-1920 | **Fax:** (949) 261-7451
**Website:** www.pasternack.com | **E-Mail:** sales@pasternack.com

© 2013 Pasternack Enterprises All Rights Reserved