

2.92mm Female to 2.92mm Male Cable Using PE-047SR Coax, LF Solder




PE3W03741LF

Configuration

- Connector 1: 2.92mm Female
- Connector 2: 2.92mm Male
- Cable Type: PE-047SR
- Coax Flex Type: Semi-Rigid

Features

- Max Frequency 40 GHz



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W03741LF 2.92mm female to 2.92mm male cable using PE-047SR coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack 2.92mm to 2.92mm cable assembly has a female to male gender configuration with 50 ohm semi-rigid PE-047SR coax. The PE3W03741LF 2.92mm female to 2.92mm male cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.4:1	

Specifications by Frequency

2.92mm Female to 2.92mm Male Cable Using PE-047SR Coax, LF Solder



PE3W03741LF

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	1000	2000	4500	9000	20000	MHz	
PE3W03741LF	Custom Lengths Available	Insertion Loss (Typ.)	0.4 1.32	0.5 1.65	0.75 2.47	1.2 3.94	1.9 6.24	dB/ft dB/m	
PE3W03741LF-3	3 inch	Insertion Loss (Typ.)	0.46	0.49	0.55	0.66	0.84	dB	0.015
PE3W03741LF-6	6 inch	Insertion Loss (Typ.)	0.56	0.61	0.74	0.96	1.31	dB	0.016
PE3W03741LF-12	12 inch	Insertion Loss (Typ.)	0.76	0.86	1.11	1.56	2.26	dB	0.018
PE3W03741LF-18	18 inch	Insertion Loss (Typ.)	0.96	1.11	1.49	2.16	3.21	dB	0.021
PE3W03741LF-60	60 inch	Insertion Loss (Typ.)	2.36	2.86	4.11	6.36	9.86	dB	0.035

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.26 dB
Loss due to Connector 2: 0.1 dB
Base Weight: 0.018 pounds
Additional Weight per Inch: 0.00034 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
Weight 0.018 lbs [8.16 g]

Cable

Cable Type	PE-047SR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Copper
Repeated Minimum Bend Radius	0.05 in [1.27 mm]

2.92mm Female to 2.92mm Male Cable Using PE-047SR Coax, LF Solder



PE3W03741LF

Connectors

Description	Connector 1	Connector 2
Type	2.92mm Female	2.92mm Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold over Nickel
Contact Plating Specification	50 μ in minimum	50 μ in minimum
Dielectric Type	PEI	PEI
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Body Plating Specification	SAE-AMS-2700	SAE-AMS-2700
Coupling Nut Material and Plating		Passivated Stainless Steel
Coupling Nut Plating Specification		SAE-AMS-2700
Hex Size		5/16 inch
Torque		8 in-lbs 0.9 Nm

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.92mm Female to 2.92mm Male Cable Using PE-047SR Coax, LF Solder




PE3W03741LF

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3W03741LF-12 = 12 inches long cable
PE3W03741LF-100cm = 100 cm long cable

2.92mm Female to 2.92mm Male Cable Using PE-047SR Coax, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Female to 2.92mm Male Cable Using PE-047SR Coax, LF Solder PE3W03741LF](#)

URL: <https://www.pasternack.com/2.92mm-female-to-2.92mm-male-cable-using-pe-047sr-lf-solder-pe3w03741lf-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W03741LF CAD Drawing

2.92mm Female to 2.92mm Male Cable Using PE-047SR Coax, LF Solder

