



## SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax

### TECHNICAL DATA SHEET


PE3W05921

#### Configuration

- Connector 1: SMP Female Right Angle
- Connector 2: MMCX Plug
- Cable Type: PE-SR047FL
- Coax Flex Type: Formable

#### Features

- Max Frequency 6 GHz
- 69.5% Phase Velocity



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W05921 SMP female right angle to MMCX plug cable using PE-SR047FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack SMP to MMCX cable assembly has a female to plug gender configuration with 50 ohm formable PE-SR047FL coax. The PE3W05921 SMP female to MMCX plug cable assembly operates to 6 GHz. The right angle SMP interface on the PE-SR047FL cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax PE3W05921](#)



## SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax

### TECHNICAL DATA SHEET

**PE3W05921**

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Velocity of Propagation		69.5		%
Capacitance		32 [104.99]		pF/ft [pF/m]
DC Resistance Inner Conductor		207 [679.13]		$\Omega$ /1000ft [ $\Omega$ /Km]
DC Resistance Outer Conductor		8 [26.25]		$\Omega$ /1000ft [ $\Omega$ /Km]

#### Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency	500	1000	2000	4000	6000	
PE3W05921	Custom Lengths Available	Insertion Loss (Typ.)	0.25	0.36	0.46	0.66	0.87	dB/ft	
			0.83	1.19	1.51	2.17	2.86	dB/m	
PE3W05921-6	6 inch	Insertion Loss (Typ.)	0.43	0.48	0.53	0.63	0.74	dB	0.01
PE3W05921-9	9 inch	Insertion Loss (Typ.)	0.49	0.57	0.65	0.8	0.96	dB	0.011
PE3W05921-12	12 inch	Insertion Loss (Typ.)	0.55	0.66	0.76	0.96	1.17	dB	0.011
PE3W05921-24	24 inch	Insertion Loss (Typ.)	0.8	1.02	1.22	1.62	2.04	dB	0.014
PE3W05921-36	36 inch	Insertion Loss (Typ.)	1.05	1.38	1.68	2.28	2.91	dB	0.017

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.2 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.011 pounds
Additional Weight per Inch:	0.00025 pounds

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

#### Mechanical Specifications

##### Cable Assembly

Weight 0.011 lbs [4.99 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax PE3W05921](#)



SMP Female Right Angle to MMCX Plug  
Cable Using PE-SR047FL Coax

**TECHNICAL DATA SHEET**

**PE3W05921**

**Cable**

Cable Type	PE-SR047FL
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor Material and Plating	Tinned Copper Braid

**Connectors**

Description	Connector 1	Connector 2
Type	SMP Female Right Angle Push-On	MMCX Plug Push-On
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Specification	MIL-DTL-45204	
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Beryllium Copper, Gold	
Body Material and Plating	Beryllium Copper, Gold	Brass, Gold
Body Plating Specification	MIL-DTL-45204	

**Environmental Specifications**

**Temperature**

Operating Range -40 to +100 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax PE3W05921](#)



## SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax

### TECHNICAL DATA SHEET

**PE3W05921**

#### How to Order

Part Number Configuration:

**PE3W05921**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3W05921-12 = 12 inches long cable  
PE3W05921-100cm = 100 cm long cable

SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax PE3W05921](#)

URL: <https://www.pasternack.com/smp-female-mmcx-plug-pe-sr047fl-cable-assembly-pe3w05921-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.


# PE3W05921 CAD Drawing

SMP Female Right Angle to MMCX Plug Cable Using PE-SR047FL Coax

F E D C B A

1 2 3 4 5 6

REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV	DESCRIPTION		
	A	INITIAL RELEASE	HBAKKE	AGANWANI



**NOTES:**

1. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.

	INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE NONE SHEET 1 OF 1	
	Website: www.Pasternack.com Phone: 1.866.727.8376   1.949.261.1920	
DESCRIPTION SMP FEMALE RIGHT ANGLE TO MMCX PLUG CABLE USING PE-SR047FL COAX		
UNLESS OTHERWISE SPECIFIED LENGTH DIMENSIONS ARE IN INCHES DIMENSIONS IN PARENS ARE IN MILLIMETERS	TOLERANCES: .X = ±.2 [5] .XX = ±.02 [0.5] .XXX = ±.005 [0.13]	FRACTIONS ± 1/32 ANGLES ± 1°
CABLE LENGTH TOLERANCES: >12 [305] ≤ 512 [1298] = ±.125 / -0 >512 [1298] ≤ 1200 [3048] = ±.25 / -0 >60 [1524] ≤ 120 [3048] = ±.102 / -0 >120 [3048] ≤ 300 [7620] = ±.6 [152] / -0 >300 [7620] = ±.5% / -0		
ALL DIMENSIONS ARE FOR REFERENCE ONLY UNLESS OTHERWISE NOTED DIMENSIONS ON CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.