

## TNC Male to SMA Male Right Angle Cable 200 cm Length Using LMR-200 Coax




### PE3W07265-200CM

#### Configuration

- Connector 1: TNC Male
- Connector 2: SMA Male Right Angle
- Cable Type: LMR-200
- Coax Flex Type: Flexible

#### Features

- Max Frequency 3 GHz
- Shielding Effectivity > 90 dB
- 83% Phase Velocity
- Double Shielded
- PE Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W07265-200CM TNC male to SMA male right angle 200 cm cable using LMR-200 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to SMA cable assembly has a male to male gender configuration with 50 ohm flexible LMR-200 coax. The PE3W07265-200CM TNC male to SMA male cable assembly operates to 3 GHz. The right angle SMA interface on the LMR-200 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.5:1	
Velocity of Propagation		83		%
RF Shielding	90			dB
Group Delay		1.22 [4]		ns/ft [ns/m]
Capacitance		24.5 [80.38]		pF/ft [pF/m]
Inductance		0.061 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		5.36 [17.59]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ohms/1000ft [Ohms/Km]

TNC Male to SMA Male Right Angle Cable  
200 cm Length Using LMR-200 Coax



**PE3W07265-200CM**

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Jacket Spark			3,000	Vrms

**Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	3	GHz
Insertion Loss (Max.)	0.63	0.78	0.99	1.41	1.5	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax use in this assembly. The Insertion Loss includes an estimated insertion loss of 0.3dB of connector Loss

**Mechanical Specifications**

**Cable Assembly**

Weight 0.34 lbs [154.22 g]

**Cable**

Cable Type LMR-200  
 Impedance 50 Ohms  
 Inner Conductor Type Solid  
 Inner Conductor Material and Plating Copper  
 Dielectric Type PE (F)  
 Number of Shields 2  
 Shield Layer 1 Aluminum Tape  
 Shield Layer 2 Tinned Copper Braid  
 Jacket Material PE, Black  
 Jacket Diameter 0.195 in [4.95 mm]  
 One Time Minimum Bend Radius 0.5 in [12.7 mm]  
 Repeated Minimum Bend Radius 2 in [50.8 mm]  
 Bending Moment 0.2 lbs-ft [0.27 N-m]  
 Flat Plate Crush 15 lbs/in [0.27 Kg/mm]  
 Tensile Strength 40 lbs [18.14 Kg]

TNC Male to SMA Male Right Angle Cable  
200 cm Length Using LMR-200 Coax



**PE3W07265-200CM**

**Connectors**

Description	Connector 1	Connector 2
Type	TNC Male	SMA Male Right Angle
Specification	MIL-STD-348	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Beryllium Copper, Gold	Brass, Gold
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Gold
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Gold
Hex Size	5/8 Inch	

**Environmental Specifications**

Operating Range Temperature -40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

TNC Male to SMA Male Right Angle Cable  
200 cm Length Using LMR-200 Coax



**PE3W07265-200CM**

**Typical Performance Data**

**How to Order**

Part Number Configuration:

**PE3W07265**

**- xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3W07265-12 = 12 inches long cable  
PE3W07265-100cm = 100 cm long cable

TNC Male to SMA Male Right Angle Cable 200 cm Length Using LMR-200 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Right Angle Cable 200 cm Length Using LMR-200 Coax PE3W07265-200CM](#)

URL: <https://www.pasternack.com/tnc-male-sma-male-lmr200-cable-assembly-pe3w07265-200cm-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3W07265-200CM CAD Drawing

TNC Male to SMA Male Right Angle Cable 200 cm Length Using LMR-200 Coax



**NOTES:**

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED, LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-04 A122

<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN PAREMILLIMETERS</p> <p>TOLERANCES:          .X = ±.2 [5]    FRACTIONS ± 1/32          .XX = ±.02 [0.5]    ANGLES ± 1°          .XXX = ±.005 [0.13]</p> <p>CABLE LENGTH TOLERANCES:          &gt;12 [305] ≤ 60 [1524] = +1 [25] / -0          &gt;60 [1524] ≤ 120 [3048] = +4 [102] / -0          &gt;120 [3048] ≤ 600 [15240] = +5 [127] / -0          &gt;600 [15240] ≤ 3000 [76200] = +5 [127] / -0</p> <p>ALL DIMENSIONS ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED. DIMENSIONS ON CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.</p>		<p><b>PE PASTERNAK</b> an INFINITTE brand</p> <p>Website: <a href="http://www.Pasternack.com">www.Pasternack.com</a>          Phone: 1.866.727.8376   1.949.261.1920</p>	
<p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p> <p>SCALE NONE</p> <p>SHEET 1 OF 1</p>		<p>DESCRIPTION  <b>TNC MALE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-200 COAX</b></p>	
REV	B	ITEM NO.	PE3W07265
REV	1	DESCRIPTION	TNC MALE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-200 COAX
REV	2	DESCRIPTION	TNC MALE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-200 COAX
REV	3	DESCRIPTION	TNC MALE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-200 COAX
REV	4	DESCRIPTION	TNC MALE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-200 COAX
REV	5	DESCRIPTION	TNC MALE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-200 COAX
REV	6	DESCRIPTION	TNC MALE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-200 COAX

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
B	B	ECO-14247	03/26/2025	AKRESOWSKI	SRAUTUS