



7/16 DIN Male Connector Crimp/Solder Attachment for PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch

## RF Connectors Technical Data Sheet

**PE44536**

### Configuration

- 7/16 DIN Male Connector
- IEC 61169-4
- 50 Ohms
- Straight Body Geometry
- PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch Interface Type
- Crimp/Solder Attachment
- 1 1/4 inch Hex

### Features

- Max. Operating Frequency 3 GHz
- Excellent VSWR of 1.1:1
- Silver Plated Brass Contact
- 5 µm minimum contact plating

### Applications

- General Purpose Test
- Custom Cable Assemblies

### Description

Pasternack's PE44536 7/16 DIN male connector with crimp/solder attachment for PE-C195, PE-P195, RG58, RG141, RG303, LMR-195 and 0.195 inch is part of our full line of RF components available for same-day shipping. Our 7/16 DIN male connector operates up to a maximum frequency of 3 GHz and offers excellent VSWR of 1.1:1.

Our 7/16 DIN male connector PE44536 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

### Electrical Specifications

| Description                          | Minimum | Typical | Maximum | Units |
|--------------------------------------|---------|---------|---------|-------|
| Frequency Range                      | DC      |         | 3       | GHz   |
| VSWR                                 |         |         | 1.1:1   |       |
| Insertion Loss                       |         |         | 0.1     | dB    |
| Operating Voltage (DC)               |         |         | 2,700   | Vdc   |
| Dielectric Withstanding Voltage (DC) |         |         | 4,000   | Vdc   |
| Inner Conductor DC Resistance        |         |         | 0.8     | mOhms |
| Outer Conductor DC Resistance        |         |         | 0.2     | mOhms |
| Insulation Resistance                | 10,000  |         |         | MOhms |

### Mechanical Specifications

#### Size

|            |                    |
|------------|--------------------|
| Length     | 1.99 in [50.55 mm] |
| Width/Dia. | 1.25 in [31.75 mm] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male Connector Crimp/Solder Attachment for PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch PE44536](#)



7/16 DIN Male Connector Crimp/Solder Attachment for PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch

## RF Connectors Technical Data Sheet

**PE44536**

Weight 0.11 lbs [49.9 g]  
Mating Torque 221 to 265 in-lbs [24.97 to 29.95 Nm]

### Material Specifications

| Description  | Material | Plating                   |
|--------------|----------|---------------------------|
| Contact      | Brass    | Silver<br>5 µm minimum    |
| Insulation   | PTFE     |                           |
| Body         | Brass    | Tri-Metal<br>2 µm minimum |
| Coupling Nut | Brass    | Tri-Metal<br>2 µm minimum |

### Environmental Specifications

#### Temperature

Operating Range -40 to +85 deg C  
Shock IEC 60068-2-27  
Vibration IEC 60068-2-6-Fc  
Thermal Shock IEC 60068-2-14-Na

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male Connector Crimp/Solder Attachment for PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch PE44536](#)



7/16 DIN Male Connector Crimp/Solder Attachment for PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch

## RF Connectors Technical Data Sheet

**PE44536**

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

7/16 DIN Male Connector Crimp/Solder Attachment for PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male Connector Crimp/Solder Attachment for PE-C195, PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch PE44536](#)

URL: <https://www.pasternack.com/7-16-male-standard-pe-c195-0.195-connector-pe44536-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE44536 CAD Drawing

7/16 DIN Male Connector Crimp/Solder Attachment for PE-C195,  
PE-P195, RG58, RG141, RG303, LMR-195, 0.195 inch



CRIMP SIZE REQUIRED

CONTACT: SOLDER  
FERRULE: .213" HEX CRIMP TOOL

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].  
4. FITS MIL-C-17 AND EQUIVALENT CABLES.

DWG TITLE

PE44536

FSCM NO. 53919

CAD FILE 032213-D

SCALE N/A

SIZE A


2233

 **PASTERNAK®**  
THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623  
Phone: (949) 261-1920 | Fax: (949) 261-7451  
Website: www.pasternack.com | E-Mail: sales@pasternack.com

**NOTICE OF PROPRIETARY RIGHTS** THIS DOCUMENT CONTAINS CONFIDENTIAL TECHNICAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

| SYM | REVISION DESCRIPTION    | DFTM  | DATE    | APPD   | DATE    |
|-----|-------------------------|-------|---------|--------|---------|
| A   | RELEASED FOR PRODUCTION | N.N.N | 1/15/14 | J.D.B. | 1/15/14 |



**NOTES:**

- ASSEMBLED CONNECTOR INTERFACE IS DESIGNED IN ACCORDANCE WITH MIL-STD-348.
- MATERIAL:  
 BODY, CONTACT - BRASS PER ASTM B16, C36000 ALLOY, TEMPER H02  
 INSULATOR - TEFLON PER ASTM D1710, TYPE 1, GRADE 1, CLASS A  
 SHRINK SLEEVE - HEAT SHRINKABLE ATUM PER MIL-I-23053/4 (NOT SHOWN)  
 CRIMP SLEEVE - D.H.P. COPPER CDA, ALLOY #122, TEMPER HARD  
 GASKET - SILICONE RUBBER PER A-A-59588, 50-75 DUROMETER  
 LOCKING RING - PHOSPHOR BRONZE PER ASTM B139, C54400 ALLOY, TEMPER HD
- FINISH:  
 CONTACT - GOLD PLATE PER ASTM B488  
 CRIMP SLEEVE - SILVER PLATE PER ASTM B700  
 ALL OTHER METAL PARTS - ALBALOY PLATE

|                |  |                                                                                                                                                                                                                                      |  |                                                          |  |                         |  |              |  |              |  |             |  |       |  |
|----------------|--|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------|--|-------------------------|--|--------------|--|--------------|--|-------------|--|-------|--|
| MATL:          |  | UNLESS OTHERWISE SPECIFIED                                                                                                                                                                                                           |  | DFTM. N, N, N                                            |  | TIMES MICROWAVE SYSTEMS |  |              |  |              |  |             |  |       |  |
|                |  | ALL DIMENSIONS ARE IN INCHES<br>MACHINED SURFACES FINISH 63 RMS MAX.<br>REMOVE ALL BURRS .004 MAX. BREAK<br>MACHINE CORNERS .005 MAX. FILLET R.<br>TOLERANCES ON DECIMALS<br>. XX ± .01 . XXX ± .005<br>ANGLES ± 1° FRACTIONS ± 1/64 |  | DATE 1/15/14                                             |  |                         |  |              |  |              |  |             |  |       |  |
| CHKD. J, D, B. |  |                                                                                                                                                                                                                                      |  | TC-195-NMH-X<br>CONNECTOR ASSEMBLY<br>N Male for LMR-195 |  |                         |  |              |  |              |  |             |  |       |  |
| DATE 1/15/14   |  |                                                                                                                                                                                                                                      |  |                                                          |  |                         |  |              |  |              |  |             |  |       |  |
| APPD. J, D, B. |  |                                                                                                                                                                                                                                      |  |                                                          |  |                         |  |              |  |              |  |             |  |       |  |
| USED ON: _     |  |                                                                                                                                                                                                                                      |  | DATE 1/15/14                                             |  |                         |  |              |  |              |  |             |  |       |  |
| SCALE: NONE    |  | DWG. SIZE A                                                                                                                                                                                                                          |  | DO NOT SCALE DRAWING                                     |  | CODE IDENT 68999        |  | DATE 1/15/14 |  | SHEET 1 of 1 |  | SD3190-2880 |  | REV A |  |
|                |  |                                                                                                                                                                                                                                      |  |                                                          |  |                         |  |              |  |              |  |             |  |       |  |

# LMR®-195

## Flexible Low Loss Communications Coax

### Ideal for...

- Jumper Assemblies in Wireless Communications Systems
- Short Antenna Feeder runs
- Any application (e.g. WLL, GPS, LMR, WLAN, WISP, WiMax, SCADA, Mobile Antennas) requiring an easily routed, low loss RF cable
- Drop-in replacement for RG-58 and RG-142



• **LMR®** standard is a UV Resistant Polyethylene jacketed cable designed for 20-year service outdoor use. The bending and handling characteristics are significantly better than air-dielectric and corrugated hard-line cables.

• **LMR® - DB** is identical to standard LMR plus has the advantage of being watertight. The addition of waterproofing compound in and around the foil/braid insures continuous reliable service should the jacket be inadvertently damaged during installation or in the future.

• **LMR® - FR** is a non-halogen (non-toxic), low smoke, fire retardant cable designed for in-building runs that can be routed anywhere except air handling plenums. LMR-FR is UL/NEC & CSA rated 'CMR' and 'FT4' respectively, meets FAA FAR25 requirements and is MSHA-P for mining applications.

• **LMR® - FR-PVC** is a general-purpose indoor cable and has a UL/NEC & CSA rating of 'CMR' and 'FT4' respectively. It is less expensive than LMR-FR, however it emits toxic fumes (HCL) and greater smoke density when burned.

• **LMR® - PVC** is designed for low loss general-purpose applications and is somewhat more flexible than the standard polyethylene jacketed LMR.

• **LMR® - PVC-W** is a white-jacketed version of LMR-PVC for marine and other applications where color compatibility is desired.

• **LMR® - MA** is a flexible cable designed specifically for mobile antenna applications. It has a PVC jacket and un-bonded aluminum tape to facilitate end stripping with automated equipment.

• **Flexibility** and bendability are hallmarks of the LMR-195 cable design. The flexible outer conductor enables the tightest bend radius available for any cable of similar size and performance.

• **Low Loss** is another hallmark feature of LMR-195. Size for size LMR has the lowest loss of any flexible cable and comparable loss to semirigid hard-line cables.

• **RF Shielding** is 50 dB greater than typical single shielded coax (40 dB). The multi-ply bonded foil outer conductor is rated conservatively at > 90 dB (i.e. >180 dB between two adjacent cables).

• **Weatherability:** LMR-195 cables designed for outdoor exposure incorporate the best materials for UV resistance and have life expectancy in excess of 20 years.

• **Connectors:** A wide variety of connectors are available for LMR-195 cable, including all common interface types, reverse polarity, and a choice of solder or non-solder center pins. Most LMR connectors employ crimp outer attachment using standard hex crimp sizes.

• **Cable Assemblies:** All LMR-195 cable types are available as pre-terminated cable assemblies. Refer to the section on FlexTech for further details.

| Part Description |                          |        |       | Stock |
|------------------|--------------------------|--------|-------|-------|
| Part Number      | Application              | Jacket | Color | Code  |
| LMR-195          | Outdoor                  | PE     | Black | 54110 |
| LMR-195-DB       | Outdoor/Watertight       | PE     | Black | 54113 |
| LMR-195-FR       | Indoor/Outdoor Riser CMR | FRPE   | Black | 54111 |
| LMR-195-FR-W     | Indoor/Outdoor Riser CMR | FRPE   | White | 54158 |
| LMR-195-FR-PVC   | Indoor/Outdoor Riser CMR | FRPVC  | Black | 54105 |
| LMR-195-MA       | Mobile Antennas          | PVC    | Black | 54210 |
| LMR-195-PVC      | General Purpose          | PVC    | Black | 54215 |
| LMR-195-PVC-W    | General Purpose          | PVC    | White | 54199 |

| Construction Specifications |                   |       |        |
|-----------------------------|-------------------|-------|--------|
| Description                 | Material          | In.   | (mm)   |
| Inner Conductor             | Solid BC          | 0.037 | (0.94) |
| Dielectric                  | Foam PE           | 0.110 | (2.79) |
| Outer Conductor             | Aluminum Tape     | 0.116 | (2.95) |
| Overall Braid               | Tinned Copper     | 0.139 | (3.53) |
| Jacket                      | (see table above) | 0.195 | (4.95) |

### Mechanical Specifications

| Performance Property      | Units          | US    | (metric) |
|---------------------------|----------------|-------|----------|
| Bend Radius: installation | in. (mm)       | 0.5   | (12.7)   |
| Bend Radius: repeated     | in. (mm)       | 2.0   | (50.8)   |
| Bending Moment            | ft-lb (N-m)    | 0.2   | (0.27)   |
| Weight                    | lb/ft (kg/m)   | 0.021 | (0.03)   |
| Tensile Strength          | lb (kg)        | 40    | (18.2)   |
| Flat Plate Crush          | lb/in. (kg/mm) | 15    | (0.27)   |

### Environmental Specifications

| Performance Property           | °F       | °C      |
|--------------------------------|----------|---------|
| Installation Temperature Range | -40/+185 | -40/+85 |
| Storage Temperature Range      | -94/+185 | -70/+85 |
| Operating Temperature Range    | -40/+185 | -40/+85 |

### Electrical Specifications

| Performance Property    | Units             | US    | (metric) |
|-------------------------|-------------------|-------|----------|
| Velocity of Propagation | %                 | 76    |          |
| Dielectric Constant     | NA                | 1.56  |          |
| Time Delay              | nS/ft (nS/m)      | 1.27  | (4.17)   |
| Impedance               | ohms              | 50    |          |
| Capacitance             | pF/ft (pF/m)      | 25.4  | (83.3)   |
| Inductance              | uH/ft (uH/m)      | 0.064 | (0.21)   |
| Shielding Effectiveness | dB                | >90   |          |
| DC Resistance           |                   |       |          |
| Inner Conductor         | ohms/1000ft (/km) | 7.6   | (24.9)   |
| Outer Conductor         | ohms/1000ft (/km) | 4.9   | (16.1)   |
| Voltage Withstand       | Volts DC          | 1000  |          |
| Jacket Spark            | Volts RMS         | 3000  |          |
| Peak Power              | kW                | 2.5   |          |

### Attenuation vs. Frequency (typical)



| Frequency (MHz)       | 30   | 50   | 150  | 220  | 450  | 900  | 1500 | 1800 | 2000 | 2500 | 5800 |
|-----------------------|------|------|------|------|------|------|------|------|------|------|------|
| Attenuation dB/100 ft | 2.0  | 2.5  | 4.4  | 5.4  | 7.8  | 11.1 | 14.5 | 16.0 | 16.9 | 19.0 | 29.9 |
| Attenuation dB/100 m  | 6.5  | 8.4  | 14.6 | 17.7 | 25.5 | 36.5 | 47.7 | 52.5 | 55.4 | 62.4 | 98.1 |
| Avg. Power kW         | 0.89 | 0.68 | 0.39 | 0.32 | 0.22 | 0.16 | 0.12 | 0.11 | 0.10 | 0.09 | 0.06 |

Calculate Attenuation =  $(0.356859) \cdot \sqrt{\text{FMHz}} + (0.000470) \cdot \text{FMHz}$  (interactive calculator available at [http://www.timesmicrowave.com/cable\\_calculators](http://www.timesmicrowave.com/cable_calculators))  
**Attenuation:** VSWR=1.0 ; Ambient = +25°C (77°F) **Power:** VSWR=1.0; Ambient = +40°C; Inner Conductor = 100°C (212°F);  
 Sea Level; dry air; atmospheric pressure; no solar loading



TC-195-NM



TC-195-SM



TC-195-NM-RA-D



TC-195-TM

## Connectors

| Interface | Description   | Part Number     | Stock Code | VSWR**<br>Freq. (GHz) | Coupling<br>Nut | Inner<br>Contact<br>Attach | Outer<br>Contact<br>Attach | Finish*<br>Body /Pin | Length<br>in (mm) | Width<br>in (mm) | Weight<br>lb (g) |
|-----------|---------------|-----------------|------------|-----------------------|-----------------|----------------------------|----------------------------|----------------------|-------------------|------------------|------------------|
| N male    | Straight Plug | TC-195-NM       | 3190-1555  | <1.25:1 (2.5)         | Knurl           | Solder                     | Crimp                      | S/G                  | 1.5 (38.1)        | 0.75 (19.1)      | 0.073 (33.1)     |
| N male    | Right Angle   | TC-195-NMH-RA-D | 3190-2425  | <1.35:1 (6)           | Hex/Knurl       | Solder                     | Crimp                      | A/G                  | 1.3 (32.1)        | 1.19 (30.1)      | 0.083 (37.5)     |
| SMA male  | Straight Plug | TC-195-SM       | 3190-1553  | <1.25:1 (2.5)         | Hex             | Solder                     | Crimp                      | SS/G                 | 1.0 (25.4)        | 0.32 (8.1)       | 0.015 (6.8)      |
| TNC male  | Straight Plug | TC-195-TM       | 3190-1554  | <1.25:1 (2.5)         | Knurl           | Solder                     | Crimp                      | S/G                  | 1.4 (35.6)        | 0.59 (15.0)      | 0.045 (20.4)     |

\* Finish metals: N=Nickel, S=Silver, G=Gold, SS=Stainless Steel, A=Alloy \*\*VSWR spec based on 3 foot cable with a connector pair

## Install Tools

| Type              | Part Number        | Stock Code | Description                                        |
|-------------------|--------------------|------------|----------------------------------------------------|
| Crimp Tool        | CT-240/200/195/100 | 3190-667   | Crimp tool for LMR-100,195, 200 and 240 connectors |
| Cutting Tool      | CCT-01             | 3190-1544  | Cable end flush cut tool                           |
| Deburr Tool       | DBT-U              | 3192-001   | Removes center conductor rough edges               |
| Replacement Blade | RB-01              | 3190-1609  | Replacement blade for cutting tool                 |



CT-240/200/195/100



DBT-U



CCT-01