



2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3W08574-12

Configuration

- Connector 1: 2.4mm Male
- Connector 2: SMA Male
- Cable Type: RG405

Features

- Max Frequency 26.5 GHz
- Shielding Effectivity > -110 dB
- 69.5% Phase Velocity
- 500 Mating Cycles

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W08574-12 2.4mm male to SMA male 12 inch cable using RG405 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack 2.4mm to SMA cable assembly has a male to male gender configuration with 50 ohm semi-rigid RG405 coax. The PE3W08574-12 2.4mm male to SMA male cable assembly operates to 26.5 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax PE3W08574-12](#)



2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3W08574-12

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		26.5	GHz
VSWR			1.28:1	
Velocity of Propagation		69.5		%
RF Shielding	-110			dB
Capacitance		29.4 [96.46]		pF/ft [pF/m]
Dielectric Withstanding Voltage (AC)			1,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	26.5	GHz
Insertion Loss (Max.)	0.3	0.4	0.62	0.98	1.88	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss is estimated as $0.04 \cdot \sqrt{\text{FGHz}}$ dB per 2.4mm male connector and $0.04 \cdot \sqrt{\text{FGHz}}$ dB per SMA male connector.

Mechanical Specifications

Cable Assembly

Length* 12 in [304.8 mm]

Cable

Cable Type RG405
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper Clad Steel, Silver
 Dielectric Type PTFE
 Number of Shields 1
 Outer Conductor Material and Plating Copper
 Repeated Minimum Bend Radius 0.05 in [1.27 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax PE3W08574-12](#)



2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3W08574-12

Connectors

Description	Connector 1	Connector 2
Type	2.4mm Male	SMA Male
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	500
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification	50 µin minimum	ASTM-B488
Dielectric Type	PEI	PTFE
Outer Conductor Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Outer Conductor Plating Specification	50 µin minimum	ASTM-B488
Body Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Body Plating Specification	50 µin minimum	ASTM-B488
Coupling Nut Material and Plating	Passivated Stainless Steel	Steel
Coupling Nut Plating Specification	ASTM-A582	
Hex Size	5/16 inch	
Torque	8 in-lbs [0.9 Nm]	7 in-lbs [0.79 Nm]
Seal Gasket Material	Silicone	Silicone

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax PE3W08574-12](#)



2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3W08574-12

How to Order

Part Number Configuration:

PE3W08574

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W08574-12 = 12 inches long cable
PE3W08574-100cm = 100 cm long cable

2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax PE3W08574-12](https://www.pasternack.com/2.4mm-male-sma-male-rg405u-cable-assembly-pe3w08574-12-p.aspx)


URL: <https://www.pasternack.com/2.4mm-male-sma-male-rg405u-cable-assembly-pe3w08574-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W08574-12 CAD Drawing

2.4mm Male to SMA Male Cable 12 Inch Using RG405 Coax

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/28/2020	S. ELLIS



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X = ± .2	[.08]	FRACTIONS
.XX = ± .02	[.51]	± 1/32
.XXX = ± .005	[.13]	ANGLES ± 1°

CABLE LENGTH (L) TOLERANCES:

L ≤ 12 [305]	= +1 [25] / -0
12 [305] < L ≤ 60 [1524]	= +2 [51] / -0
60 [1524] < L ≤ 120 [3048]	= +4 [102] / -0
120 [3048] < L ≤ 300 [7620]	= +6 [152] / -0
300 [7620] < L ≤ +5% L / -0	

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

Pasternack Enterprises, Inc.
 P. O. Box 16759, Irvine, CA 92623.
 Phone: 1.949.261.1920 | 1.866.727.8376
 Fax: 1.949.261.7451
 Website: www.pasternack.com
 E-mail: sales@pasternack.com

SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	53919	K. DANG	PE3W08574
REV			A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.