

SMA Male to SHV Plug Cable Using RG223 Coax




PE3W09191

Configuration

- Connector 1: SMA Male
- Connector 2: SHV Plug
- Cable Type: RG223
- Coax Flex Type: Flexible

Features

- Max Frequency 300 MHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W09191 SMA male to SHV plug cable using RG223 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SHV cable assembly has a male to plug gender configuration with 50 ohm flexible RG223 coax. The PE3W09191 SMA male to SHV plug cable assembly operates to 300 MHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		300	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

Specifications by Frequency

SMA Male to SHV Plug Cable Using RG223 Coax



PE3W09191

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
		Frequency	50	100	250	300	MHz	
PE3W09191	Custom Lengths Available	Insertion Loss (Typ.)	0.01	0.02	0.05	0.06	dB/ft	
			0.04	0.07	0.17	0.21	dB/m	
PE3W09191-12	12 inch	Insertion Loss (Typ.)	0.22	0.23	0.26	0.27	dB	0.1
PE3W09191-24	24 inch	Insertion Loss (Typ.)	0.23	0.25	0.31	0.33	dB	0.132
PE3W09191-36	36 inch	Insertion Loss (Typ.)	0.24	0.27	0.36	0.39	dB	0.163
PE3W09191-60	60 inch	Insertion Loss (Typ.)	0.26	0.31	0.46	0.51	dB	0.225
PE3W09191-72	72 inch	Insertion Loss (Typ.)	0.27	0.33	0.51	0.57	dB	0.256

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.1 pounds
 Additional Weight per Inch: 0.00259 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
 Weight 0.1 lbs [45.36 g]

Cable

Cable Type	RG223
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.209 in [5.31 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]

SMA Male to SHV Plug Cable Using RG223 Coax



PE3W09191

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SHV Plug
Specification	MIL-STD-348	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	MIL-G-45204	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	QQ-N-290	100 μ in minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	QQ-N-290	100 μ in minimum
Hex Size	16-May inch	
Torque	3 in-lbs 0.34 Nm	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

SMA Male to SHV Plug Cable Using RG223 Coax

**PE3W09191****Typical Performance Data****How to Order**

Part Number Configuration:



Example: PE3W09191-12 = 12 inches long cable
PE3W09191-100cm = 100 cm long cable

SMA Male to SHV Plug Cable Using RG223 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SHV Plug Cable Using RG223 Coax PE3W09191](#)

URL: <https://www.pasternack.com/sma-male-to-shv-plug-cable-using-rg223-pe3w09191-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W09191 CAD Drawing

SMA Male to SHV Plug Cable Using RG223 Coax

