

C Male to C Male Right Angle Cable Using RG214 Coax




PE3W11250

Configuration

- Connector 1: C Male
- Connector 2: C Male Right Angle
- Cable Type: RG214
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W11250 type C male to type C male right angle cable using RG214 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type C to type C cable assembly has a male to male gender configuration with 50 ohm flexible RG214 coax. The PE3W11250 type C male to type C male cable assembly operates to 3 GHz. The right angle type C interface on the RG214 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation	66			%
Capacitance	30.8 [101.05]			pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency

C Male to C Male Right Angle Cable Using RG214 Coax



PE3W11250

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	3000	MHz	
PE3W11250	Custom Lengths Available	Insertion Loss (Typ.)	0.021	0.03	0.045	0.077	0.142	dB/ft	
			0.07	0.1	0.15	0.26	0.47	dB/m	
PE3W11250-12	12 inch	Insertion Loss (Typ.)	0.43	0.43	0.45	0.48	0.55	dB	0.413
PE3W11250-36	36 inch	Insertion Loss (Typ.)	0.47	0.49	0.54	0.64	0.83	dB	0.67
PE3W11250-48	48 inch	Insertion Loss (Typ.)	0.49	0.52	0.58	0.71	0.97	dB	0.798
PE3W11250-72	72 inch	Insertion Loss (Typ.)	0.53	0.58	0.67	0.87	1.26	dB	1.054
PE3W11250-108	108 inch	Insertion Loss (Typ.)	0.59	0.67	0.81	1.1	1.68	dB	1.438

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.2 dB
 Base Weight: 0.413 pounds
 Additional Weight per Inch: 0.01067 pounds

Mechanical Specifications

Cable Assembly

Weight 0.413 lbs [187.33 g]

Cable

Cable Type RG214
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PE
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Braid
 Shield Layer 2 Silver Plated Copper Braid
 Jacket Material PVC, Black
 Jacket Diameter 0.425 in [10.8 mm]
 Repeated Minimum Bend Radius 1.6 in [40.64 mm]

C Male to C Male Right Angle Cable Using RG214 Coax



PE3W11250

Connectors

Description	Connector 1	Connector 2
Type	C Male	C Male Right Angle
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	100 μ in minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 μ in minimum	100 μ in minimum

Environmental Specifications

Operating Range Temperature

-20 to +80 deg C

Compliance Certifications

(see product page for current document)


Plotted and Other Data

Notes:

C Male to C Male Right Angle Cable Using RG214 Coax

**PE3W11250****Typical Performance Data****How to Order**

Part Number Configuration:



Example: PE3W11250-12 = 12 inches long cable
PE3W11250-100cm = 100 cm long cable

C Male to C Male Right Angle Cable Using RG214 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [C Male to C Male Right Angle Cable Using RG214 Coax PE3W11250](#)

URL: <https://www.pasternack.com/c-male-to-c-male-cable-using-rg214-pe3w11250-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W11250 CAD Drawing

C Male to C Male Right Angle Cable Using RG214 Coax

