



2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax

TECHNICAL DATA SHEET


PE3W11452

Configuration

- Connector 1: 2.2-5 Male
- Connector 2: N Male
- Cable Type: 1/4" Superflexible
- Coax Flex Type: Corrugated

Features

- Max Frequency 3 GHz
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket



Applications

- General Purpose
- Laboratory Use
- Low PIM Applications

Description

Pasternack's PE3W11452 2.2-5 male to type N male cable using 1/4 inch superflexible coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack 2.2-5 to type N cable assembly has a male to male gender configuration with 50 ohm corrugated 1/4" superflexible coax. The PE3W11452 2.2-5 male to type N male cable assembly operates to 3 GHz. Our low PIM design also offers excellent passive intermodulation performance.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax PE3W11452](#)



2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax

TECHNICAL DATA SHEET

PE3W11452

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.27:1	
Velocity of Propagation		82		%
RF Shielding	120			dB
Capacitance		24.4 [80.05]		pF/ft [pF/m]
Inductance		0.059 [0.19]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ω /1000ft [Ω /Km]
DC Resistance Outer Conductor		2.53 [8.3]		Ω /1000ft [Ω /Km]
Jacket Spark			2,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency	100	250	500	1000	3000	
PE3W11452	Custom Lengths Available	Insertion Loss (Typ.)	0.02	0.03	0.04	0.06	0.11	dB/ft	
			0.06	0.09	0.13	0.19	0.36	dB/m	
PE3W11452-12	12 inch	Insertion Loss (Typ.)	0.22	0.23	0.24	0.26	0.31	dB	0.282
PE3W11452-24	24 inch	Insertion Loss (Typ.)	0.24	0.26	0.28	0.32	0.42	dB	0.324
PE3W11452-36	36 inch	Insertion Loss (Typ.)	0.25	0.28	0.32	0.38	0.53	dB	0.366
PE3W11452-48	48 inch	Insertion Loss (Typ.)	0.27	0.31	0.36	0.43	0.63	dB	0.408
PE3W11452-60	60 inch	Insertion Loss (Typ.)	0.28	0.33	0.39	0.49	0.74	dB	0.45

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.282 pounds
Additional Weight per Inch:	0.00867 pounds

Mechanical Specifications

Cable Assembly

Weight	0.282 lbs [127.91 g]
--------	----------------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax PE3W11452](#)



2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax

TECHNICAL DATA SHEET

PE3W11452

Cable

Cable Type	1/4" Superflexible
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	1
Shield Layer 1	Helically Corrugated Copper Tube
Jacket Material	PE, Black
Jacket Diameter	0.303 in [7.7 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Typical Flex Cycles	20
Tensile Strength	79 lbs [35.83 Kg]

Connectors

Description	Connector 1	Connector 2
Type	2.2-5 Male Threaded	N Male Threaded
Specification		IEC 60169-16
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Silver	Spring Copper, Silver
Contact Plating Specification		5 µm minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Nickel
Outer Conductor Plating Specification		5 µm minimum
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification		2 µm minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Nickel
Coupling Nut Plating Specification		5 µm minimum
Hex Size		19 mm

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax PE3W11452](#)



2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax

TECHNICAL DATA SHEET

PE3W11452

How to Order

Part Number Configuration:

PE3W11452

- **xx**

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE3W11452-12 = 12 inches long cable
PE3W11452-100cm = 100 cm long cable

2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax PE3W11452](https://www.pasternack.com/2.2-5-male-to-n-male-low-pim-cable-using-1-4-inch-superflexible-pe3w11452-p.aspx)

URL: <https://www.pasternack.com/2.2-5-male-to-n-male-low-pim-cable-using-1-4-inch-superflexible-pe3w11452-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W11452 CAD Drawing

2.2-5 Male to N Male Low PIM Cable Using 1/4 inch Superflexible Coax



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED, LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. PIM LEVEL LABEL PLACEMENT: APPROXIMATELY 6 INCHES FROM CABLE END, 1 PLACE, FOR ALL LENGTHS OF CABLE.
3. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: APPROXIMATELY 6 INCHES FROM CABLE END, 1 PLACE, FOR ALL LENGTHS OF CABLE.
4. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE NONE SHEET 1 OF 1	
Website: www.PasterNack.com Phone: 1.866.727.8376 1.949.261.1920		DESCRIPTION 2.2-5 MALE TO N MALE LOW PIM CABLE USING 1/4 INCH SUPERFLEXIBLE COAX	
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES: .X = ±.2 [5] FRACTIONS ±.732 .XX = ±.02 [0.13] ANGLES ± 1° CABLE LENGTH TOLERANCES: <12 [305] ≤ 60 [1524] = +1 [25] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL DIMENSIONS ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED. UNDIMENSIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.			
ZONE REV A	DESCRIPTION INITIAL RELEASE	CHANGED BY DMAY	APPROVED AGANWANI
SIZE A		CAGE CODE DMAY	ITEM NO. PE3W11452