

Water Blue FAKRA Jack Right Angle to SMA Male
Low Loss Cable Using LMR-100A-UF Coax



RF Cable Assemblies Technical Data Sheet

PE3W12749

Configuration

- Connector 1: FAKRA Jack Right Angle
- Connector 2: SMA Male
- Cable Type: LMR-100A-UF

Features

- Max Frequency 4 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- Double Shielded
- TPE Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W12749 water blue FAKRA jack right angle to SMA male 12 inch cable using LMR-100A-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack FAKRA to SMA cable assembly has a jack to male gender configuration with 50 ohm flexible LMR-100A-UF coax. The PE3W12749 FAKRA jack to SMA male cable assembly operates to 4 GHz. The right angle FAKRA interface on the LMR-100A-UF cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Water Blue FAKRA Jack Right Angle to SMA Male Low Loss Cable Using LMR-100A-UF Coax PE3W12749](#)

Water Blue FAKRA Jack Right Angle to SMA Male Low Loss Cable Using LMR-100A-UF Coax



RF Cable Assemblies Technical Data Sheet

PE3W12749

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
Velocity of Propagation		66		%
RF Shielding	90			dB
Group Delay		1.54 [5.05]		ns/ft [ns/m]
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Inductance		0.077 [0.25]		uH/ft [uH/m]
DC Resistance Inner Conductor		81 [265.75]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		9.5 [31.17]		Ω/1000ft [Ω/Km]
Jacket Spark			2,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	4	GHz
Insertion Loss (Typ.)	0.07	0.115	0.165	0.24	0.508	dB/ft

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the male connector and 0.2 dB for the plug connector.

Mechanical Specifications

Cable Assembly

Weight 0.035 lbs [15.88 g]

Cable

Cable Type LMR-100A-UF
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper
Dielectric Type PE
Number of Shields 2
Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper
Jacket Material TPE, Black
Jacket Diameter 0.11 in [2.79 mm]

One Time Minimum Bend Radius 0.25 in [6.35 mm]
Repeated Minimum Bend Radius 1 in [25.4 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Water Blue FAKRA Jack Right Angle to SMA Male Low Loss Cable Using LMR-100A-UF Coax PE3W12749](#)

Water Blue FAKRA Jack Right Angle to SMA Male Low Loss Cable Using LMR-100A-UF Coax



RF Cable Assemblies Technical Data Sheet

PE3W12749

Bending Moment
Flat Plate Crush
Tensile Strength

0.1 lbs-ft [0.14 N-m]
10 lbs/in [0.18 Kg/mm]
15 lbs [6.8 Kg]

Connectors

Description	Connector 1	Connector 2
Type	FAKRA Jack Right Angle	SMA Male
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Phosphor Bronze, Gold	Brass, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Nickel	
Body Material and Plating	Plastic	Brass, Gold
Coupling Nut Material and Plating		Brass, Gold
Hex Size		5/16 in
Torque		5 in-lbs [0.57 Nm]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Water Blue FAKRA Jack Right Angle to SMA Male Low Loss Cable Using LMR-100A-UF Coax PE3W12749](#)

Water Blue FAKRA Jack Right Angle to SMA Male
Low Loss Cable Using LMR-100A-UF Coax



RF Cable Assemblies Technical Data Sheet

PE3W12749

How to Order

Part Number Configuration:

PE3W12749

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W12749-12 = 12 inches long cable
PE3W12749-100cm = 100 cm long cable

Water Blue FAKRA Jack Right Angle to SMA Male Low Loss Cable Using LMR-100A-UF Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Water Blue FAKRA Jack Right Angle to SMA Male Low Loss Cable Using LMR-100A-UF Coax PE3W12749](#)

URL: <https://www.pasternack.com/jack-right-angle-to-sma-male-low-loss-cable-using-lmr-100a-uf-pe3w12749-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W12749 CAD Drawing
 Water Blue FAKRA Jack Right Angle to SMA Male Low Loss Cable Using LMR-100A-UF Coax

