



Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax

RF Cable Assemblies Technical Data Sheet

PE3W12927

Configuration

- Connector 1: Mini SMP Female
- Connector 2: SMP Female Right Angle
- Cable Type: PE-SR047FL
- Coax Flex Type: Formable

Features

- Max Frequency 18 GHz
- 69.5% Phase Velocity

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W12927 Mini SMP female to SMP female right angle cable using PE-SR047FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack Mini SMP to SMP cable assembly has a female to female gender configuration with 50 ohm formable PE-SR047FL coax. The PE3W12927 Mini SMP female to SMP female cable assembly operates to 18 GHz. The right angle SMP interface on the PE-SR047FL cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax PE3W12927](#)

Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax



RF Cable Assemblies Technical Data Sheet

PE3W12927

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
Capacitance		32 [104.99]		pF/ft [pF/m]
DC Resistance Inner Conductor		207 [679.13]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		8 [26.25]		Ω/1000ft [Ω/Km]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.36	0.505	0.807	1.196	1.8	dB/ft
	1.18	1.66	2.65	3.92	5.91	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the Mini SMP female connector and 0.2 dB for the SMP female connector.

Mechanical Specifications

Cable Assembly

Weight 0.006 lbs [2.72 g]

Cable

Cable Type PE-SR047FL
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper Clad Steel, Silver
 Dielectric Type PTFE
 Number of Shields 1
 Outer Conductor Material and Plating Tinned Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax PE3W12927](#)



Mini SMP Female to SMP Female Right Angle
Cable Using PE-SR047FL Coax

RF Cable Assemblies Technical Data Sheet

PE3W12927

Connectors

Description	Connector 1	Connector 2
Type	Mini SMP Female	SMP Female Right Angle
Specification	MIL-STD-348A	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification		MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Plating Specification		MIL-G-45204

Environmental Specifications

Temperature

Operating Range

-40 to +100 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax PE3W12927](#)



Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax

RF Cable Assemblies Technical Data Sheet

PE3W12927

How to Order

Part Number Configuration:

PE3W12927- **xx****uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: PE3W12927-12 = 12 inches long cable
PE3W12927-100cm = 100 cm long cable

Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax PE3W12927](#)

URL: <https://www.pasternack.com/mini-smp-female-to-smp-female-cable-using-pe-sr047fl-pe3w12927-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W12927 CAD Drawing

Mini SMP Female to SMP Female Right Angle Cable Using PE-SR047FL Coax

