

## 2.2-5 Male to SMA Male Low PIM Cable 60 Inch Length Using TFT-5G-402 Coax with Times Microwave Components




### PE3W13539-60

#### Configuration

- Connector 1: 2.2-5 Male
- Connector 2: SMA Male
- Cable Type: TFT-5G-402
- Coax Flex Type: Flexible

#### Features

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 80 dB
- 76% Phase Velocity
- Double Shielded
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use
- Low PIM Applications

#### Description

Pasternack's PE3W13539-60 2.2-5 male to SMA male 60 inch cable using TFT-5G-402 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 2.2-5 to SMA cable assembly has a male to male gender configuration with 50 ohm flexible TFT-5G-402 coax. The PE3W13539-60 2.2-5 male to SMA male cable assembly operates to 6 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	80			dB
Passive Intermodulation			-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				
Capacitance		26.7 [87.6]		pF/ft [pF/m]

#### Specifications by Frequency

## 2.2-5 Male to SMA Male Low PIM Cable 60 Inch Length Using TFT-5G-402 Coax with Times Microwave Components



### PE3W13539-60

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
			Frequency	500	1000	2500	6000	
PE3W13539	Custom Lengths Available	Insertion Loss (Typ.)	0.081	0.111	0.188	0.295	dB/ft	
			0.27	0.37	0.62	0.97	dB/m	
PE3W13539-12	12 In	Insertion Loss (Typ.)	0.57	0.6	0.67	0.78	dB	0.088
PE3W13539-24	24 In	Insertion Loss (Typ.)	0.65	0.71	0.86	1.07	dB	0.117
PE3W13539-36	36 In	Insertion Loss (Typ.)	0.73	0.82	1.05	1.37	dB	0.145
PE3W13539-60	60 In	Insertion Loss (Typ.)	0.89	1.04	1.42	1.96	dB	0.201
PE3W13539-200CM	200 CM	Insertion Loss (Typ.)	1.02	1.21	1.72	2.42	dB	0.245

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.24 dB
Loss due to Connector 2:	0.24 dB
Base Weight:	0.088 pounds
Additional Weight per Inch:	0.00234 pounds

### Mechanical Specifications

#### Cable Assembly

Length	60 in [152.4 cm]
Width/Diameter	.5 in [12.7 mm]
Weight	0.201 lbs [91.17 g]

#### Cable

Cable Type	TFT-5G-402
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Tin
Outer Conductor 1 Material and Plating	Copper, Tin
Jacket Material	FEP, Blue
Jacket Diameter	0.16 in [4.06 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]

2.2-5 Male to SMA Male Low PIM Cable 60 Inch Length  
Using TFT-5G-402 Coax with Times Microwave Components



**PE3W13539-60**

**Connectors**

Description	Connector 1	Connector 2
Type	2.2-5 Male	SMA Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	100	
Contact Material and Plating	Beryllium Copper, Silver	Brass, Silver
Contact Plating Specification	200 μin	5 μin
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Silver	Brass, Silver
Body Plating Specification	100 μin	5 μin
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	100 μin	3 μin
Torque	26 in-lbs 2.94 Nm	9 in-lbs 1.02 Nm

**Environmental Specifications**

Operating Range Temperature -40 to +125 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

## 2.2-5 Male to SMA Male Low PIM Cable 60 Inch Length Using TFT-5G-402 Coax with Times Microwave Components



### PE3W13539-60

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**PE3W13539**

**- xx**

**uu**

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE3W13539-12 = 12 inches long cable  
PE3W13539-100cm = 100 cm long cable

2.2-5 Male to SMA Male Low PIM Cable 60 Inch Length Using TFT-5G-402 Coax with Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to SMA Male Low PIM Cable 60 Inch Length Using TFT-5G-402 Coax with Times Microwave Components PE3W13539-60](#)

URL: <https://www.pasternack.com/2.2-5-male-to-sma-male-low-pim-cable-60-inch-length-using-tft-5g-402-pe3w13539-60-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3W13539-60 CAD Drawing

2.2-5 Male to SMA Male Low PIM Cable 60 Inch Length Using TFT-5G-402 Coax with Times Microwave Components

