

## 1.85mm Female to Mini SMP Female Cable Using PE-047SR Coax




### PE3W14540

#### Configuration

- Connector 1: 1.85mm Female
- Connector 2: Mini SMP Female
- Cable Type: PE-047SR
- Coax Flex Type: Semi-Rigid

#### Features

- Max Frequency 40 GHz



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W14540 1.85mm female to Mini SMP female cable using PE-047SR coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack 1.85mm to Mini SMP cable assembly has a female to female gender configuration with 50 ohm semi-rigid PE-047SR coax. The PE3W14540 1.85mm female to Mini SMP female cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.4:1	

#### Specifications by Frequency

## 1.85mm Female to Mini SMP Female Cable Using PE-047SR Coax



### PE3W14540

Part Number	Length	Description	F1	F2	F3	F4	F5	Units MHz	Weight (lbs)
		Frequency	1000	2000	4500	9000	20000		
PE3W14540	Custom Lengths Available	Insertion Loss (Typ.)	0.4 1.32	0.5 1.65	0.75 2.47	1.2 3.94	1.9 6.24	dB/ft dB/m	
PE3W14540-3	3 inch	Insertion Loss (Typ.)	0.3	0.33	0.39	0.5	0.68	dB	0.014
PE3W14540-6	6 inch	Insertion Loss (Typ.)	0.4	0.45	0.58	0.8	1.15	dB	0.015
PE3W14540-12	12 inch	Insertion Loss (Typ.)	0.6	0.7	0.95	1.4	2.1	dB	0.017
PE3W14540-18	18 inch	Insertion Loss (Typ.)	0.8	0.95	1.33	2	3.05	dB	0.02
PE3W14540-60	60 inch	Insertion Loss (Typ.)	2.2	2.7	3.95	6.2	9.7	dB	0.034

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.017 pounds

Additional Weight per Inch: 0.00034 pounds

### Mechanical Specifications

#### Cable Assembly

Width/Diameter 0.5 in [12.7 mm]  
Weight 0.017 lbs [7.71 g]

#### Cable

Cable Type	PE-047SR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Copper
Repeated Minimum Bend Radius	0.05 in [1.27 mm]

## 1.85mm Female to Mini SMP Female Cable Using PE-047SR Coax



### PE3W14540

#### Connectors

Description	Connector 1	Connector 2
Type	1.85mm Female	Mini SMP Female
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	50 $\mu$ Inches.	
Dielectric Type		PTFE
Body Material and Plating	Passivated Stainless Steel	Beryllium Copper, Gold
Body Plating Specification	SAE-AMS-2700	
Coupling Nut Material and Plating	Passivated Stainless Steel	
Coupling Nut Plating Specification	SAE-AMS-2700	

#### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

## 1.85mm Female to Mini SMP Female Cable Using PE-047SR Coax




### PE3W14540

#### Typical Performance Data

#### How to Order

Part Number Configuration:



Example: PE3W14540-12 = 12 inches long cable  
PE3W14540-100cm = 100 cm long cable

1.85mm Female to Mini SMP Female Cable Using PE-047SR Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [1.85mm Female to Mini SMP Female Cable Using PE-047SR Coax PE3W14540](#)

URL: <https://www.pasternack.com/1.85mm-female-to-mini-smp-female-cable-using-pe-047sr-pe3w14540-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3W14540 CAD Drawing

## 1.85mm Female to Mini SMP Female Cable Using PE-047SR Coax

