

## N Male to N Male Low Loss Cable Using LMR-500-UF Coax



### PE3W14343

#### Configuration

- Connector 1: N Male
- Connector 2: N Male
- Cable Type: LMR-500-UF
- Coax Flex Type: Flexible

#### Features

- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- Double Shielded
- TPE Jacket

#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W14343 type N male to type N male cable using LMR-500-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-500-UF coax. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		85		%
RF Shielding	90			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		0.68 [2.23]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		1.27 [4.17]		Ohms/1000ft [Ohms/Km]
Jacket Spark			8,000	Vrms

#### Mechanical Specifications

##### Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.541 lbs [245.39 g]

## N Male to N Male Low Loss Cable Using LMR-500-UF Coax



### PE3W14343

#### Cable

Cable Type	LMR-500-UF
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	Foam PE
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper
Jacket Material	TPE, Black
Jacket Diameter	0.5 in [12.7 mm]
One Time Minimum Bend Radius	1.25 in [31.75 mm]
Repeated Minimum Bend Radius	5 in [127 mm]
Bending Moment	1.25 lbs-ft [1.7 N-m]
Flat Plate Crush	35 lbs/in [0.63 Kg/mm]
Tensile Strength	260 lbs [117.93 Kg]

#### Connectors

Description	Connector 1	Connector 2
Type	N Male	N Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	100 µin minimum

#### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:



## N Male to N Male Low Loss Cable Using LMR-500-UF Coax

### PE3W14343

#### Typical Performance Data

#### How to Order

Part Number Configuration: **PE3W14343** - **xx** **uu**

\_\_\_\_\_ Unit of Measure:  
 cm = Centimeters  
 <blank> = Inches  
 \_\_\_\_\_ Length  
 \_\_\_\_\_ Base Number

Example: PE3W14343-12 = 12 inches long cable  
 PE3W14343-100cm = 100 cm long cable

N Male to N Male Low Loss Cable Using LMR-500-UF Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-500-UF Coax PE3W14343](#)

URL: <https://www.pasternack.com/n-male-to-n-male-cable-using-lmr-500-uf-pe3w14343-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3W14343 CAD Drawing

N Male to N Male Low Loss Cable Using LMR-500-UF Coax

