

Mini SMP Female Right Angle to SMP Female Right Angle Cable Using Tinned RG405 Coax, LF Solder




PE3W17234LF

Configuration

- Connector 1: Mini SMP Female Right Angle
- Connector 2: SMP Female Right Angle
- Cable Type: RG405 Tinned
- Coax Flex Type: Semi-Rigid

Features

- Max Frequency 12.4 GHz



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W17234LF Mini SMP female right angle to SMP female right angle cable using tinned RG405 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack Mini SMP to SMP cable assembly has a female to female gender configuration with 50 ohm semi-rigid RG405 tinned coax. The PE3W17234LF Mini SMP female to SMP female cable assembly operates to 12.4 GHz. The right angle Mini SMP and right angle SMP interfaces on the RG405 tinned cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.4:1	

Specifications by Frequency

Mini SMP Female Right Angle to SMP Female Right Angle Cable Using Tinned RG405 Coax, LF Solder



PE3W17234LF

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	1000	2500	5000	10000	12400	MHz	
PE3W17234LF	Custom Lengths Available	Insertion Loss (Typ.)	0.22	0.32	0.477	0.8	0.896	dB/ft	
			0.73	1.04	1.57	2.63	2.94	dB/m	
PE3W17234LF-6	6 inch	Insertion Loss (Typ.)	0.51	0.56	0.64	0.8	0.85	dB	0.016
PE3W17234LF-12	12 inch	Insertion Loss (Typ.)	0.62	0.72	0.88	1.2	1.3	dB	0.022
PE3W17234LF-18	18 inch	Insertion Loss (Typ.)	0.73	0.88	1.12	1.6	1.75	dB	0.029
PE3W17234LF-24	24 inch	Insertion Loss (Typ.)	0.84	1.04	1.36	2	2.2	dB	0.036
PE3W17234LF-36	36 inch	Insertion Loss (Typ.)	1.06	1.35	1.84	2.8	3.09	dB	0.049

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.2 dB
Loss due to Connector 2:	0.2 dB
Base Weight:	0.022 pounds
Additional Weight per Inch:	0.00109 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.022 lbs [9.98 g]

Cable

Cable Type	RG405 Tinned
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Tinned Copper
One Time Minimum Bend Radius	0.05 in [1.27 mm]

Connectors

Description	Connector 1	Connector 2
Type	Mini SMP Female Right Angle	SMP Female Right Angle
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Beryllium Copper, Gold	
Body Material and Plating	Brass, Gold	Beryllium Copper, Gold

Mini SMP Female Right Angle to SMP Female Right Angle Cable Using Tinned RG405 Coax, LF Solder



PE3W17234LF

Environmental Specifications

Operating Range Temperature -55 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

How to Order

Part Number Configuration: **PE3W17234LF - xx uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W17234LF-12 = 12 inches long cable
PE3W17234LF-100cm = 100 cm long cable

Mini SMP Female Right Angle to SMP Female Right Angle Cable Using Tinned RG405 Coax, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Female Right Angle to SMP Female Right Angle Cable Using Tinned RG405 Coax, LF Solder PE3W17234LF](#)

URL: <https://www.pasternack.com/mini-smp-female-right-angle-to-smp-female-cable-using-tinned-rg405-lf-solder-pe3w17234lf-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W17234LF CAD Drawing
Mini SMP Female Right Angle to SMP Female Right Angle Cable Using Tinned RG405 Coax, LF Solder

