

Plenum SMA Female to SMA Female Low PIM Cable 50 CM Length Using SPP-250-LLPL Coax




PE3W17229-50CM

Configuration

- Connector 1: SMA Female
- Connector 2: SMA Female
- Cable Type: SPP-250-LLPL
- Coax Flex Type: Corrugated

Features

- Max Frequency 6 GHz
- Low PIM: -155 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use
- Low PIM Applications

Description

Pasternack's PE3W17229-50CM SMA female to SMA female 50 cm cable using SPP-250-LLPL coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack SMA to SMA cable assembly has a female to female gender configuration with 50 ohm corrugated SPP-250-LLPL coax. The PE3W17229-50CM SMA female to SMA female cable assembly operates to 6 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -155 dBc.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	100			dB
Passive Intermodulation			-155	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				
Capacitance	27 [88.58]			pF/ft [pF/m]
Inductance	0.067 [0.22]			uH/ft [uH/m]
DC Resistance Inner Conductor	3 [9.84]			Ohms/1000ft [Ohms/Km]

Specifications by Frequency

Plenum SMA Female to SMA Female Low PIM Cable 50 CM Length Using SPP-250-LLPL Coax



PE3W17229-50CM

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
		Frequency	500	1000	2500	6000	MHz	
PE3W17229	Custom Lengths Available	Insertion Loss (Typ.)	0.039	0.054	0.093	0.148	dB/ft	
			0.13	0.18	0.31	0.49	dB/m	
PE3W17229-12	12 in	Insertion Loss (Typ.)	0.24	0.26	0.3	0.35	dB	0.11
PE3W17229-24	24 in	Insertion Loss (Typ.)	0.28	0.31	0.39	0.5	dB	0.181
PE3W17229-36	36 in	Insertion Loss (Typ.)	0.32	0.37	0.48	0.65	dB	0.251
PE3W17229-60	60 in	Insertion Loss (Typ.)	0.4	0.47	0.67	0.94	dB	0.391
PE3W17229-50CM	50 CM	Insertion Loss (Typ.)	0.27	0.29	0.36	0.45	dB	0.155

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.11 pounds
 Additional Weight per Inch: 0.00584 pounds

Mechanical Specifications

Cable Assembly

Length 19.685 in [500 mm]
 Width/Diameter .5 in [12.7 mm]
 Weight 0.155 lbs [70.31 g]

Cable

Cable Type	SPP-250-LLPL
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Copper
Jacket Material	FEP, Blue
Jacket Diameter	0.28 in [7.11 mm]
One Time Minimum Bend Radius	1.25 in [31.75 mm]
Bending Moment	0.8 lbs-ft [1.08 N-m]

Plenum SMA Female to SMA Female Low PIM Cable
50 CM Length Using SPP-250-LLPL Coax



PE3W17229-50CM

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	SMA Female
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Silver	Beryllium Copper, Silver
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal

Environmental Specifications

Operating Range Temperature -40 to +155 deg C

Compliance Certifications

(see [product page](#) for current document)

Plotted and Other Data

Notes:

Plenum SMA Female to SMA Female Low PIM Cable 50 CM Length Using SPP-250-LLPL Coax




PE3W17229-50CM

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3W17229-12 = 12 inches long cable
PE3W17229-100cm = 100 cm long cable

Plenum SMA Female to SMA Female Low PIM Cable 50 CM Length Using SPP-250-LLPL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Plenum SMA Female to SMA Female Low PIM Cable 50 CM Length Using SPP-250-LLPL Coax PE3W17229-50CM](#)

URL: <https://www.pasternack.com/plenum-sma-female-to-sma-female-low-pim-cable-50-cm-length-using-spp-250-llpl-pe3w17229-50cm-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W17229-50CM CAD Drawing

Plenum SMA Female to SMA Female Low PIM Cable 50 CM Length Using SPP-250-LLPL Coax

