

4.3-10 Male to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink




PE3W17888/HS

Configuration

- Connector 1: 4.3-10 Male
- Connector 2: N Male
- Cable Type: LMR-400-UF
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- Double Shielded
- TPE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W17888/HS 4.3-10 male to type N male cable using LMR-400-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 4.3-10 to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-400-UF coax. The PE3W17888/HS 4.3-10 male to type N male cable assembly operates to 6 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.07 [3.51]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		1.65 [5.41]		Ohms/1000ft [Ohms/Km]

4.3-10 Male to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink



PE3W17888/HS

Electrical Specifications

Description	Minimum	Typical				Maximum	Units
Jacket Spark					8,000		Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000	MHz	
PE3W17888/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.023	0.035	0.05	0.081	0.112	dB/ft	
			0.08	0.12	0.17	0.27	0.37	dB/m	
PE3W17888/HS-12	12 inch	Insertion Loss (Typ.)	0.23	0.24	0.25	0.29	0.32	dB	0.254
PE3W17888/HS-24	24 inch	Insertion Loss (Typ.)	0.25	0.27	0.3	0.37	0.43	dB	0.341
PE3W17888/HS-36	36 inch	Insertion Loss (Typ.)	0.27	0.31	0.35	0.45	0.54	dB	0.428
PE3W17888/HS-60	60 inch	Insertion Loss (Typ.)	0.32	0.38	0.45	0.61	0.76	dB	0.602
PE3W17888/HS-300	300 inch	Insertion Loss (Typ.)	0.78	1.08	1.45	2.23	3	dB	2.342

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
Loss due to Connector 2: 0.1 dB
Base Weight: 0.254 pounds
Additional Weight per Inch: 0.00725 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
Weight 0.254 lbs [115.21 g]

Cable

Cable Type LMR-400-UF
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper
Dielectric Type PE (F)
Number of Shields 2
Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid
Jacket Material TPE, Black
Jacket Diameter 0.405 in [10.29 mm]
One Time Minimum Bend Radius 1 in [25.4 mm]
Repeated Minimum Bend Radius 4 in [101.6 mm]
Bending Moment 0.38 lbs-ft [0.52 N-m]
Flat Plate Crush 20 lbs/in [0.36 Kg/mm]
Tensile Strength 160 lbs [72.57 Kg]

4.3-10 Male to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink



PE3W17888/HS

Connectors

Description	Connector 1	Connector 2
Type	4.3-10 Male	N Male
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	
Contact Material and Plating	Brass, Silver	Brass, Silver
Contact Plating Specification		70 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Nickel
Body Plating Specification		100 μ in minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Nickel
Coupling Nut Plating Specification		100 μ in minimum
Seal Gasket Material	Silicone	

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

4.3-10 Male to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink



PE3W17888/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3W17888/HS - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3W17888/HS-12 = 12 inches long cable
PE3W17888/HS-100cm = 100 cm long cable

4.3-10 Male to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [4.3-10 Male to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink PE3W17888/HS](#)

URL: <https://www.pasternack.com/4.3-10-male-to-n-male-low-loss-cable-using-lmr-400-uf-with-heatshrink-pe3w17888-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W17888/HS CAD Drawing

4.3-10 Male to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink



NOTES:
1. C/A
36
CE
AF
C/A
C/A
2. C/A
3. C/A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE, WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC., IS PROHIBITED. THESE COMMODITIES TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS.

© 2025 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.

+1 (866) 558-2786 | sales@pasternack.com | pasternack.com