

## 2.92mm Male Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid



### PE51263

#### Configuration

- 2.92mm Male Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: PE-034SR, .034 Semi-Rigid

#### Features

- Max. Operating Frequency 40 GHz
- Excellent VSWR of 1.25:1
- Gold over Nickel Plated Beryllium Copper Contact

#### Applications

- General Purpose Test
- Custom Cable Assemblies

#### Description

Pasternack's PE51263, 2.92mm, Standard, Connector is part of our full line of RF components available for same-day shipping. Our 2.92mm male connector operates up to a maximum frequency of 40 GHz and offers excellent VSWR of 1.25:1.

Our 2.92mm male connector PE51263 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

#### Electrical Specifications

| Description                          | Minimum | Typical | Maximum | Units |
|--------------------------------------|---------|---------|---------|-------|
| Frequency Range                      | DC      |         | 40      | GHz   |
| VSWR                                 |         |         | 1.25:1  |       |
| Insertion Loss                       |         |         | 0.252   | dB    |
| Operating Voltage (AC)               |         |         | 250     | Vrms  |
| Dielectric Withstanding Voltage (AC) |         |         | 750     | Vrms  |
| Inner Conductor DC Resistance        |         |         | 3       | mOhms |
| Outer Conductor DC Resistance        |         |         | 2       | mOhms |
| Insulation Resistance                | 5,000   |         |         | MOhms |
| RF Leakage                           | 100     |         |         | dB    |
| Impedance                            |         | 50      |         | Ohms  |

Electrical Specification Notes:

Insertion loss is =  $0.04 * \sqrt{F(\text{GHz})}$  dB

#### Mechanical Specifications

##### Size

|               |  |
|---------------|--|
| Length        | 0.291339 in [7.4 mm]                   |
| Width         | 0.291339 in [7.4 mm]                   |
| Height        | 0.629921 in [16 mm]                    |
| Weight        | 0.015 lbs [6.8 g]                      |
| Mating Cycles | 500 Cycles                             |
| Mating Torque | 11.47 to 15 in-lbs [[1.30 to 1.70 Nm]] |

## 2.92mm Male Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid



### PE51263

|                       |                   |
|-----------------------|-------------------|
| Cable Retention Force | 4.9 lbs [2.22 kg] |
|-----------------------|-------------------|

#### Material Specifications

| Description    | Material         | Plating               |
|----------------|------------------|-----------------------|
| Contact        | Beryllium Copper | Gold over Nickel      |
| Insulation     | PPO              |                       |
| Body           | Stainless Steel  | Passivated            |
| Coupling Nut   | Stainless Steel  | Passivated            |
| Retaining Ring | Beryllium Copper | Copper-Tin-Zinc Alloy |
| Gasket         | Silicone         |                       |
| Solder Sleeve  | Stainless Steel  | Passivated            |

#### Environmental Specifications

|                    |                                      |
|--------------------|--------------------------------------|
| <b>Temperature</b> |                                      |
| Operating Range    | -55 to +105 deg C                    |
| Thermal Shock      | MIL-STD-202, Method 107, Condition B |

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

2.92mm Male Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid PE51263](#)

URL: <https://www.pasternack.com/2.92mm-male-pe-034sr-.034-semi-rigid-connector-pe51263-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

## 2.92mm Male Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid

+1 (866) 558-2786 | [sales@pasternack.com](mailto:sales@pasternack.com) | [pasternack.com](http://pasternack.com)

## 2.92mm Female Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid



### PE51264

#### Configuration

- 2.92mm Female Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: PE-034SR, .034 Semi-Rigid

#### Features

- Max. Operating Frequency 40 GHz
- Excellent VSWR of 1.25:1
- Gold over Nickel Plated Beryllium Copper Contact

#### Applications

- General Purpose Test
- Custom Cable Assemblies

#### Description

Pasternack's PE51264 , 2.92mm, Standard, Connector is part of our full line of RF components available for same-day shipping. Our 2.92mm female connector operates up to a maximum frequency of 40 GHz and offers excellent VSWR of 1.25:1.

Our 2.92mm female connector PE51264 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

#### Electrical Specifications

| Description                          | Minimum | Typical | Maximum | Units |
|--------------------------------------|---------|---------|---------|-------|
| Frequency Range                      | DC      |         | 40      | GHz   |
| VSWR                                 |         |         | 1.25:1  |       |
| Insertion Loss                       |         |         | 0.252   | dB    |
| Operating Voltage (AC)               |         |         | 250     | Vrms  |
| Dielectric Withstanding Voltage (AC) |         |         | 750     | Vrms  |
| Inner Conductor DC Resistance        |         |         | 3       | mOhms |
| Outer Conductor DC Resistance        |         |         | 2       | mOhms |
| Insulation Resistance                | 5,000   |         |         | MOhms |
| RF Leakage                           | 100     |         |         | dB    |
| Impedance                            |         | 50      |         | Ohms  |

Electrical Specification Notes:

Insertion loss is =  $0.04 * \sqrt{F(\text{GHz})}$  dB

#### Mechanical Specifications

##### Size

|               |  |
|---------------|--|
| Length        | 0.291339 in [7.4 mm]                   |
| Width         | 0.291339 in [7.4 mm]                   |
| Height        | 0.540945 in [13.74 mm]                 |
| Weight        | 0.015 lbs [6.8 g]                      |
| Mating Cycles | 500 Cycles                             |
| Mating Torque | 11.47 to 15 in-lbs [[1.30 to 1.70 Nm]] |

## 2.92mm Female Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid



### PE51264

|                       |                   |
|-----------------------|-------------------|
| Cable Retention Force | 4.9 lbs [2.22 kg] |
|-----------------------|-------------------|

#### Material Specifications

| Description   | Material         | Plating          |
|---------------|------------------|------------------|
| Contact       | Beryllium Copper | Gold over Nickel |
| Insulation    | PPO              |                  |
| Body          | Stainless Steel  | Passivated       |
| Coupling Nut  | Stainless Steel  | Passivated       |
| Solder Sleeve | Stainless Steel  | Passivated       |

#### Environmental Specifications

|                    |                                      |
|--------------------|--------------------------------------|
| <b>Temperature</b> |                                      |
| Operating Range    | -55 to +105 deg C                    |
| Thermal Shock      | MIL-STD-202, Method 107, Condition B |

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

2.92mm Female Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Female Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid PE51264](#)

URL: <https://www.pasternack.com/2.92mm-female-pe-034sr-.034-semi-rigid-connector-pe51264-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

## 2.92mm Female Connector Clamp/Solder Attachment for PE-034SR, .034 Semi-Rigid

+1 (866) 558-2786 | [sales@pasternack.com](mailto:sales@pasternack.com) | [pasternack.com](http://pasternack.com)

## 034 Semi-rigid Coax Cable with Copper Outer Conductor

### TECHNICAL DATA SHEET

PE-034SR

#### 034 Semi-rigid Coax Cable with Copper Outer Conductor

##### Configuration

|                                      |                           |
|--------------------------------------|---------------------------|
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type                      | PTFE                      |
| Shield Materials                     | Copper                    |
| Jacket Material and Color            | Tan                       |

##### Electrical Specifications

|                                  |       |
|----------------------------------|-------|
| Impedance, Ohms                  | 50    |
| Maximum Operating Frequency, GHz | 40    |
| Maximum Operating Voltage, Volts | 2,000 |

##### Electrical Specifications by Frequency

###### Frequency 1

|                                 |             |
|---------------------------------|-------------|
| Frequency, MHz                  | 1000        |
| Attenuation, dB/100ft [dB/100m] | 60 [196.85] |
| Power Handling, Watts           | 10          |

###### Frequency 2

|                                 |              |
|---------------------------------|--------------|
| Frequency, GHz                  | 10           |
| Attenuation, dB/100ft [dB/100m] | 190 [623.36] |
| Power Handling, Watts           | 3.1          |

###### Frequency 3

|                                 |              |
|---------------------------------|--------------|
| Frequency, GHz                  | 20           |
| Attenuation, dB/100ft [dB/100m] | 280 [918.64] |
| Power Handling, Watts           | 2            |

##### Mechanical Specifications

###### Temperature

|                        |             |
|------------------------|-------------|
| Operating Range, deg C | -55 to +100 |
|------------------------|-------------|

###### Inner Conductor

|                   |                   |
|-------------------|-------------------|
| Number of Strands | 1                 |
| Material          | Copper Clad Steel |
| Plating           | Silver            |
| Diameter, in [mm] | 0.008 [0.2]       |

###### Dielectric:

|                   |              |
|-------------------|--------------|
| Type              | PTFE         |
| Diameter, in [mm] | 0.026 [0.66] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [034 Semi-rigid Coax Cable with Copper Outer Conductor PE-034SR](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



## 034 Semi-rigid Coax Cable with Copper Outer Conductor

## TECHNICAL DATA SHEET

PE-034SR

**Shield:**

|                   |              |
|-------------------|--------------|
| Number of         | 1            |
| Material 1        | Copper       |
| Diameter, in [mm] | 0.034 [0.86] |

**Jacket:**

|                                       |            |
|---------------------------------------|------------|
| Color                                 | Tan        |
| One Time Minimum Bend Radius, in [mm] | 0.5 [12.7] |
| Weight, lbs/ft [Kg/m]                 | 0.002 [0]  |

**Compliance Certifications** (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

**Plotted and Other Data**

|        |                            |
|--------|----------------------------|
| Notes: | Values at 25 °C, sea level |
|--------|----------------------------|

034 Semi-rigid Coax Cable with Copper Outer Conductor from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [034 Semi-rigid Coax Cable with Copper Outer Conductor PE-034SR](#)


URL: <http://www.pasternack.com/semirigid-0.034-50-ohm-coax-cable-copper-pe-034sr-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



### 034 Semi-rigid Coax Cable with Copper Outer Conductor

### 034 Semi-rigid Coax Cable with Copper Outer Conductor



NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE

**PE-034SR**

REV. A  
FSCM NO. 53919

**CAD FILE 022808-A**

**SCALE N/A**

**SIZE A**

147

**PE PASTERNAK®**  
Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623  
**Phone:** (949) 261-1920 | **Fax:** (949) 261-7451  
**Website:** [www.pasternack.com](http://www.pasternack.com) | **E-Mail:** [sales@pasternack.com](mailto:sales@pasternack.com)