

MHV Male Right Angle Connector Clamp/Solder Attachment for RG59B/U, RG62, RG71

PE4227



Configuration

- MHV Male Connector
- MIL-STD-348A
- 50 Ohms
- Right Angle Body Geometry
- Connector Interface Types: RG59B/U, RG62, RG71

Features

- Max. Operating Frequency 200 MHz
- Good VSWR of 1.6:1
- Gold Plated Brass Contact
- 30 µin minimum contact plating

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

Pasternack's PE4227 Right Angle, MHV, Standard, Connector is part of our full line of RF components available for same-day shipping. Our MHV male connector operates up to a maximum frequency of 200 MHz and offers good VSWR of 1.6:1. Its right angle body geometry allows for easier connections in tight spaces.

Our MHV male right angle connector PE4227 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		200	MHz
VSWR			1.6:1	
Operating Voltage (AC)			1,600	Vrms
Impedance		50		Ohms

Mechanical Specifications

Size

Length	1.22 in [30.99 mm]
Width	0.57 in [14.48 mm]
Height	1.02 in [25.91 mm]
Weight	0.068 lbs [30.84 g]

MHV Male Right Angle Connector Clamp/Solder Attachment for RG59B/U, RG62, RG71

PE4227



Material Specifications

Description	Material	Plating
Contact	Brass	Gold 30 µin minimum
Insulation	PTFE	
Body	Brass	Nickel 100 µin minimum
Coupling Nut	Brass	Nickel 100 µin minimum
Gasket	Silicone	
Washer	Brass	Nickel
O-Ring	Silicone	

Mechanical Specification Notes:

When attaching the connector to the cable use a clamp torque value of 26 to 30 in-lbs [2.94 to 3.39 Nm]

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:


MHV Male Right Angle Connector Clamp/Solder Attachment for RG59B/U, RG62, RG71

PE4227




Assembly Instruction

1. SLIDE CLAMP NUT ①, THIN-WASHER ② & GASKET ③ OVER CABLE. STRIP CABLE AS SHOWN. DO NOT NICK BRAID WHILE CUTTING JACKET. TAPER END OF BRAID TO PERMIT ASSEMBLY OF CLAMP ④.



2. SLIDE BRAID CLAMP ④ OVER BRAID & SEAT AGAINST CABLE. FORM BRAID OVER CLAMP NUT. TRIM BRAID BACK TO SHOULDER. CUT DIELECTRIC & CENTER CONDUCTOR TO DIMENSION SHOWN. DO NOT NICK CENTER CONDUCTOR. TIN CENTER CONDUCTOR. SLIDE ASSEMBLY INTO BODY, SOLDER CENTER CONDUCTOR IN PLACE & TIGHTEN CLAMP NUT ①. SLIDE O-RING GASKET ⑥ OVER THE CAP ⑤ BEFORE SCREW DOWN INTO PLACE.



MHV Male Right Angle Connector Clamp/Solder Attachment for RG59B/U, RG62, RG71

PE4227



MHV Male Right Angle Connector Clamp/Solder Attachment for RG59B/U, RG62, RG71 from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MHV Male Right Angle Connector Clamp/Solder Attachment for RG59B/U, RG62, RG71 PE4227](https://www.pasternack.com/mhv-male-rg59b-u-rg62-rg71-connector-pe4227-p.aspx)


URL: <https://www.pasternack.com/mhv-male-rg59b-u-rg62-rg71-connector-pe4227-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE4227 CAD Drawing

MHV Male Right Angle Connector Clamp/Solder Attachment for RG59B/U, RG62, RG71

REVISIONS		
REV.	DESCRIPTION	DATE
A	PCR PE4227 20200930	11/18/20
		SRAUTUS



THIRD-ANGLE PROJECTION



THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
PASTERNAK CORPORATION
ALL RIGHTS RESERVED

SHEET OF

1

SCALE
N/A

	N/A
--	-----

REV

17	A
----	---

PE **PASTERNAK**
an INFINITE[®] brand

Pasternack Enterprises, Inc.
P.O.Box 16759, Irvine, CA 92623.

Phone: 1.949.261.1920 | 1.866.727.8376

Fax: 1.949.261.7451

Website: www.pasternack.com

E-mail: sales@pasternack.com

SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	50040	CH	D

A	53919	SLI	PE419
---	-------	-----	-------

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

	$X = \pm 2$	[5.08]	FRACTIONS
max	1.00	1.54	1.418

.XX = ±.02 [.51]	± 1/32
.XXX = ±.005 [.13]	ANGLES ± 1°

CABLE LENGTH (L) TOLERANCES:

$$L \leq 12 [305] = +1 [25] / -0$$
$$12[305] < L \leq 60[1524] = +2[51] / -0$$
$$20 [3048] < L \leq 300 [7620] = +6 [152] / -0$$

300 [7620] < L = +5%L / -0

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY

ARE FOR REFERENCE ONLY.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T-Rev.D