

Mini SMP Male VITA 67 Connector Solder Attach for PE-086, PE-P086HF, PE-P086LL, PE-P086FLX



PE45540

Configuration

- Mini SMP Male Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: PE-P086, PE-P086HF, PE-P086LL, PE-P086FLX
- VITA 67 Design

Features

- Max. Operating Frequency 26.5 GHz
- Good VSWR of 1.45:1
- Gold Plated Beryllium Copper Contact
- Contact plating according to ASTM B488
- Blind Mate Connector
- Coaxial interconnects on VPX platforms
- Standard MIL-STD-348 SMPM interface
- Rugged Stainless Steel construction
- Accepts 0.047" and 0.086" cable contacts for end-to-end solution

Applications

- General Purpose Test
- Custom Cable Assemblies
- Robust and Rugged high speed cabled solution
- VITA 67 Backplane
- High Density Applications

Description

Pasternack's PE45540 4-position block housing is part of our full line of VITA 67 Backplane solutions and is available for same-day shipping. Pasternack introduces 4 position (VITA 67.1) and 8 position (VITA 67.2) RF connector housings designed for 3U and 6U formats within the OpenVPX architecture. These blocks are machined from stainless steel for a rugged solution. The blocks are designed to accept both PE45535 (.047" cable contact) & PE45536 (.086" cable contact) used in flexible or semi-rigid cables. These blocks are ideal for blind mating daughtercards to motherboards as the RF contacts provide +/- .010" radial misalignment tolerance and have excellent return loss up to 26.5 GHz.

The SMPM (Mini-SMP) blind mate connector is ideal for applications where direct visual or tactile access to the connection point is not possible, for example, when two circuit boards need to be mated. The block's right angle body geometry allows for easier connections in tight spaces.

Our SMPM (Mini-SMP) right angle block PE45540 specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		26.5	GHz
VSWR			1.45:1	
Dielectric Withstanding Voltage (AC)			325	Vrms
Inner Conductor DC Resistance			6	mOhms
Outer Conductor DC Resistance			5	mOhms
Insulation Resistance	5,000			MOhms

Mini SMP Male VITA 67 Connector Solder Attach for
PE-086, PE-P086HF, PE-P086LL, PE-P086FLX



PE45540

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Impedance		50		Ohms

Mechanical Specifications

Size	
Length	0.42 in [10.67 mm]
Width	0.16 in [4.06 mm]
Height	0.16 in [4.06 mm]
Weight	0.0016 lbs [0.73 g]
Mating Cycles	500 Cycles
Engagement Force	4.25lbs [1.93kg]
Disengagement Force	3.5lbs [1.59kg]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold ASTM B488
Insulation	Teflon	
Body	Beryllium Copper	Gold ASTM B488
Retaining Ring	Beryllium Copper	Nickel SAE-AMS-QQ-N-290

Environmental Specifications

Temperature

Operating Range

Humidity

Shock

Vibration

Thermal Shock

-55 to 125 deg C

1,000 megohms within 5 minutes after removal from humidity, tested per MIL-STD-202, Method 106

Sawtooth pulse of 100 g 6ms per MIL-STD-202, Method 213, Condition I

MIL-STD-202, Method 214, Test Condition I, Curve D

MIL-STD-202, Method 107, Test Condition A

Compliance Certifications

(see product page for current document)

Plotted and Other Data

Notes:

Mini SMP Male VITA 67 Connector Solder Attach for
PE-086, PE-P086HF, PE-P086LL, PE-P086FLX



PE45540

Mini SMP Male VITA 67 Connector Solder Attach for PE-086, PE-P086HF, PE-P086LL, PE-P086FLX from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Male VITA 67 Connector Solder Attach for PE-086, PE-P086HF, PE-P086LL, PE-P086FLX PE45540](#)

URL: <https://www.pasternack.com/mini-smp-male-pe-p086-pe-p086hf-pe-p086flx-connector-pe45540.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE45540 CAD Drawing

Mini SMP Male VITA 67 Connector Solder Attach for PE-086, PE-P086HF, PE-P086LL, PE-P086FLX

