



4.9 GHz to 5.8 GHz 23 dBi Broadband Patch Antenna

Antennas Technical Data Sheet

PE51FP1010

Features

- Heavy duty UV-resistant all weather radome
- DC ground lightning protection
- Can be mounted for horizontal or vertical polarization

- N-Female connector
- Includes tilt and swivel mast mount

Applications

- 4.9/5.8 GHz Indoor/Outdoor Wireless LAN systems
- Supports IEEE 802.11 a/n applications
- WiMAX, WISP, WiFi, Communication

- Homeland Security and Public Safety Band
- Wireless video systems

Description

The Hyperlink PE51FP1010 flat panel antenna is designed to operate from 4.9 GHz to 5.8 GHz (4750-5850MHz). The wide band design of this antenna eliminates the need to purchase different antennas for each frequency. This simplifies installations since the same antenna can be used for a wide array of wireless applications.

This aesthetically pleasing antenna features a heavy-duty UV-resistant plastic radome ideal for all-weather indoor and outdoor operation. The PE51FP1010 antenna is supplied with a tilt and swivel mast mount kit. This allows quick installation at various degrees of up/down tilt for easy alignment.

Configuration

Design	Panel
Band Type	Wide
Radiation Pattern	Directional
Polarization	Vertical or Horizontal
Connector Type	N Female
Number of Ports	1
Lightning Protection	DC Ground

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Input VSWR			1.5:1	
Impedance		50		Ohms
Input Power			50	Watts

Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	4,900-5,850					MHz
Gain	23	23				dBi
Horizontal Beam Width	11					Degrees
Vertical Beam Width	11					Degrees
Maximum Input Power	50	50				Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [4.9 GHz to 5.8 GHz 23 dBi Broadband Patch Antenna PE51FP1010](#)



4.9 GHz to 5.8 GHz 23 dBi Broadband Patch Antenna

Antennas Technical Data Sheet

PE51FP1010

Mechanical Specifications

Radome Material

ASA

Size

Overall Length

12.4 in [314.96 mm]

Width

12.4 in [314.96 mm]

Height

0.98 in [24.89 mm]

Mounting Mast Diameter

0.75 to 2 in [19.05 to 50.80 mm]

Weight

3.65 lbs [1.66 kg]

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Wind Loading


130 MPH [209.21 KPH]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Radiation Pattern



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [4.9 GHz to 5.8 GHz 23 dBi Broadband Patch Antenna PE51FP1010](#)



4.9 GHz to 5.8 GHz 23 dBi Broadband Patch Antenna

Antennas Technical Data Sheet

PE51FP1010

4.9 GHz to 5.8 GHz 23 dBi Broadband Patch Antenna from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [4.9 GHz to 5.8 GHz 23 dBi Broadband Patch Antenna PE51FP1010](#)




URL: <https://www.pasternack.com/wide-antenna-0-dbi-gain-n-pe51fp1010-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE51FP1010 CAD Drawing

4.9 GHz to 5.8 GHz 23 dBi Broadband Patch Antenna

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/12/2020	M.MILLER



THIRD-ANGLE PROJECTION	
THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.	
PASTERNAK an INFINITE® brand	© Pasternak Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasternak.com E-mail: sales@pasternak.com
SCALE	1 OF 1
ITEM NO.	PE51FP1010

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS
TOLERANCES:

X = ± 2 [5.08]	FRACTIONS $\pm 1/32$
XX = $\pm .02$ [.51]	ANGLES $\pm 1^\circ$
XXX = $\pm .005$ [.13]	CABLE LENGTH (L) TOLERANCES: L \leq 12 [305] = ± 1 [25] / -0 12 [305] < L \leq 60 [1524] = ± 2 [51] / -0 60 [1524] < L \leq 120 [3048] = ± 4 [102] / -0 120 [3048] < L \leq 300 [7620] = ± 6 [152] / -0 300 [7620] < L = $\pm 5\%$ L / -0

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
EU RoHS Directive (Most Recent Released Version)
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE
WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.