

## Low PIM 100 Watt RF Load 0.4 GHz to 6 GHz with N-type Female Black Anodized Aluminum



### RF Terminations Technical Data Sheet

**PE6TR1152**

#### Features

- 50 Ohm Impedance
- 400 to 6,000 MHz Frequency Range
- VSWR 1.25:1
- Max Power 100 Watts (CW)
- PIM rating -168dBc Typical
- N Female Coaxial Interface

#### Applications

- Wireless
- SatCom
- Test and Measurement
- Commercial and Military Communication
- Base Station
- 4G/AWS/PCS

#### Description

Pasternack's PE6TR1152 is a high power RF cable termination (also called RF load or dummy load) that operates from 400 to 6,000 MHz and handles up to 100 Watts (CW). Our N termination / load is a 50 Ohm impedance and has a female gender. PE6TR1152 load termination offers 1.25:1 VSWR and low PIM (passive intermodulation) of -168 dBc typical. This Pasternack 100 Watts terminator has a heatsink body which is designed to provide adequate heat dissipation within its full frequency of operation.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, hybrids, and combiners. They are also widely used in measurement systems to ensure accurate results. Pasternack offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watts (CW).

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.4		6	GHz
Impedance		50		Ohms
VSWR		1.25:1		
Passive Intermodulation		-168	-160	dBc
2x43dBm				
Input Power (CW)			100	Watts
Input Power (Peak)			1	kWatts
8% duty cycle, 20us PW				

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Low PIM 100 Watt RF Load 0.4 GHz to 6 GHz with N-type Female Black Anodized Aluminum PE6TR1152](#)

Low PIM 100 Watt RF Load 0.4 GHz to 6 GHz with  
N-type Female Black Anodized Aluminum



## RF Terminations Technical Data Sheet

**PE6TR1152**

### Mechanical Specifications

#### Size

Length

5.12 in [130.05 mm]

Width

4.25 in [107.95 mm]

Height

3.78 in [96.01 mm]

Weight

2.2 lbs [997.9 g]

Package Type

Connectorized

#### Configuration

Connector

N Female

Termination Design

RF Load

### Material Specifications

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold
Body	Brass	Tri-Metal
Housing	Black Anodized Aluminum Heatsink	

### Environmental Specifications

#### Temperature

Operating Range

-40 to +75 deg C

Storage Range

-50 to +85 deg C

Humidity

<95%

Shock

IEC 60068-2-27

Vibration

IEC 60068-2-6-Fc

Altitude

<5000m

Thermal Shock

IEC 60068 -2-14-Na

### Compliance Certifications

(see [product page](#) for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Low PIM 100 Watt RF Load 0.4 GHz to 6 GHz with N-type Female Black Anodized Aluminum PE6TR1152](#)

Low PIM 100 Watt RF Load 0.4 GHz to 6 GHz with  
N-type Female Black Anodized Aluminum



## RF Terminations Technical Data Sheet

**PE6TR1152**

Low PIM 100 Watt RF Load 0.4 GHz to 6 GHz with N-type Female Black Anodized Aluminum from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Low PIM 100 Watt RF Load 0.4 GHz to 6 GHz with N-type Female Black Anodized Aluminum PE6TR1152](#)

URL: <https://www.pasternack.com/100-watts-n-female-rf-load-6-ghz-low-pim-pe6tr1152-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE6TR1152 CAD Drawing

Low PIM 100 Watt RF Load 0.4 GHz to 6 GHz with N-type Female Black Anodized Aluminum

