

5 Watt RF Load Up to 18 GHz With N-Type Female Input Brass Body



PE6TR1175

Features

- DC to 18 GHz Frequency Range
- VSWR <1.2:1
- Max Power 5 Watt (CW)
- N-Type Female Coaxial Interface

Applications

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communications

Description

Pasternack's PE6TR1175 is an RF termination (also called RF load or dummy load) that operates from DC to 18 GHz and handles up to 5 Watt (CW). Our N-Type termination/load has a female gender. PE6TR1175 N-Type load termination offers 1.2:1 VSWR max.

RF load / termination are indispensable components in many RF, microwave and millimeter wave systems where signal reflections from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Pasternack offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
VSWR, Input			1.2:1	
Input Power (CW)			5	Watts
Derated linearly to 1.5W @ 165°C				
Dielectric Withstanding Voltage (AC)			2,500	Vrms
Operating Voltage (AC)			1,000	Vrms

Mechanical Specifications

Size

Length	1.587 in [40.31 mm]
Width	0.709 in [18.01 mm]
Height	0.709 in [18.01 mm]
Weight	0.086 lbs [39.01 g]

Configuration

Connector	N Female
Mating Torque	6 to 10 in-lbs [0.68 to 1.13 Nm]

5 Watt RF Load Up to 18 GHz With N-Type Female Input Brass Body



PE6TR1175

Material Specifications

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold over nickel
Insulation	Teflon	
Connector 1 Body	Brass	Copper-Tin-Zinc Alloy

Environmental Specifications

Temperature

Operating Range

-55 to +70 deg C

Humidity

MIL-STD-202, Method 106

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

5 Watt RF Load Up to 18 GHz With N-Type Female Input Brass Body from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [5 Watt RF Load Up to 18 GHz With N-Type Female Input Brass Body PE6TR1175](#)

URL: <https://www.pasternack.com/5-watts-n-female-rf-load-18-ghz-pe6tr1175-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE6TR1175 CAD Drawing

5 Watt RF Load Up to 18 GHz With N-Type Female Input Brass Body

